

BC020008

LED Strip Drivers

24V 30W Non-dimmable IP20 driver

Features & Benefits

- 24V 30W Non-dimmable IP20 driver for use with single colour and RGBW LED strip



WARRANTY



CLASS II



RATING

General Information

Trade Name

Environment

Suitable For Zones

Product Group

Color Finish

Product Shape

Overall Dimensions

Length (mm)

Width (mm)

Height (mm)

Product Weight(kg)

Additional Information

Recommended Product Location

IP Rating

Origin of manufacturer

Warranty

Led Tape

Indoor

Outside zone 2

LED Strip - accessory

White

Rectangular

153 x 41 x 32mm

153

41

32

0.125

For use with: LED Strip 24V 4.8W(max run 6.25m) LED Strip

24V 9.6W(max run 3.12m)LED Strip 24V 14.4W(max run 2.08m)

For indoor use only

IP20

Made in China

2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for

Driver Manufacturer

Lighting Product Type 1

Lighting Product Type 2

Electrical

Voltage Rating

Primary Running Current(Amp)

Operating Frequency Hz

Constant Current or Constant Voltage

Class

Output Voltage Max/Range (VDC)

EMC Compliant (EN55015)

Power Factor Correction

Input Electrical Connections

Dimmable

Thermals

Thermal Cut Out

Insulation Coverage

Operating Temperature Range °C

Controls and Sensors

Power Consumption

Max LED Load

Construction

Primary Material

Packaging

Quantity Per Outer Carton

Outer carton(L)- cm

Outer carton(W)- cm

Outer carton(H)- cm

Outer carton Gross weight- kg

Product Bar Code EAN-13 Number

Standards & Approvals

Manufactured In Accordance To

CE Marked

UKCA Marked

Date code/Purchase order No.

WEEE Symbol

terms and conditions)

JCC

Accessory

Tapelight

220-240

1.25

50/60Hz

CV

II

24

Yes

0.95

Loop in/out, Live and Neutral

No

yes

Do not cover

-15 to +45

>0.5W with no load

30W

Polycarbonate

50

32.5

23.5

19

9.25

5052544104428


IEC 62384:2006, GB24825-2009

Yes

Yes

Yes

Yes



L:153mm W:41mm H:32mm

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.

Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | sales@jcc.co.uk | www.jcc.co.uk

Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 141 [17/01/2023]