

BC020007

LED Strip Drivers

24V 180W Non-dimmable IP20 driver

Features & Benefits

- 24V 180W Non-dimmable IP20 driver for use with single colour and RGBW LED strip



WARRANTY



CLASS II



RATING

General Information

Trade Name

Environment

Suitable For Zones

Product Group

Color Finish

Product Shape

Overall Dimensions

Length (mm)

Width (mm)

Height (mm)

Product Weight(kg)

Additional Information

Recommended Product Location

IP Rating

Origin of manufacturer

Warranty

Led Tape

Indoor

Outside zone 2

LED Strip - accessory

White

Rectangular

345 x 50 x 35mm

345

50

35

0.85

For use with: LED Strip 24V 4.8W(max run 37.5m) LED Strip 24V 9.6W(max run 18.75m)LED Strip 24V 14.4W(max run 12.5m)


For indoor use only

IP20

Made in China

2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for

Driver Manufacturer	terms and conditions)
Lighting Product Type 1	JCC
Lighting Product Type 2	Accessory
	Tapelight
Electrical	
Voltage Rating	220-240
Operating Frequency Hz	50/60Hz
Secondary running current(mA)	7500
Constant Current or Constant Voltage	CV
Class	II
Output Voltage Max/Range (VDC)	24
EMC Compliant (EN55015)	Yes
Power Factor Correction	0.95
Input Electrical Connections	Loop in/out, Live and Neutral
Dimmable	No
Thermals	
Thermal Cut Out	yes
Insulation Coverage	Do not cover
Operating Temperature Range °C	-20 to +50
Controls and Sensors	
Power Consumption	>1W with no load
Max LED Load	180W
Construction	
Primary Material	Polycarbonate
Packaging	
Quantity Per Outer Carton	20
Product Bar Code EAN-13 Number	5052544092183
Standards & Approvals	
Manufactured In Accordance To	BS EN 61347
CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



L:345mm W:50.1mm H:35mm

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.
Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | sales@jcc.co.uk | www.jcc.co.uk
Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 141 [17/01/2023]