

# JC14224BLK

## Discontinued – No Longer Available

Starspot 600 Track spot kit 3000K Black

### Features & Benefits

- Track kit includes: 3 x Starspot 600 spotlights
- 1120mm track section and 86mm live end section and 86mm live end
- 20% greater light output than 50W GU10 halogen
- Over 80% energy saving against halogen
- Zero maintenance
- no need to relamp
- Triac dimmable as standard



### General Information

|                                |   |
|--------------------------------|---|
| Trade Name                     | Starscoop   |
| Environment                    | Indoor  |
| Product Group                  | LED - Track   |
| Color Finish                   | Black   |
| Product Shape                  | Cylinder  |
| Product Range                  | Starspot 600  |
| Product Weight(kg)             | 1.97  |
| Light Source                   | LED   |
| Light Source Features          | Warm White  |
| Luminaire Accessories          | Track Kit Includes: 3 x JC14222BLK & 1120mm track section & 86mm live end |
| Recommended product location   | Indoor use only   |
| IP Rating                      | IP20  |
| Origin of manufacturer         | Made in Taiwan  |
| Warranty                       | 5 Year Warranty (See Website for terms and conditions)                    |
| Dimming Protocol Compatibility | Triac   |
| Driver manufacturer            | Mains LED CHIP  |
| LED manufacturer/type          | EDC/38C/8W/830/230V/A001/LUMENS   |

|                         |            |
|-------------------------|------------|
| Lighting Product Type 1 | Track Head |
| Customs Tariff code**   | 9405421000 |

Electrical

|                            |     |
|----------------------------|-----|
| Luminaire Circuit Wattage1 | 21  |
| Class                      | I   |
| Dimmable                   | yes |

Performance Data



|                                |   |
|--------------------------------|---|
| Energy Rating                  | This product contains a light source of energy efficiency class F |
| Lumens Per Circuit Watt1       | 83  |
| Color Rendering Index          | 80-89   |
| CRI: Ra                        | 85  |
| Correlated Colour Temperature1 | 3000K   |
| Beam Angle °                   | 36  |

Packaging

|                                |               |
|--------------------------------|---------------|
| Product Bar Code EAN-13 Number | 5052544084096 |
|--------------------------------|---------------|

Standards & Approvals

|                               |                                  |
|-------------------------------|----------------------------------|
| Manufactured in accordance to | BS EN 60598-2-1                  |
| CE Marked                     | yes                              |
| UKCA Marked                   | Yes                              |
| Date code/Purchase order No.  | Yes                              |
| Certificate Of Conformity     | Available on request             |
| Accredited Members            | LIA, ISO9001-2015, ISO14001-2015 |



\*\*JCC Lighting Limited makes every effort to ensure that the Customs Tariff information in this document is timely and accurate. However, it's not possible for us to assure the absolute veracity and completeness of that information, as errors may occur. The placement of any inaccurate tariff information is completely unintentional. JCC Lighting Limited reserves the right, in its sole discretion, to correct any errors or omissions to the tariff code and to make any and all changes contained in this document at any time and without notice. It is the sole responsibility of the importer to ensure that

the commodity code advised is correct for the products/goods being supplied by JCC Lighting Limited. JCC Lighting Limited does not assume any liabilities, losses, costs, and expenses arising out of or related to the importers use of this commodity code or the information related to the import of any JCC Lighting products.

---

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.

Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | [sales@jcc.co.uk](mailto:sales@jcc.co.uk) | [www.jcc.co.uk](http://www.jcc.co.uk)

Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 114 [17/02/2025]