


S1000 and S2000 Series Surge Protective Strips

TYPE 3 SURGE PROTECTIVE DEVICES



Overview:

Leviton's S1000 and S2000 Series Surge Protected Strips provide superior protection for everyday use in professional work areas and home offices, protecting computers, peripherals and other electronic devices from damaging surges, voltage transients and noise spikes.

These surge protective strips feature a convenient right angle plug that keeps the cord close to the wall making it easier to install behind furniture and other equipment. The high quality construction and superior electronic circuitry ensures long service life of both the surge protective strip and protected equipment.

Features:


- Diagnostic LEDs for Surge Protection, Polarity, and Ground
- Resettable circuit breaker and internal fusing circuit protection
- Audible alarm indicates loss of surge protection
- Multi-line protection (L-N, L-G, N-G)
- Optional Coax and Telco surge protection
- All units feature a right angle NEMA 5-15P Plug
- UL 1449 Compliant
- 5-Year Limited Product Warranty
- 5-Year Limited Connected Equipment Warranty up to \$25,000

Specifications


Catalog Number	S1000-PS, S1000-S15, S1000-PTC	S2000-PS, S2000-S15, S2000-PTC
Electrical Specifications		
Amperage	15 A	
Voltage	120 VAC	
Frequency	50/60 Hz	
Surge Technology	MOV	
Performance Data		
Maximum Continuous Operating Voltage	150 V	
Joules	1010 J	2020 J
Maximum Surge Current, Per Mode (L-N)	25 kA	62.5 kA
Voltage Protection Rating (VPR)	L-N	600 V
	L-G	700 V
	N-G	700 V
Noise Filtering	-8 dB to -25 dB (@100K-100MHz)	-10 dB to -20 dB (@5M-100MHz)
Material Specifications		
Enclosure	ABS Plastic	
Standards and Certifications		
UL 1449	cULus Listed	
ANSI/IEEE Category A, B & C	C-62.41 & C-62.45	
NOM	057	
Warranties		
Product Warranty	5-Year Limited	
Connected Equipment Warranty	Up to \$10,000	Up to \$25,000

Dimensions

Common to S1000 Series



Common to S2000 Series



Ordering Information

Type 3 Surge Protective Strips, 6 & 9 NEMA 5-15R Outlets, Beige							
Catalog Number	Maximum Input Current	Joules	Audible Alarm	Data Protection	Enclosure	Number of Outlets	Cord Length
S1000-PS	15 Amp	1010 J	Yes	-	ABS Plastic	6	6 Feet
S1000-S15	15 Amp	1010 J	Yes	-	ABS Plastic	6	15 Feet
S1000-PTC	15 Amp	1010 J	Yes	RJ-11, Coax	ABS Plastic	6	6 Feet
S2000-PS	15 Amp	2020 J	Yes	-	ABS Plastic	9	6 Feet
S2000-S15	15 Amp	2020 J	Yes	-	ABS Plastic	9	15 Feet
S2000-PTC	15 Amp	2020 J	Yes	RJ-45, Coax	ABS Plastic	9	6 Feet

Visit our Website at:
www.leviton.com/surge
 email: commercial@leviton.com

Q-684A

110821

Leviton Manufacturing Co., Inc.
 201 N Service Rd, Melville, NY 11747
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2021 Leviton Manufacturing Co., Inc. All rights reserved.

