

Multi-Lens PAR Fixture



The Leviton Multi-Lens PAR fixture offers the economies of a PAR style fixture with the flexibility of multiple lenses to achieve different field angles and the popular 575 & 750W lamps as the LEO Ellipsoidal fixture. Four lenses are offered with each fixture to achieve Very Narrow, Narrow Spot, Medium, and Wide Flood field angles. Tool free entry for lamp replacement and lens changes, cooltouch lens rotating ring, and rugged die-cast construction make this fixture an excellent complement to any inventory.

FEATURES

- Rugged die-cast aluminum construction
- Tool free access to reflector, lens, and lamp replacement
- Thermally insulated knobs
- Gel frame retainer clip
- ETL listed
- 120-240V, 50/60 Hz
- Up to 750W
- Tool free lens changes
- Insulated lens rotating ring
- 36" high temperature lead
- Four lenses provided:
 - Very Narrow Spot (round beam)
 - Narrow Spot (round beam)
 - Medium Flood (oval beam)
 - Wide Flood (oval beam)
- The removable, two-slot accessory holder has a self-closing, self-locking latch for safety
- Parabolic reflector made of high-grade aluminum, polished to a mirror finish
- Positive locking dog on yoke
- G9.5 medium two-pin lamp holder accepts a wide variety of non-proprietary lamps
- Lower wattage lamps drastically reducing power consumption while simultaneously increasing dimmer capacity
- Accepts standard 10" accessories

ORDERING INFORMATION

CAT. NO.	DESCRIPTION
PARML-00B	Multi-Lens PAR fixture, black, bare wire. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL
PARML-00W	Multi-Lens PAR fixture, white, bare wire. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0PB	Multi-Lens PAR fixture, black, with 15A 5-15 PBG plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0PW	Multi-Lens PAR fixture, white, with 15A 5-15 PBG plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0SB	1, Multi-Lens PAR fixture, black, with stage pin plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0SW	Multi-Lens PAR fixture, white, with stage pin plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0TB	Multi-Lens PAR fixture, black, with locking L5-15 plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-0TW	Multi-Lens PAR fixture, white, with locking L5-15 plug. Include C-clamp, color frame, and (4) lenses: VNSP, NSP, MFL, & WFL.
PARML-LEN	Multi-Lens PAR lens set, (4) lenses (VNSP, NSP, MFL, & WFL)
PARML-SPB	Multi-Lens PAR socket assembly, cord & 5-15P, Black
PARML-SPW	Multi-Lens PAR socket assembly, cord & 5-15P, White

LAMPS

CAT. NO.	DESCRIPTION	DIMENSIONAL DATA	
LOGLA-000	GLA 115V 575W	Width	8 1/2" (21.59cm)
LOGLC-000	GLC 115V 575W	Length	8 5/16" (21.59cm)
LOGLD-000	GLD 115V 750W		
LOGLE-000	GLE 115V 750W	Height	10 5/8" (26.99cm)
LOGKV-000	GKV 230V 600W	Weight	13.3lbs (6kg)
LOGKV-LLO	GKV/LL 230V 600W		

Multi-Lens PAR Lighting Fixtures