

NE200 Infrared Remote Control

Application

Leviton's NE200 Infrared Remote Control is a handheld device for use with LCnet devices equipped with an IR receiver.

Operation

Leviton's NE200 Infrared Remote Control allows lighting control and programming from up to 40 feet (and a 100° angle) from compatible Leviton wall controllers and other IR-receiving devices. The NE200 has four programming buttons, four preset buttons, and four lighting control buttons: On, Off, Dim, and Bright. Its preset buttons allow four distinct light levels to be stored and selected.

The NE200 can be used to program the following LCnet power pack settings:

- Minimum Light Level
- Maximum Light Level
- Light Maintain Level
- Preset Light Levels

Features and Benefits

GENERAL

- Provides handheld remote control of LCnet lighting systems.
- Enables programming of four preset light levels, which can be selected with a push of a button.
- Features a range of 40 feet, at a 100° maximum angle.
- Can be used to program an LCnet power pack with Minimum Light, Maximum Light, and Light Maintain Levels.


Specifications

Electrical

Input Voltage: 6VDC
 Batteries Required: 4 AAA (sold separately)
 Infrared Range: Up to 40 feet and a 100° angle from IR receiver

Physical

Size: 6.8 x 2.0 x .84in. (10.5 x 5.1 x 2.1cm)
 Color: black



Environmental

Operating Temperature Range: 0°C to +55°C
 Storage Temperature Range: -10°C to +85°C
 Relative Humidity: 20% to 90% non-condensing

Warranty: Limited 2-Year Warranty

Leviton's Limited Two-Year Warranty

This warranty gives you specific rights, and you may also have other rights, which vary in different states and countries. Leviton warrants to the original consumer purchaser that this product is free of defects in materials and workmanship for 2 years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option, if within such 2 years the product is returned prepaid, with proof of purchase date, and a description of the problem to the Leviton Manufacturing Co., Inc., ATTN: Quality Assurance Department, 59-25 Little Neck Pkwy., Little Neck, NY 11362-2591. This warranty does not cover labor for removal or reinstallation of the product and is void on any product installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner. There are no implied warranties of any kind, but if implied warranties are required by the applicable jurisdiction, Leviton limits the duration of any implied warranty of fitness for use or merchantability to 2 years. Leviton is not liable for incidental or consequential damages, including without limitation, loss of equipment use and lost sales or profits for breach of any warranty on this product. Some jurisdictions may not allow exclusion of or limitations on how long an implied warranty lasts or the exclusion or limitation of incidental or consequential damages, so the above exclusions or limitations may not even apply to you.

LEVITON SPECIFICATIONS SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>



Leviton Mfg. Co., Inc.
 59-25 Little Neck Pkwy • Little Neck, NY 11362-2591 • Tech Line: 1-800-824-3005 • Fax: 1-800-832-9538

Visit our Website at: www.leviton.com

