


PAR Lighting Fixtures



Leviton's rugged and cost-effective PAR can fixtures offer a durable and value-conscious lighting option.

APPLICATIONS

- Musical Groups
- Performance troupes
- Theatres
- Event venues
- DJ's
- Clubs
- Houses of worship

FEATURES

- UL Listed: UL File #E187577
- Rigid, rolled edge frame
- Solid steel clutch mechanism (Par 56, 64)
- Includes color frame at no extra cost
- Black, white and polished aluminum versions available



DIMENSIONAL DATA: IN. [CM] LBS. [KG]			
	38	56	64
Width	7-1/4 (18.42)	9-7/8 (25.08)	10-3/16 (25.88)
Length	7-1/2 (19.05)	14-1/2 (36.83)	16-3/4 (42.55)
Height	9-3/4 (24.77)	9-7/8 (25.08)	18-3/16 (46.20)
Weight	2.75 (1.25)	4.65 (2.11)	5.5 (2.48)

RATINGS		
Model	Max Wattage	Socket Type
Par 38	120	Medium Screw Base
Par 56	500	Mogul End-Prong
Par 64	1,000	Mogul End-Prong

PAR Lighting Fixtures

CAT.NO.	DESCRIPTION
PAR38-oBL	Par 38 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, Black, UL Listed
PAR38-oCR	Par 38 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, Polished, UL Listed
PAR56-oBL	Par 56 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, Black, UL Listed
PAR56-oCR	Par 56 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, Polished, UL Listed
PAR56-oWH	Par 56 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, White, UL Listed
PAR64-oBL	Par 64 Fixture with Color Frame, 15A PBG Connector, Black, UL Listed
PAR64-oCR	Par 64 Fixture with Color Frame, 15A PBG Connector, Polished, UL Listed
PAR64-oWH	Par 64 Fixture with Yoke and 3 Foot Cable, 15A PBG Connector, White, UL Listed
ACCESSORIES	
NCCLA-MP0	Light Duty Black Steel C-Clamp
DYS56-000	DYS Par 56 Reflector Kit
DYS64-000	DYS Par 64 Reflector Kit
TAoCC-000	C-Clamp for 1 1/2" ID Pipe
TAoSC-000	Safety Cable

NOTE: Limited PAR38 lamps are available. Please contact customer service to order. Par38 lamps are also widely available from various suppliers.

LAMPS	
LP56N-300	300W Par 56 NSP
LP56M-300	300W Par 56 MFL
LP56W-300	300W Par 56 WFL
LP64N-500	500W Par 64 NSP
LP64M-500	500W Par 64 MFL
LP64W-500	500W Par 64 WFL
LQ500-MFL	500W Par 56 MFL
LQ500-NSP	500W Par 56 NSP
LQ500-WFL	500W Par 56 WFL
LoFFN-000	FFN/VNSP 1000W 120V 3200K 500HR PAR 64
LoFFR-000	FFR/MFL 1000W 120V 3200K 500HR PAR 64
LoFFS-000	FFS/WFL 1000W 120V 3200K 500HR PAR 64
CONNECTORS	
TAOCI-OSB	Factory-Installed 20A Stagepin Connector
TAOCI-OPB	Factory-Installed 20A PBG (5-15P)
TAOCI-OTB	Factory-Installed Locking (L5-20P)

LEVITON SPECIFICATION SUBMITTAL	
JOB NAME:	CATALOG NUMBERS:
JOB NUMBER:	

Leviton Manufacturing Co., Inc. Lighting & Energy Solutions

20497 SW Teton Avenue, Tualatin, OR 97062
 Telephone: 1-800-736-6682 • FAX: 503-404-5594 • Tech Line (6:00AM-4:00PM P.S.T. Monday-Friday): 1-800-959-6004

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 • Telephone: 1-800-469-7890 • FAX: 1-800-563-1853

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel. (+52) 55-5082-1040 • FAX: (+52) 5386-1797 • www.leviton.com.mx

Visit our Website at: www.leviton.com/les

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.