


## Combo Phone and Data Board 1x4 Bridged Phone and 4-port Cat 5e

### APPLICATION

Telephone and Data Expansion Boards are designed for use in Leviton STRUCTURED MEDIA™ enclosures, including the Multi Dwelling Unit (MDU) Enclosure and 14", 21", 28", and 42" STRUCTURED MEDIA Enclosures to support a variety of telephone distribution configurations. Expansion boards snap into molded-in brackets in Leviton MDU Enclosures, or can be attached to Leviton pre-configured structured cabling panels, single plastic brackets, or expansion plastic brackets.



### SPECIFICATION

The Combo Phone and Data Board shall provide a 1x4 bridged telephone interface and four Cat 5e ports supporting up to four telephone and four data locations. Boards shall mount in compatible Leviton Structured Media brackets and panels. Telephone and Data Expansion Boards shall be ANSI/TIA compliant for performance and transmission requirements and shall be UL Listed.

### FEATURES & BENEFITS

- Provides both data and phone connections on a single board
- Phone portion provides four telephone lines to up to four locations via IDC punchdowns
- Provides four ports of Cat 5e 150 MHz data connections via modular RJ-45 jacks and 4-pair 110-type IDC punchdowns

### STANDARDS & REGULATIONS

- ANSI/TIA-570
- ANSI/TIA-568
- ANSI/TIA-1096 (formerly FCC Part 68)
- UL Listed cULus, UL 1863

### MECHANICAL SPECIFICATIONS

Dimensions: See page 2  
Temp. (Storage): -40 °C to +70 °C (-40 °F to +158 °F)  
Temp. (Installation): Refer to cable installation temperature  
Temp. (Operating): -10 °C to +60 °C (+14 °F to +140 °F)

### COUNTRY OF ORIGIN


Mexico

### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](http://Leviton.com/ns/warranty)

**PRODUCT SPECIFICATIONS**  
**47609-4DP**

**47609-4DP**



| PART NUMBER   |           |
|---|-----------|
| Description   | Part No.  |
| Combo Phone and Data Board, 1x4 Bridged Phone and 4-port Cat 5e | 47609-4DP |

For further support information, visit [Leviton.com/ns/support](http://Leviton.com/ns/support)

Page 2 of 2

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
[infoUSA@leviton.com](mailto:infoUSA@leviton.com)  
 BERK-TEK™ Cable  
 +1 (800) 237 5835 | [infoUSA@leviton.com](mailto:infoUSA@leviton.com)

**Asia Pacific**  
 +852 3620 2602  
[infoAPAC@leviton.com](mailto:infoAPAC@leviton.com)

**Canada**  
 +1 (800) 461 2002  
[infoCanada@leviton.com](mailto:infoCanada@leviton.com)

**Europe**  
 +44 (0) 1592 772124  
[infoEurope@leviton.com](mailto:infoEurope@leviton.com)

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

**Middle East & Africa**  
 +971 (4) 247 9800  
[infoMEA@leviton.com](mailto:infoMEA@leviton.com)

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.