

## 38 mm x 25 mm LJ6C-Style Inserts

### APPLICATION

LJ6C-style inserts fit into 38 mm x 25 mm LJ6C-style openings. Inserts with spring-loaded shutters accept all QUICKPORT™ UTP and shielded jacks. Inserts without shutters accept QUICKPORT shuttered fiber adapters. The inserts are available in flat and angled designs and include ID window kits for port designation. Inserts are available in white ABS plastic.



LI137-AW1



LI137-AFW



LI137-1W1



LI137-FFW

### SPECIFICATION

Inserts shall be compatible with 25 mm x 38 mm LJ6C-style openings and shall be available in flat or angled port orientation. Inserts with shutters shall accept QUICKPORT UTP and shielded jacks. Inserts with shutters shall include port designation kits and shall have a shutter to protect QUICKPORT connectors without built in shutters from dust and debris when not in use. Inserts without shutters shall be available in flat or angled port orientation and shall accept QUICKPORT fiber adapters.

### FEATURES & BENEFITS

- Inserts with shutters are compatible with all Leviton QUICKPORT UTP and shielded jacks
- Includes ID window for port designation
- Inserts with spring-loaded shutters protect copper jacks while not in use
- Inserts without shutters are compatible with QUICKPORT fiber shuttered adapters

### DESIGN CONSIDERATIONS

- Designed to fit 22 mm x 37 mm, 1.2-2.0 mm thick plate openings

### MECHANICAL SPECIFICATIONS

Dimensions: See page two  
Materials: ABS plastic

### COUNTRY OF ORIGIN

LI137-1W1, -AW1: Taiwan  
LI137-FFW, -AFW: China  
MMCBLK06C3: China






### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](http://Leviton.com/ns/warranty)

LI137-xxx; MMCBLK06C3

**PRODUCT SPECIFICATIONS**  
**LI137-xxx; MMCBLK06C3**

**LI137-xxx; MMCBLK06C3**



Measurements are in mm and [inches]

**COMPATIBILITY**

Part No.	Compatible with LI137-FFW	Compatible with LI137-AFW
41086-LL*	Yes	Yes
41085-AS*	Yes	Yes
41085-S+C	Yes	No
41085-TP*	Yes	No
41084-S+Z	Yes	No

\* = colors: Ivory (I), White (W), Grey (G), Black (E), Orange (O), Blue (L), Yellow (Y), Dark Red (R), Brown (B), Light Almond (T), Green (V), Purple (P), Crimson Red (C)  
 † = colors: Ivory (I), White (W), Grey (G), Black (E).



**Installation Note:** With angled adapter LI137-AFW applications, installers must manually flip orientation of fiber adapter inside the QUICKPORT™ bezel by 180° to allow fiber patch cord release tabs access. See product instruction sheet for details.

**PART NUMBER**

Description	Part No.
38 mm x 25 mm 1-Port Flat Lj6C-Style Insert with Shutter, white	LI137-1W1
38 mm x 25 mm 1-Port Angled Lj6C-Style Insert with Shutter, white	LI137-AW1
38 mm x 25 mm 1-Port Flat Lj6C-Style Insert, for QUICKPORT™ fiber adapters, white	LI137-FFW
38 mm x 25 mm 1-Port Angled Lj6C-Style Insert, for QUICKPORT fiber adapters, white	LI137-AFW
38 mm x 25 mm Blank Flat Lj6C-Style Insert, white	MMCBLK06C3

For further support information, visit [Leviton.com/ns/support](http://Leviton.com/ns/support)