

## DECORA<sup>®</sup> Dual-gang AC Power Enclosure

### APPLICATION

The DECORA Dual-Gang AC Power Enclosure provides power to active gear housed inside the STRUCTURED MEDIA™ Center enclosure. The enclosure is comprised of a powder-coated steel box and dual DECORA cover plate. Install up to two DECORA receptacles to power the active devices housed in the enclosure including routers, switches, modems, AV, and security active gear.



### SPECIFICATION

The AC power enclosure shall have openings for two DECORA receptacles. It shall be a 54.8 cubic inch box and a dual DECORA cover plate constructed from 16 gauge powder-coated steel. The enclosure shall be compatible with Leviton DECORA style rectangular power devices and install in to Leviton STRUCTURED MEDIA center enclosures. The enclosure shall provide four (4) knock-out options for cable ingress and two #10-32 grounding points. The enclosure shall be c(UL)us listed (UL 514A).

### DESIGN CONSIDERATIONS

- Customize power and connectivity based on project needs
- Allows for upgrading and swapping receptacles in the future without replacing the entire enclosure
- White powder coating contains up to 25% post-consumer recycled plastic, mitigating plastic waste and reducing carbon emissions
- A total of four (4) 1/2 in cable knock-outs, on sides and bottom for power service connections accept installer provided cable clamp or box connector
- Two grounding points provided with green grounding screws supporting up to two independent circuits
- Supports up to two DECORA style rectangular devices. If configuring with a single device use a blank DECORA style insert to fill unused opening (PART NO. 80414-2W)

### MECHANICAL SPECIFICATIONS

Dimensions: 70.6 mm (2.78") (H) x 251 mm (9.88") (W) x 74.1 mm (2.92") (D)  
Materials: 16 gauge galvanized steel  
Temp. (Storage): -40 °C to +70 °C (-40 °F to +158 °F)  
Temp. (Installation): Refer to cable installation temperature  
Temp. (Operating): -10 °C to +60 °C (+14 °F to +140 °F)  
Humidity (Max.): 95% relative humidity, non-condensing

### STANDARDS & REGULATIONS

- UL 514A Listed Outlet Box

### COUNTRY OF ORIGIN




Mexico

### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](http://Leviton.com/ns/warranty)

**PRODUCT SPECIFICATIONS**  
**47605-EDP**

47605-EDP



Shown with separately available DECORA receptacles installed

**PART NUMBER**

Description	Part No.
DECORA® Dual-Gang AC Power Enclosure, white, empty	47605-EDP

**RECOMMENDED LEVITON POWER OUTLETS FOR THE DECORA® AC POWER ENCLOSURE**

Description	Color Options	Part No.
Duplex Receptacle, Non-surge Lever Edge 15 Amp	White	E5325-W
15 Amp Decora Tamper-Resistant Duplex Outlet/Receptacle, grounding	White, Black, Brown, Gray, Ivory, Light Almond	T5325
15 Amp, 125 Volt, Decora Plus Surge Protective Duplex Outlet/Receptacle, commercial grade	White, Blue, Black, Ivory, Light Almond	T7280
30W (6A) USB Dual Type-C/C Power Delivery Wall Outlet Charger with 15A Tamper Resistant Outlet	White, Black, Brown, Gray, Ivory, Light Almond	T5635
60W (6A) USB Dual Type-C/C Power Delivery Wall Outlet Charger with 15A Tamper Resistant Outlet	White, Black, Brown, Gray, Ivory, Light Almond	T5636
60W (20V@2.5A+ 5V@2A) USB Dual Type A/Type-C Power Delivery Wall Outlet Charger with 15A Tamper-Resistant Outlet	White, Black, Brown, Gray, Ivory, Light Almond	T5634
5.1A USB Type A/Type-C Wall Outlet Charger with 15A Tamper-Resistant Outlet	White, Red, Black, Brown, Gray, Ivory, Light Almond	T5633
30W (6A) USB Dual Type-C/C Wall Outlet Charger with 15A Tamper-Resistant Outlet	White, Black, Brown, Gray, Ivory, Light Almond	T5637
4.2A 4-Port USB Type-A Wall Outlet Charger	White, Black, Gray, Ivory, Light Almond	USB4P

For further support information, visit [Leviton.com/ns/support](http://Leviton.com/ns/support)



**USA**  
Network Solutions Headquarters  
+1 (800) 722 2082  
infoUSA@leviton.com  
  
BERK-TEK™ Cable  
+1 (800) 237 5835 | infoUSA@leviton.com

**Asia Pacific**  
+852 3620 2602  
infoAPAC@leviton.com

**Canada**  
+1 (800) 461 2002  
infoCanada@leviton.com

**Europe**  
+44 (0) 1592 772124  
infoEurope@leviton.com

**Latin America**  
MX: +52 (55) 2128 6286  
LATAM: +52 (55) 2333 5963  
infoLATAM@leviton.com

**Middle East & Africa**  
+971 (4) 247 9800  
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.