


Half RU Universal Flat Patch Panel

APPLICATION

Leviton's Half RU Universal Flat Patch Panels provide high density patching where rack space is a premium. This makes them ideal for use in many applications including health care, manufacturing, datacenters, and other environments where rack space is limited. Universal Flat QUICKPORT™ Patch Panels are available in 24 ports and designed to provide a high-density option with a low profile.



SPECIFICATION

Patch panels shall be available in a 24-port configuration and shield data from electromagnetic and radio frequency interference. Panels shall accept both shielded and unshielded QUICKPORT™ jacks and connectors. Panels shall have a black powder coat finish with white silk screening. Panels shall meet or exceed ANSI/TIA-568.0-E, and IEC 60603-7.

FEATURES & BENEFITS

- Panels allow mix-and-match of shielded and unshielded QUICKPORT™ jacks and connectors
- Panel includes hardware to accept standards-compliant grounding connectors
- Shielding provides EMI/RFI protection and data security
- Included Rear Cable Manager supports incoming copper cables
- Mounts on standard 19-inch racks and cabinets

DESIGN CONSIDERATIONS

- Verify rack is grounded according to commercial building grounding and bonding requirements for telecommunications

STANDARDS & REGULATIONS

- ANSI/TIA 568.0-E
- IEC 60603-7

MECHANICAL SPECIFICATIONS

Dimensions:	See page two
Materials:	18-gauge steel, black powder coat
Temp. (Storage):	-40 °C to +70 °C (-40 °F to +158 °F)
Temp. (Installation):	Refer to cable installation temperature
Temp. (Operating):	-10 °C to +60 °C (+14 °F to +140 °F)
Humidity (Max.):	95% relative humidity, non-condensing

COUNTRY OF ORIGIN

China




WARRANTY INFORMATION

For Leviton product warranties, go to Leviton.com/ns/warranty

4S255-4BH

PRODUCT SPECIFICATIONS
4S255-4BH

4S255-4BH



PART NUMBER	
Description	Part No.
Universal Flat Patch Panel, 24 ports, Half RU with cable management tray	4S255-4BH

For further support information, visit Leviton.com/ns/support

Page 2 of 2

USA
Network Solutions Headquarters
+1 (800) 722 2082
infoUSA@leviton.com

Leviton Cable (formerly Berk-Tek)
+1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
+852 3620 2602
infoAPAC@leviton.com

Canada
+1 (800) 461 2002
infoCanada@leviton.com

Europe
+44 (0) 1592 772124
infoEurope@leviton.com

Latin America
MX: +52 (55) 2128 6286
LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
+971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.