


Angled Optical Fiber Cleaver for APC Connectors

APPLICATION

The 49886-APC angled optical fiber cleaver supports the 49991-ASC FastCAM field installable prepolished SC/APC connector, having an internal 8° cleave resulting in the greatest level of return loss performance. The advanced cleaver design features a simple “stapler action” for streamlined and uninterrupted cleaving with maximum reliability and time efficiency. This compact cleaver also includes a built-in scrap collector for securely storing fiber scraps. The 49886-APC represents an economical cleaver with advanced functions for user-friendly and precision cleaving.



FEATURES

- Rugged low maintenance construction
- Cleave angle of 8° (+/- 0.5 degree)
- Repeatable preset 8° cleaves
- Easy to use “stapler action”
- Built-in fiber scrap collector
- Multi-position diamond blade provides 10,000 cleaves per blade
- RoHS compliant

DESIGN CONSIDERATIONS

The cleaver design features a simple “stapler action” for streamlined and uninterrupted cleaving with maximum reliability and time efficiency. This compact cleaver also includes a built-in scrap collector for securely storing fiber scraps. The 49886-APC is an economical cleaver with advanced functions for user-friendly and precision cleaving. Required for termination of Leviton SC/APC FastCAM connectors

STANDARDS COMPLIANCE

RoHS compliant

PHYSICAL SPECIFICATIONS

Dimensions: 60W x 50D x 40H (mm)
 Weight: 200 g
 Coating Diameter: 250-900 μm
 Cladding Diameter: 125 μm
 Typical Cleave Angle: 8° (+/- 1 degree)

COUNTRY OF ORIGIN

United Kingdom

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.

PART NUMBERS

Description	Part No.
Angled Optical Fiber Cleaver for APC Connectors	49886-APC

Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +44.0.1592.772124 E customerservice@brand-rex.com	India / SAARC T +971.4.886.4722 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com