

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

OPT-X™ HDX Connectivity Platform

100G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QSFP-100G-SR4	MM	MPO12	Yes 4 x SFP-25G-SR	LC	42NM2-S5C	24	42NM2-S5C	42LSM2-21C	25G		3		12
					42NM4-BCN	12	42NM4-BEN	N/A	N/A		3	N/A	N/A
					5FUHD-6MP	8 or 12	5FUHD-6MP	42LSM1-41C	25G		6		12
QSFP-100G-SRBD	MM	LC	No	N/A	42LM2-21C	24	42LM2-21C	N/A	N/A		12	N/A	N/A
					41LSM1-UNN	12	41LSM1-UNN	N/A	N/A		6	N/A	N/A
					48LSM1-41C	8 or 12	48LSM1-41C	N/A	N/A		4	N/A	N/A
QSFP-100G-PSM4	SM	MPO12	Yes 4 x SFP-25G-LR	LC	U2NM2-S5C	24	U2NM2-S5C	U2LM2-21C	25G		3		12
					U2MM1-BCN	12	U2MM1-BEN	U1LSM1-UNN	25G		3		6
					5FUHD-6MP	8 or 12	U2MM1-BEN	U2LSM1-41C	25G		6		12

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

OPT-X™ HDX Connectivity Platform

100G MODULES (CONTINUE)													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QSFP-100G-CWDM4	SM	LC	No	N/A	U2LSM2-21C	24	U2LSM2-21C	N/A	N/A		12	N/A	N/A
					U1LSM1-UNN	12	U1LSM1-UNN	N/A	N/A		6	N/A	N/A
					U8LSM1-41C	8 or 12	U8LSM1-41C	N/A	N/A		4	N/A	N/A
400G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QDD-400G-VSR4 OSFP-400G-VSR4	MM	MPO-12 APC	Yes 4x 100G to QSFP-100G-VR/SR	LC	42NM2-S5C	24	42NM2-S5C	42LSM2-21C	25G		3		12
					42NM4-BCN	12	42NM4-BEN	N/A	N/A		3	N/A	N/A
					5FUHD-6MP	8 or 12	5FUHD-6MP	42LSM1-41C	25G		6		12
QDD-400G-DR4 QSFP-400G-DR4	SM	MPO-12	Yes 4x 100G to QSFP-100G-DR	LC	U2NM2-S5C	24	U2NM2-S5C	U2LSM2-21C	100G		3		12
					U2NM1-BCN	12	U2NM1-BEN	U1LSM1-UNN	100G		3		6
					5FUHD-6MP	8 or 12	5FUHD-6MP	U2LSM1-41C	100G		6		12

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

OPT-X™ HDX Connectivity Platform

400G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QDD-400G-SRBD OSFP-400G-SRBD	MM	MPO12	Yes 4 x QSFP-100G-SRBD	LC	42NM2-S5C	24	42NM2-S5C	42LSM2-21C	100G		3		12
					42NM4-BCN	12	42NM4-BEN	41LSM1-UNN	100G		3	N/A	N/A
					5FUHD-6MP	8 or 12	5FUHD-6MP	42LSM1-41C	100G		6		12
QDD-400G-FR4 OSFP-400G-FR4	SM	LC	No	N/A	U2LM2-21C	24	U2LM2-21C	N/A	N/A		12	N/A	N/A
					U1LSM1-UNN	12	U1LSM1-UNN	N/A	N/A		6	N/A	N/A
					U8LSM1-41C	8 or 12	U8LSM1-41C	N/A	N/A		4	N/A	N/A
QDD-400G-SR8 OSFP-400G-SR8	MM	MPO16	Yes 2 x 200GBASE-SR4		S44TM2-JUP	24	S44TM2-JUP	S46LSM2-JUP	50G		N/A		N/A
QDD-400G-SR8 OSFP-400G-SR8	MM	MPO16	Yes 4x 100GBASE-SR		S44TM2-JUP	24	S44TM2-JUP	S46LSM2-JUP	50G		N/A		N/A

Note: Above does not include Long Reach and Extended Reach Modules (LR4, ER4)

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

e2XHD Connectivity Platform

100G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QSFP-100G-SR4	MM	MPO12	Yes 4 x SFP-25G-SR	LC	ULE2XHD-F024NHKDS5	24	ULE2XHD-F024NHKDS5	ULE2XHD-F024CSHQES4	25G		3		12
					E2XHD-4MP	12	N/A	ULE2XHD-F012CSKQDU	25G		4		4 Active / 6
					E2XHD-4MP	8 or 12	N/A	ULE2XHD-F008CSKQDJ	25G		4		4
QSFP-100G-SRBD		LC	No	N/A	ULE2XHD-F024CSHQES4	24	ULE2XHD-F024CSHQES4	N/A	N/A		12	N/A	N/A
					ULE2XHD-F012CSKQDU	12	ULE2XHD-F012CSKQDU	N/A	N/A		6	N/A	N/A
					ULE2XHD-F008CSKQDJ	8 or 12	ULE2XHD-F008CSKQDJ	N/A	N/A		4	N/A	N/A
QSFP-100G-PSM4	SM	MPO12	Yes 4 x SFP-25G-LR	LC	ULE2XHD-A024NHKDS5	24	ULE2XHD-A024NHKDS5	ULE2XHD-A024CSHLES4	25G		3		12
					E2XHD-4MP	12	N/A	ULE2XHD-A012CSKLDU	25G		4		4 Active / 6
					E2XHD-4MP	8 or 12	E2XHD-4MP	N/A	25G		4	N/A	12

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

e2XHD Connectivity Platform

100G MODULES (CONTINUE)													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QSFP-100G-CWDM4	SM	LC	No	N/A	ULE2XHD-A024CSHLES4	24	ULE2XHD-A024CSHLES4	N/A	N/A		12	N/A	N/A
					ULE2XHD-A012CSKLDU	12	ULE2XHD-A012CSKLDU	N/A	N/A		6	N/A	N/A
					ULE2XHD-F008CSKQDJ	8 or 12	ULE2XHD-F008CSKQDJ	N/A	N/A		4	N/A	N/A
400G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QDD-400G-VSR4 OSFP-400G-VSR4	MM	MPO-12 APC	Yes 4x 100G to QSFP28 100GBASE-VR1/ SR1	Duplex LC	ULE2XHD-F024NHKDS5	24	ULE2XHD-F024NHKDS5	ULE2XHD-F024CSHQES4	100G		3		12
					E2XHD-4MP	12	N/A	ULE2XHD-F012CSKQDU	100G		4		4 Active / 6
					E2XHD-4MP	8 or 12	N/A	ULE2XHD-F008CSKQDJ	100G		4		4
QDD-400G-DR4 OSFP-400G-DR4	SM	MPO-12	Yes 4x 100G to QSFP- 100G-DR	LC	ULE2XHD-A024NHKDS5	24	ULE2XHD-A024NHKDS5	ULE2XHD-A024CSHLES4	100G		3		12
					E2XHD-4MP	12	N/A	ULE2XHD-A012CSKLDU	100G		4		4 Active / 6
					E2XHD-4MP	8 or 12	E2XHD-4MP	N/A	100G		4	N/A	12

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics

e2XHD Connectivity Platform


400G MODULES													
Arista P/N	Media Connector Interface		Breakout	B/O Media Connector Interface	Leviton Near End Cassette P/N	Leviton Trunk Connector BASE	Leviton Far End Cassette P/N	Leviton Far End Breakout Cassette P/N	Breakout Lane Speed	Example (Near End/Far End)	Number of Native Ports per cassette	HDX Example (Breakout Side)	Number of Breakout Ports per cassette
QDD-400G-SRBD OSFP-400G-SRBD	MM	MPO12	Yes 4 x QSFP-40/100G-SRBD	LC	ULE2XHD-F024NHKDS5	24	ULE2XHD-F024NHKDS5	ULE2XHD-F024CSHQES4	100G		3		12
					E2XHD-4MP	12	N/A	ULE2XHD-F012CSKQDU	100G		3		4 Active / 6
					E2XHD-4MP	8 or 12	N/A	ULE2XHD-F008CSKQDJ	100G		4		4
QDD-400G-FR4 OSFP-400G-FR4	SM	LC	No	N/A	FME2XHD-A024CKLEA	24	FME2XHD-A024CKLEA	N/A	N/A		12	N/A	N/A
					ULE2XHD-A012CSLLDU	12	ULE2XHD-A012CSLLDU	N/A	N/A		6	N/A	N/A
					ULE2XHD-A008CSLLDJ	8 or 12	ULE2XHD-A008CSLLDJ	N/A	N/A		4	N/A	N/A

Note: Above does not include Long Reach and Extended Reach Modules (LR4, ER4)

Leviton Cabling Guide for Arista 100G, 400G, and 800G Optics e2XHD Connectivity Platform

BASIC CABLING COMPONENTS			
Description	Leviton Plenum P/N	Leviton LSZH P/N	
24F MTP®-MTP Trunk, OS2	FTU-AW4024JJxxxM36C36CN-NNBS	FTU-AZ024JJyyyy09C09CN-NNBS	[A]
24F MTP-MTP Trunk, OM4	FTU-FW4024JJxxxM36C36CN-NNBS	FTU-FZ024JJyyyy09C09CN-NNBS	[B]
24F Array Cord, OS2	ULUP4JJ-BxxxM	ULUP4CJJ-Byyyy-S	[C]
24F Array Cord, OM4	UL544JJ-BxxxM	UL544CJJ-Byyyy-S	[D]
16F Array Cord, OM4 APC	546PSS-ByyyyM	546CSS-Byyyy-S	[E]
16F Array Cord, OS2	UP6PSS-ByyyyM	UP6CSS-Byyyy-S	[F]
8F Array Cord, OS2	UP8FMM-ByyyyM	UP8CMM-Byyyy-S	[G]
8F Array Cord, OM4	548FMM-ByyyyM	548CMM-Byyyy-S	[H]
8F Array Cord, OM4 APC	548FGG-ByyyyM	548CGG-Byyyy-S	[I]
LC-LC Patch Cord, OS2	PCF-S2PR2VV-yyyyMAB	VPC-S2R2LULUyyyy	[J]
LC-LC Patch Cord, OM4	PCF-M4PD1RR-yyyyMAB	VPC-M4D1LCLCyyyy	[K]
CS - LC Patch Cord, OS2	FPC-S2PR2VJ-xxxMAB	PCF-S2LR2VJ-yyyyMAB	[L]

xxx = Length in whole digits (Ex. "050 is 50 ft/m overall length)
 yyyy = Length including one decimal place (Ex. "0500 is 50 ft/m in overall length, "0505" is 50.5 ft/m in overall length)
 Trunk Fiber Count: replace "024" in part number with 012, 016, 032, 048, 064, 072, 096, 128, 144, 192
 MTP is a registered trademark of US Conec, Ltd.



ARISTA TRANSCEIVER EXAMPLES

