

# The Leviton Load Center Meter Main for Canadian Market

**UG/OH Service Entrance with Distribution Section and Feed-thru Lugs**

## APPLICATION

Leviton Load Center Meter Main Panels combine the Meter and Main Breaker into one easy-to-install unit. Each Meter Main includes 8 spaces to enable easy wiring of outdoor circuits.

## FEATURES AND BENEFITS

- NEMA 3R
- 22kA Interrupt Rating
- In Compliance with CSA Std. C22.2 No.29, 94.2, and 0.19 and Standards UL 50, UL 50E, UL 67
- Powder Coated

**FASTEST INSTALLATION** - Wire the entire panel without a single circuit breaker in place. At final installation, simply plug on the breaker.

**INTUITIVE** - Circuit Breakers feature color indicators in the handle for operational status at-a-glance

**SPACIOUS** - Ample room for hands to move and work freely



Cat. No. LS815-BRC

THE LEVITON LOAD CENTER METER MAIN

# PRODUCT SPECIFICATIONS

## Ring-Type Meter Main, UG/OH Service Entrance with Distribution Section and Feed-Through Lugs

Amp Rating	# of Spaces/Circuits	Catalog Number	Bypass	Cover
100	8	LS810-BRC	None	Ring-Type
150	8	LS815-BRC	None	Ring-Type
200	8	LS820-BRC	None	Ring-Type

### SPECIFICATIONS

**Warranty:** 10-Year Limited

### ELECTRICAL SPECIFICATIONS

**Short Circuit Current Rating:** 22 KA

**Spaces/Circuits:** 8/8

**Type:** Outdoor

**Type of Load Center:** Meter Main

**Voltage:** 120/240 VAC

**Busbar rating (all panels):** 225A

### MECHANICAL SPECIFICATIONS

**Busbar Material:** Copper, Bright Tin-Plated

**Enclosure Material:** Galvanized Steel, Gray Baked Enamel

**Ground Connection:** 4 AWG - 2/0 AWG Cu/Al

**Material:** Galvanized Steel

**Supply Connections:** 6 AWG - 350 MCM

**Weight:** 56.8 lbs

### STANDARDS & CERTIFICATIONS

**CSA Std. C22.2 No.29:** Yes

**CSA Std. C22.2 No.94.2:** Yes

**CSA Std. C22.2 No.0.19:** Yes

**UL 50:** Yes

**UL 50E:** Yes

**UL 67:** Yes


**UL 869A:** Yes

### DIMENSIONAL DRAWINGS

**LS810-BRC, LS815-BRC, LS820-BRC**

Meter Socket Over/Under Construction - 100, 150 & 200 Ampere,  
Ring-Type, No Bypass

**Dimensions:** 37.11" H x 16.47" W x 5.2" D



THE LEVITON LOAD CENTER METER MAIN



**Leviton Manufacturing Co., Inc.**

Tech Line: 1-800-824-3005

Mon-Fri 8am-10pm EST, Saturday 9am-7pm EST, Sunday 9am-5pm EST

For 24/7 product support visit [www.leviton.com/support](http://www.leviton.com/support)

**Visit our Website at: [www.leviton.com/loadcenter](http://www.leviton.com/loadcenter)**

© 2022 Leviton Manufacturing Co., Inc. All rights reserved.  
All trademarks are the property of their respective owners.