

## e2XHD QuickPort Pass-Through Fiber Cassettes

### APPLICATION

The e2XHD Patching System, an easy-to-connect, high-density solution, provides simple termination and improved cable routing for both fiber and copper applications. QuickPort Pass-Through Cassettes quickly snap-in and pull out of the e2XHD high-density panels, making installation easier than ever.



e2XHD MTP  
Pass-Through Cassette



e2XLC-SBL 12-fiber OS2  
QuickPort LC Shuttered  
Cassette

### SPECIFICATION

Pass-Through Fiber cassettes shall snap into rear of all e2XHD panels and shall require no tools to remove. Fiber cassettes shall accept 12 fibers in QuickPort LC and 96 fibers in QuickPort MTP. LC adapters shall use ceramic ferrules and shall provide IP5x-rated internal shutters, compliant with IEC 60529, that open and close automatically with the insertion and removal of an LC Connector. Cassettes shall meet all ANSI/TIA-568.3-D requirements (for performance) and respective ANSI/TIA-604-X (for intermateability) standards. QuickPort Pass-Through LC Cassettes shall use zirconia ceramic sleeves. All cassettes shall be made in the USA.

### COUNTRY OF ORIGIN

USA

### FEATURES

- OM3, OM4, or OS2 available for pass-through cassettes
- Alignment tabs on panel ensure upright insertion of cassettes
- To remove cassettes from panel, simply pull on back handle
- A QuickPort Connector Removal Tool is available to remove QuickPort connectors from cassettes

### DESIGN CONSIDERATIONS

- Panels hold up to 48 duplex fiber channels per rack unit
- Panel accepts up to eight copper and/or fiber cassettes

### PHYSICAL SPECIFICATIONS

Materials: Cold-rolled steel and high-performance plastics  
Capacity: 6 LC fiber adapters or 4 MTP adapters

### STANDARDS COMPLIANCE

- ANSI/TIA-568.3-D for performance requirements
- ANSI/TIA-604-5 (MTP), -10B (LC) for connector intermateability
- IEC 60529 IP5x dust protection (LC)

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com](http://www.leviton.com).

#### Leviton Network Solutions

2222 - 222nd St. SE  
Bothell, WA 98021-4416

tel 1-800-824-3005  
tel +1-425-486-2222  
[appeng@leviton.com](mailto:appeng@leviton.com)  
[www.leviton.com](http://www.leviton.com)

**Asia / Pacific**  
T +1.631.812.6228  
E [infoasean@leviton.com](mailto:infoasean@leviton.com)

**Europe**  
T +44.0.1592.772124  
E [customerserviceeu@leviton.com](mailto:customerserviceeu@leviton.com)

**Canada**  
T +1.514.954.1840  
E [pcservice@leviton.com](mailto:pcservice@leviton.com)

**Mexico**  
T +52.55.5082.1040  
E [lsamarketing@leviton.com](mailto:lsamarketing@leviton.com)

**Caribbean**  
T +1.954.593.1896  
E [infocaribbean@leviton.com](mailto:infocaribbean@leviton.com)

**Middle East & Africa**  
T +971.4.247.9800  
E [imeinfo@leviton.com](mailto:imeinfo@leviton.com)

**China**  
T +852.2774.9876  
E [infochina@leviton.com](mailto:infochina@leviton.com)

**South Korea**  
T +82.2.3273.9963  
E [infokorea@leviton.com](mailto:infokorea@leviton.com)

**Colombia**  
T +57.1.743.6045  
E [infocolombia@leviton.com](mailto:infocolombia@leviton.com)

