

British Standard Receptacle BS 1363 Switched Outlet

Modern design with outstanding performance

The smart choice for residential and light commercial applications



Safe. Reliable. Quality. Performance.

As a leader in the electrical wiring device industry, Leviton is proud to introduce the new british standard receptacle. This stylish 13A 250V tamper-resistant receptacle, includes a double pole switch, integrated to the circuit to cut off the current on both contacts.

- Accommodates plug and outlet type G markets
- Durability in impact resistant materials
- Contacts and terminals made of brass for top quality performance
- Tamper-resistant for safety of children and others
- Certified: BS 1363, SASO 2203, IEC 60884-1, IEC 60884-2-3
- Aesthetically appealing Decora design



BSRDP-W

Locations Using Plug Type G

Country	Voltage	Frequency	Plug Type
Bahrain	230V	50Hz	G
Bangladesh	220V	50Hz	C, D, G, K
Belize	110V 220V	60Hz	A, B, G
Bhutan	230V	50Hz	C, D, F, G, M
Botswana	230V	50Hz	D, G, M
Brunei Darussalam	240V	50Hz	G
Cambodia	230V	50Hz	A, C, G
Cyprus	240V	50Hz	G
Dominica	230V	50Hz	D, G
Falkland Islands (Malvinas)	240V	50Hz	G
Gambia	230V	50Hz	G
Ghana	230V	50Hz	D, G
Gibraltar	240V	50Hz	C, G
Grenada	230V	50Hz	G
Guyana	240V	60Hz	A, B, D, G
Hong Kong	220V	50Hz	G, D
Iraq	230V	50Hz	C, D, G
Ireland	230V	50Hz	G
Isle of Man	240V	50Hz	C, G
Jordan	230V	50Hz	B, C, D, F, G, J
Kenya	240V	50Hz	G
Kuwait	240V	50Hz	C, G
Lebanon	220V	50Hz	A, B, C, D, G
Macau	220V	50Hz	D, M, G, F
Malawi	230V	50Hz	G
Malaysia	240V	50Hz	A, C, G, M

Country	Voltage	Frequency	Plug Type
Maldives	230V	50Hz	A, C, D, G, J, K, L
Malta	230V	50Hz	G
Mauritius	230V	50Hz	C, G
Myanmar	230V	50Hz	C, D, F, G
Nigeria	230V	50Hz	D, G
Oman	240V	50Hz	C, G
Pakistan	230V	50Hz	C, D, G, M
Qatar	240V	50Hz	D, G
Saint Kitts and Nevis	230V	60Hz	A, B, D, G
Sain Lucia	240V	50Hz	G
Saint Vincent and the Grenadines	230V	50Hz	A, C, E, G, I, K
Saudi Arabia	127V 220V	60Hz	A, B, F, G
Seychelles	240V	50Hz	G
Sierra Leone	230V	50Hz	D, G
Singapore	230V	50Hz	C, G, M
Solomon Islands	220V	50Hz	I, G
Sri Lanka	230V	50Hz	D, M, G
Tanzania	230V	50Hz	D, G
Uganda	240V	50Hz	G
United Arab Emirates	220V	50Hz	C, D, G
United Kingdom	230V	50Hz	G
Vanuatu	220V	50Hz	C, G, I
Yemen	230V	50Hz	A, D, G
Zambia	230V	50Hz	C, D, G
Zimbabwe	220V	50Hz	D, G


Residential Applications

- Single Family Homes
- Multi-Dwelling Units
- Condominiums
- High-Rises
- Living Room
- Bedroom
- Kitchen
- Bathroom
- Hallway

Light Commercial Applications

- Education Facilities
- Offices
- Hotels
- Restaurants
- Light Commercial Buildings
- and more...

Dimensions





Specifications

Electrical Specifications	
Amperage	13 Amp
Voltage	250 Volt
Type	BS 1363 Switched Outlet
Dielectric Voltage	Withstands 2000V per IEC 60884 and SASO 2203
Grounding	Self-Grounding
Environmental Specifications	
Flammability	Rated V-2 per UL94
Material Specifications	
Face Material	Polycarbonate
Body Material	Polycarbonate
Contact Material	Brass 0.031 Thick
Terminal Screws	Brass-M4 X 0.7 Thread
Grounding Screw	Brass 8-32
Strap Material	Galvanized Steel
Grounding Clips	Brass

Mechanical Specifications	
Line Terminal ID	Marked on device with "L"
Neutral Terminal ID	Marked on device with "N"
Ground ID	Green Screw
Terminal Accomm.	14-12 AWG
Product ID	Ratings permanently marked on device
Standards and Certifications	
BS	1363
SASO	2203
IEC	60884-1
IEC	60884-2-3
Warranty	2 Year Limited

Ordering Information

Catalog Number	Description	Color
BSRDP-W 	British Standard Receptacle, 13 Amp, 250 Volt, Decora, Tamper-Resistant, with Double-Pole Switch Integrated to the Circuit, to Cut Off the Current On Both Contacts	White
BSRDP-I 	British Standard Receptacle, 13 Amp, 250 Volt, Decora, Tamper-Resistant, with Double-Pole Switch Integrated to the Circuit, to Cut Off the Current On Both Contacts	Ivory

Leviton Mfg. Co., Inc.

201 North Service Road, Melville, NY 11747 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538

www.leviton.com © 2014

Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

Please visit our website to find your local Leviton representative and/or office near you:

www.leviton.com/worldwide