

## Renu® USB Charger/Tamper-Resistant Duplex Receptacle



### The latest addition to the Renu family of products.

The Renu® USB Charger/Tamper-Resistant Duplex Receptacle is the smart way to update the look of any room while enjoying the latest charging technology. Keep all of your favorite electronic devices charged and running – all in a snap! This innovative device combines fast, efficient charging power and the color versatility of Renu, turning your electrical wiring device into a decorative, easy to change accessory.

Renu devices feature faces which can be snapped on and off easily to update the color and create a new look for any room in the home. The latest addition to the Renu collection of switches, dimmers and receptacles, the Renu USB Charger/Tamper-Resistant Duplex Receptacle is available in 20 popular colors to blend in or contrast with a room's walls or trim.

The Renu USB Charger/Tamper-Resistant Duplex Receptacle has the capability to charge two USB powered electronic devices utilizing its two USB Ports, leaving the two Tamper-Resistant Receptacles free for other uses. The device uses smart chip technology to recognize and optimize the charging requirements of individual smart phones, tablets and more for efficient charging every time. Strategically placed vertical USB Ports provide generous room to insert and maneuver charging cords and adapter-free charging eliminates unsightly clutter contributing to a neat appearance on countertops, desktops or wherever users choose to charge.




Shown with Renu screwless wallplate  
sold separately

## Features

- Smart chip recognizes and optimizes the charging requirements of individual devices
- 3.6A charging capacity
- Two high-powered charging ports
- Two 15A or 20A Tamper-Resistant receptacles for improved safety
- USB ports are positioned vertically providing more space for maneuvering and reducing stress on USB cables
- Compatible with USB 2.0 devices
- Fits in a standard wallbox
- Back and side wired for easy installation
- Can replace existing outlets
- Can be multi-ganged with Renu devices
- Available in 20 popular colors to match any décor
- Once installed, face easily snaps OFF and ON. Change color by ordering the RKAA1 or RKAA2 color change kit
- Uses only Renu wallplates (sold separately)
- Spec Grade
- cCSAus Listed
- 5-year limited warranty

## Change colors



## Ordering Information

### Spec Grade

Cat. No.	Description	Charging Capability	Rating	Color
RUAA1	15A Renu USB Charger/ Tamper-Resistant Receptacle	3.6 AMP	15 AMP, 125V	See Color Palette
RUAA2	20A Renu USB Charger/ Tamper-Resistant Receptacle	3.6 AMP	20 AMP, 125V	See Color Palette
RKAA1	Renu USB Color Change Kit for 15A Receptacle	N/A	N/A	See Color Palette
RKAA2	Renu USB Color Change Kit for 20A Receptacle	N/A	N/A	See Color Palette

\* To order colors, add suffix to basic catalog numbers.

## Color Palette



# LEVITON®

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747-3138  
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538  
 Tech Line (8:30AM-7:00PM E.T. Monday-Friday): 1-800-824-3005

Visit our Website at: [www.leviton.com/renu](http://www.leviton.com/renu)

© 2016 Leviton Manufacturing Co., Inc. All rights reserved.  
 All trademarks are the property of their respective owners.

