

## Home Theater Interface and Multi-Room Wallplates

### APPLICATION

Leviton Home Theater Interface and Multi-Room Wallplates combine the convenience of a ready-made Wallplate with the convenience of a ready-made pre-configured wallplate with high-quality audiophile-grade connectors. Both wallplates are intended for installation 12 inches above the base of the floor and typically will be placed behind the equipment rack, in a cabinet or behind the entertainment center.



AEHTK-000



AEMRK-000

### FEATURES

- Include painted screws to match wallplates
- Home Theater Interface Wallplate features two QuickPort snap-in openings for adding other connectors (such as video connectors)
- Home Theater Interface Wallplate features RCA connectors for connecting subwoofers
- Multi-Room Stereo Speaker Wallplate integrates wallplate for connecting left and right audio speakers (+/- connections), and two extra openings for additional QuickPort connectors (e.g., adding a subwoofer)

### DESIGN CONSIDERATIONS

- For use with low-voltage rings and standard low-voltage junction boxes
- Designed for easy cable installation
- AEHTK Home Theater Interface Wallplate accommodates from 5.1 to 7.1 channel surround-sound systems which connect to the A/V Receiver
  - 5.1 = FrontR, FrontL, Center, BackR, BackL, and Subwoofer
  - 6.1 = Same as 5.1 plus Center Back
  - 7.1 = Same as 5.1 plus Back Left Surround/Back

### PHYSICAL SPECIFICATIONS

#### Home Theater Interface Wallplate

Connector Type: (front of module)	14 audiophile-grade, gold-plated black and red spring clips; 2 RCA connectors; 2 QuickPort openings
Connector Type: (back of module)	8-pin and 6-pin in-line pluggable screw terminals
Wallplate:	High-quality impact-resistant plastic
Color:	White
Design:	Standard three-gang wallplate
Mounting Depth:	2.5"/64 mm
Wiring:	14-16 gauge speaker wire

#### Multi-Room Wallplate

Connector Type: (front of module)	4 audiophile-grade, gold-plated black and red spring clips; 2 QuickPort openings
Connector Type: (back of module)	Two 2-pin in-line pluggable screw terminals
Wallplate:	High-quality impact-resistant plastic
Color:	White
Design:	Standard single-gang wallplate
Mounting Depth:	2.5"/64 mm
Wiring:	14-16 gauge speaker wire

### COUNTRY OF ORIGIN

China

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty).

#### Leviton Network Solutions

2222 - 222nd St. SE  
 Bothell, WA 98021-4416

tel 1-800-824-3005  
 tel +1-425-486-2222  
[appeng@leviton.com](mailto:appeng@leviton.com)  
[www.leviton.com](http://www.leviton.com)

**Asia / Pacific**  
 T +1.631.812.6228  
 E [infoasean@leviton.com](mailto:infoasean@leviton.com)

**Europe**  
 T +33.6.8869.1380  
 E [infoeurope@leviton.com](mailto:infoeurope@leviton.com)

**Canada**  
 T +1.514.954.1840  
 E [pcservice@leviton.com](mailto:pcservice@leviton.com)

**India / SAARC**  
 T +971.4.886.4722  
 E [infoindia@leviton.com](mailto:infoindia@leviton.com)

**Caribbean T**  
 +1.954.593.1896  
 E [infocaribbean@leviton.com](mailto:infocaribbean@leviton.com)

**Mexico**  
 T +52.55.5082.1040  
 E [lsamarketing@leviton.com](mailto:lsamarketing@leviton.com)

**China**  
 T +852.2774.9876  
 E [infochina@leviton.com](mailto:infochina@leviton.com)

**Middle East & Africa**  
 T +971.4.886.4722  
 E [lmeinfo@leviton.com](mailto:lmeinfo@leviton.com)


**Colombia**  
 T +57.1.743.6045  
 E [infocolombia@leviton.com](mailto:infocolombia@leviton.com)

**South Korea**  
 T +82.2.3273.9963  
 E [infokorea@leviton.com](mailto:infokorea@leviton.com)

**ELECTRONIC FILES**

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit [www.leviton.com](http://www.leviton.com).

**AEHTK-000, AEMRK-000**



**PART NUMBERS**

Description	Part No.
Home Theater Interface Wallplate	AEHTK-000
Multi-Room Wallplate	AEMRK-000



<b>Leviton Network Solutions</b> 2222 - 222nd St. SE Bothell, WA 98021-4416  tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	<b>Asia / Pacific</b> T +1.631.812.6228 E infoasean@leviton.com	<b>Canada</b> T +1.514.954.1840 E pcservice@leviton.com	<b>Caribbean</b> T +1.954.593.1896 E infocaribbean@leviton.com	<b>China</b> T +852.2774.9876 E infochina@leviton.com	<b>Colombia</b> T +57.1.743.6045 E infocolombia@leviton.com
	<b>Europe</b> T +33.6.8869.1380 E infoeurope@leviton.com	<b>India / SAARC</b> T +971.4.886.4722 E infoindia@leviton.com	<b>Mexico</b> T +52.55.5082.1040 E lsamarketing@leviton.com	<b>Middle East &amp; Africa</b> T +971.4.886.4722 E lmeinfo@leviton.com	<b>South Korea</b> T +82.2.3273.9963 E infokorea@leviton.com