


## Indoor/Outdoor Riser CL3R (ACRC)

### APPLICATION

Leviton's composite copper/fiber cables incorporate high bandwidth optical fibers with insulated copper TFFN or THWN conductors. A wide variety of design options are available including; up to eight 12 AWG solid conductors, twelve loose tube fibers (ACRC), and interlock armoring. These cables are listed as CMR and CL3R-OF/ PLTC-OF. A key application of these cables is to extend the distance that powered devices can be installed from the power source in Power over Ethernet (PoE+) installations using Leviton's OneReach™ PoE Extender System. The 12 AWG conductors can increase this distance from 328 feet to several thousand feet. The powered device could be an IP camera, a wireless access point, or other building automation device located in an area where an electrical outlet is not readily available.



### COUNTRY OF ORIGIN

USA

### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/NS/Warranty](http://Leviton.com/NS/Warranty)

### FEATURES & BENEFITS

- Single-mode, multimode, and hybrid designs available
- CMR and CL3R-OF/PLTC-OF, wet and dry rated
- Aluminum interlock armored cables available
- Loose tube fibers (ACRC, 1-12 fibers)
- Each cable consists of multiple TFFN or THWN copper conductors and multiple fibers cabled together within an outer jacket
- Cable design accommodates from 2 to 8 conductors and up to 12 fibers
- Enables PoE+ equipment to be located more than 100 meters from the switch when used with Leviton's OneReach™ system
- Cost savings versus installation of a new electrical outlet
- CMR and CL3R-OF/PLTC-OF allows cable to be installed in communication pathways
- Ease of installation, accommodating last minute relocations or pathway changes
- Broad design selection allows for mix and match of copper and fiber components to specific networking applications

### STANDARDS & REGULATIONS

- EN 50173; ISO/IEC 11801
- ANSI/ICEA S-104-696; ANSI/TIA-568.3-D; Telcordia GR-409; UL 13; UL 444
- ETHERNET: 10BASE – 40GBASE (10BASE, 100BASE, 1000BASE, 10GBASE, 40GBASE, 100GBASE, 400GBASE)
- Fibre Channel: 1G-FC – 128GFC (1, 2, 4, 8, 16, 32, 128 GFC)
- SONET: OC-1 – OC-768 (OC -1, 3, 12, 24, 48, 192, 768)
- SDH: STM-0 – STM-256 (STM-0, 1, 4, 16, 64, 256)
- OTN: OTU-1 – OTU4 (OTU1, 2, 2e, 2f, 3, 3e2, 4)
- CPRI: CPRI-1 – CPRI-9 (CPRI-1, 2, 3, 4, 5, 6, 7, 7a, 8, 9)
- PON (SMF ONLY): RFoG, APON, BPON, EPON, GPON, WDM-PON, NG-PON

**PRODUCT SPECIFICATIONS**  
**Indoor/Outdoor Riser CL3R (ACRC)**

**Indoor/Outdoor Riser CL3R (ACRC)**

CHARACTERISTICS	
<b>Construction</b>	
Type of cable	Loose Tube
Jacket material	Riser
<b>Usage Characteristics</b>	
Temp. (Storage):	-40 °C to +85 °C (-40 °F to +185 °F)
Temp. (Installation):	-20 °C to +60 °C (-4 °F to +140 °F)
Temp. (Operating):	-40 °C to +75 °C (-40 °F to 167 °F)

CONDUCTOR COLOR SEQUENCE	
1	Black
2	White
3	Blue
4	Yellow
5	Brown
6	Orange
7	Purple
8	Pink

TECHNICAL DATA - PHYSICAL													
Fiber	Part Number Prefix	Diameter		Weight		Min. Bend Radius				Max. Loading			
		in	mm	lb./kft	kg/km	Install		Long Term		Install		Long Term	
						in	cm	in	cm	lbf	N	lbf	N
4	ACRC004-002x12AWG	0.375	9.5	87	129	5.6	14.3	3.8	9.5	300	1335	90	400
8	ACRC008-002x12AWG	0.375	9.5	87	129	5.6	14.3	3.8	9.5	300	1335	90	400
12	ACRC012-002x12AWG	0.375	9.5	87	129	5.6	14.3	3.8	9.5	300	1335	90	400
12	ACRC012-004x12AWG	0.480	12.2	159	237	7.2	18.3	4.8	12.2	300	1335	90	400
12	ACRC012-006x12AWG	0.530	13.5	206	307	8.0	20.2	5.3	13.5	300	1335	90	400
12	ACRC012-008x12AWG	0.570	14.5	263	392	8.6	21.7	5.7	14.5	300	1335	90	400

FIBER DATA AND SHEATH COLORS											
Fiber Type	Part Number Suffix	Leviton Fiber	Core Size	Wavelength (nm)	Maximum Attenuation (dB/km)	Effective Modal Bandwidth @ 850 nm (MHz*km)	Distance (meters)				Sheath Color
Multimode - 62.5 µm Standard, and 50 µm Bend Insensitive							1 GbE	10 GbE	40 GbE	100 GbE	
OM1	CB3510/25	CB	62.5 µm	850/1300	3.5/1.0	200	300	33	N/A	N/A	Black
OM3	EB3010/25	EB	50 µm	850/1300	2.8/0.8	2000	1000	300	100	70	Black
OM4	FB3010/F5	FB	50 µm	850/1300	2.8/0.8	4700	1040	550	150	100	Black
OM4+	XB3010/X5	XB	50 µm	850/1300	2.8/0.8	4900	1210	600	300	150	Black
WideBand Multimode - Bend Insensitive							1 GbE	10 GbE	40 GbE	100 GbE	
OM5	WB3010/W5	WB	50 µm	850-953/1300	2.8/0.8	4700	1040	550	190	100	Black
Single-mode Bend Insensitive - ITU-T G.652.D and G.657.A1 Compliant							1 GbE	10 GbE	40 GbE	100 GbE	
OS2	AB0403	AB	SMF	1310/1550	0.4/0.3	N/A	≥ 5000	≥ 10000	≥ 10000	≥ 10000	Black

For further support information, visit [Leviton.com/NS/Support](http://Leviton.com/NS/Support)