


THE FUTURE IS ON®

LEVITON®



Health Care Facility Solutions

LINE CARD



HOSPITAL GRADE RECEPTACLES

Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Isolated Ground & Illuminated Versions Available
- UL/Fed. Spec./CSA/NOM



Extra Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 & 250 Volt
- 0.050" Nickel-Plated 1-piece Brass Strap
- Triple-wipe 0.040" high-performance brass alloy contacts
- Tamper-Resistant, Power Indication & MRI Versions Available
- UL/Fed. Spec./CSA/NOM



Decora® Plus Extra Heavy Duty Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Back & Side Wired
- Tamper-Resistant, Isolated Ground & Power Indication Versions Available
- UL/CSA/NOM



Hospital Grade 4-in-1 Receptacles

- 15 & 20 Amp/125 Volt NEMA Configurations
- Steel Strap
- Isolated Ground and Surge Versions Available
- UL/CSA/NOM



AFCI & GFCI RECEPTACLES

Hospital Grade AFCI Receptacles

- 15 & 20 Amp/125 Volt
- LED Indicator Light
- Tamper-Resistant
- Self-Grounding
- UL/CSA/NOM/Fed.Spec.



Hospital Grade GFCI Receptacles

- 15 & 20 Amp/125 Volt
- PBT Cover
- NAFTA Compliant, Tamper-Resistant & Weather-Resistant Versions Available
- UL/CSA/NOM/Fed. Spec.



Hospital Grade Dual Function AFCI/GFCI Receptacles

- 15 & 20 Amp / 125 Volt
- LED Indicator Light
- Tamper-Resistant
- UL/CSA/NOM/Fed. Spec.



Hospital Grade GFCI Receptacle with Amber Guidelight

- For applications where disrupting patient circadian rhythms is a concern



USB RECEPTACLES

Hospital Grade USB Charger/Tamper-Resistant Receptacles

- 15 & 20 Amp/125 Volt
- USB Charger/Tamper-Resistant Receptacle & 4-Port USB Charger Versions Available
- 3.6A Charging Capacity for Duplex Receptacle Versions
- 4.2A Charging Capacity for 4-Port USB Version
- cCSAus/NOM



LEV-LOK® MODULAR WIRING DEVICES

Lev-Lok® Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Standard, Decora, Illuminated or Power Indication
- GFCI, Tamper-Resistant, MRI & Isolated Ground versions available



Lev-Lok® Decora Plus Hospital Grade Receptacles

- 15 & 20 Amp/125 Volt
- Standard, Illuminated or Power Indication
- Tamper-Resistant, USB & Surge Protective versions available



Lev-Lok® Toggle Switches

- 15 & 20 Amp/120 & 240 Volt
- Standard, Tamper-Resistant, Antimicrobial and Illuminated versions available
- Color-coded covers: 15 Amp - Blue, 20 Amp - Red for easy circuit identification



Lev-Lok® Wiring Modules

- Receptacle, Switch, and Occupancy Modules
- Solid or Stranded Wire Leads with optional push-wire connectors and low leakage color-coded versions



SURGE PROTECTIVE DEVICES

Decora® Hospital Grade Tamper-Resistant & Non-Tamper-Resistant Receptacles

- 15 & 20 Amp/125 Volt
- Indicator Light and Audible Alarm
- Conform to UL 1449



Medical Grade Power Strips

- 15 & 20 Amp/125 Volt
- 2, 4 or 6 hospital grade outlets
- 7 or 15 feet cord length
- UL 60601-1, UL 1363A, UL 60950-1 and UL 1449 compliant to meet all major safety regulations required for health care facilities
- Surge protected versions available
- Versions with load monitoring Inform™ Technology featuring real-time, line-of-sight LED indication that NFPA 99 current limit has been exceeded



Surge Protective Panels

- 120/208, 277/480 3-Phase Voltages
- Compliant with 2023 NEC requirement for emergency power systems



SWITCHES

Key Locking Switches

- Single Pole, Double Pole, 3-Way, 4-Way
- Replacement keys available

Safety Disconnect Switches

- Available in stainless steel and non-metallic enclosures
- IP69K for high pressure, high temperature washdown
- NSF Certified for hygiene requirements
- IP67, IP65, NEMA 3R, 4X, 12K
- 24/7 Remote Condition Monitoring available



AC Toggle and Decora Plus Switches

- 20 A, 120/277 VAC
- Single Pole, Double Pole, 3-Way
- Pilot Light, Illuminated and Antimicrobial Treated versions
- UL/Fed.Spec./CSA



Tamper-Resistant Toggle Switches

- 20 A, 120/277 V
- 1 HP, 120 V; 2HP, 240 V-277 V
- UL/Fed.Spec./CSA/NOM



Antimicrobial Treated Devices

- 20 A, 120/277 VAC
- Available in Toggle, Decora Plus, and Lev-Lok switches and stainless steel toggle and Decora wallplates
- Made with an E.P.A. registered additive
- Helps resist development of mold, mildew, fungi and odor-causing bacteria



OCCUPANCY SENSORS ¹

Decora® Wall Switch Multi-Technology Occupancy Sensors

- 120-277 VAC, 50/60 Hz
- LED, Incandescent/Tungsten, Fluorescent
- UL and cUL Listed, ETL and cETL Listed



Ceiling-Mount Multi-Technology Occupancy Sensors

- Supports 24 VAC/DC power supplies
- Coverage Range: 500-2000 Sq. Ft.
- CUL/US, FCC and NOM Certified



Multi-Technology Wall or Corner Mount Occupancy Sensors

- Supports 24 VAC/DC power supplies
- Coverage: 1200 Sq. Ft.
- Adjustable swivel neck rotates 80° vertically and 60° horizontally
- CUL/US Certified



¹ Can be used to comply with IECC, ASHRAE 90.1, and 2019 Title 24, Part 6 occupancy/vacancy sensing requirements

² Can be used to comply with IECC, ASHRAE 90.1, and 2019 Title 24, Part 6 service separation of electrical circuits for electrical monitoring requirements

SUBMETERING SOLUTIONS ²

VerifEye™ Meter Kits – Indoor & Outdoor

- 100 A - 5000 A, 120 V - 277/480 V
- Single Phase & Three Phase
- Isolated Pulse Output Standard
- NEMA 1, 4X Enclosures
- Data collection hardware and BMO 3.0 energy information software available



RELAY PANELS ³

GreenMAX®

- Cabinets with Short Circuit Current Rating (SCCR) of 25,000 A at 277 VAC
- Available in 8, 16, 32, or 48 relays
- Latching Relay Modules in 1-pole and 2-pole configurations
- LumaCAN and Ethernet network



EZ-MAX® Plus

- 120 V, 277 V and 347 V
- Available in 4 or 8 relays
- Standard 30 A Relay Card with 20,000 A Short Circuit Current Rating



LIGHTING CONTROLS

IllumaTech Dimmers

- 120 VAC, 60 Hz, Neutral wire required
- 1000 W Incandescent
- 150 W LED/CFL
- 1000 VA Magnetic Low Voltage
- 1000 VA Fluorescent Ballast
- 1200 VA 0-10 V Power Supplies



ROOM CONTROLS ⁴

Provolt™ Room Controller (PRC) and App

- 120/277 V
- Self-contained device for occupancy sensing, 0-10 V dimming, daylight harvesting, partial-ON, partial-OFF, plug load control and demand response
- Configuration and control via the Provolt Bluetooth® mobile app
- Install with Provolt Keypad for manual control - 1, 2, or 4 button
- 1- or 2-zone control
- UL/cUL, CE, NOM, RoHS, NEMA



Integrated Room Control (IRC) Kit

- 120/277 V, 347 V
- Kit includes IRC, sensor, photocell and keypad for occupancy sensing, 0-10 V dimming, daylight harvesting, partial-ON, partial-OFF and demand response
- Add OPP20 for plug load control
- 2- or 3-zone control
- UL/cUL Listed



³ Can be used to comply with IECC, ASHRAE 90.1, and 2019 Title 24, Part 6 occupancy/vacancy sensing, 0-10V dimming, daylight harvesting, partial-ON, partial-OFF, scheduling, demand response, and receptacle control requirements

⁴ Can be used to comply with IECC, ASHRAE 90.1, and 2019 Title 24, Part 6 occupancy/vacancy sensing, 0-10V dimming, daylight harvesting, partial-ON, partial-OFF and demand response requirements

NETWORK SOLUTIONS

DuraPort Industrial Connectivity

- IP67 Rated
- Twist-lock connector housings
- Safe watertight Cat 6 and Cat 6A connectivity systems



Secure RJ Port Blockers, Tools and Patch Cords

- Compatible with industry standard RJ-45 ports
- Meets or exceeds all TIA-568-C.2 requirements
- Polycarbonate, UL94V-2



Pre-Terminated Trunk Cables

- Custom-built pre-terminated copper and fiber trunks
- Reduces installation time by up to 75 percent



Atlas-X1™ System

- Highest level of verified performance
- Supports high-bandwidth wireless networks
- Easily scalable for migrations up to 40GBASE-T PoE up to 100 W



Power Distribution Units

- 16 A continuous input current (5-20P & L5-20P input plug)
- 24 A continuous input current (L5-30P input plug)
- Amperage and wattage accuracy: ± 5%
- Voltage accuracy: ± 2%
- Type DP cords included for NEC 645 compliance



WALLPLATES

Metallic Wallplates

- Available in Type 302 and 430 Stainless Steel, Aluminum, Chrome and Brass
- Expansive selection of single- and multi-gang configurations
- Gasketed wallplates reduce liquid intrusion and air seepage when installed properly on a flat, smooth surface



Special Purpose Wallplates Pre-marked with "EMERGENCY" for Easy Identification

- Available in nylon or stainless steel single- and two-gang configurations; Standard or Midway sizes
- Nylon wallplates are red in color with "EMERGENCY" lettering in black or white
- Stainless steel wallplates have "EMERGENCY" lettering in high visibility red



PLUGS & CONNECTORS

Hospital Grade

- 15 & 20 Amp/125 Volt
- NEMA and Non-NEMA Configurations
- 2 Pole, 3 Wire



Black & White® Industrial Grade

- 15, 20 & 30 Amp
- 125 V thru 600 Volt
- 2 Pole, 2 Wire thru 4 Pole, 5 Wire
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec./CSA/NOM



Hospital Grade Python®

- 15 & 20 A/125 & 250 V
- NEMA and Non-NEMA Configurations
- Patented interlock design for secure installation
- Clear thermoplastic terminal cover



WEATHERPROOF & WATERTIGHT

Weatherproof Device Covers & Boxes

- Available in 1- and 2-gang configurations
- Complies with the NEC® (2023) Section 406.9(A) for weatherproof enclosures in damp locations
- Vertical or Horizontal Mounting



Wetguard® Straight Blade and Locking Devices

- 15, 20 and 30 Amp
- 125 V thru 600 V
- 2 Pole, 2 Wire thru 4 Pole, 5 Wire
- NEMA and Non-NEMA Configurations



Wetguard® Watertight Switch Cover

- IEC IP66 and NEMA 4X watertight ratings
- For use with any standard single pole toggle switch 15 A to 30 A
- Lockout handle meets OSHA safety regulations



ELECTRIC VEHICLE CHARGING

EV Series Charging Stations

- 32, 48 or 80 Amp
- Level 2: SAE J1772™ Compatible
- Restrict access with optional RFID
- Compatible with the My Leviton app
- Available with 4G and management software capabilities



Visit our Website at:

leviton.com/healthcare

email: commercial@leviton.com

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2023 Leviton Manufacturing Co., Inc. All rights reserved.

092223

Q-913D

