

P Series

Surge Protective Device

Designed for **RESIDENTIAL AND LIGHT COMMERCIAL APPLICATIONS**,

the P Series provides protection in single, split or three phase configurations.

Features

- Maximum Surge Current Rating 25kA per Mode, 50kA per Phase
- UL 1449 Listed



- 20kA Nominal Discharge Current Rating (I_n)
- 200kA SCCR
- NEMA 4X

Product Specifications

General Specifications			
Maximum Surge Current Rating	25kA per Mode, 50kA per Phase		
UL 1449 Type Designation	Type 1		
UL 1449 Nominal Discharge Current Rating (I _n)	20kA		
UL 1449 Short Circuit Current Rating (SCCR)	200kA		
Design Specifications			
Custom MOV design for High Energy Handling in IEEE Category C locations			
Thermally Protected MOVs			
External Parallel Connected for Mounting next	to Electrical Gear		
Multi-mode protection			
Diagnostic & Status Monitoring Specifications			
LED Protection Status Monitoring Audible Alarm			
			Form C Dry Contacts, 240V, 2A
Phase Loss Monitoring			
Stacked MOV design for High Energy Handling			
Enclosure			
Polycarbonate			
NEMA 4X			
3/4 inch NPT Side Mount Nipple			
Filtering			
NO			

Pł	nysical Specifications	
	Humidity Range	0-95% non-condensing
	Operating Frequency	50-60Hz
	Operating Temperature	-31°F (-35°C) to 185°F (+85°C)
	Typical Connection	#12 AWG Type TFW

JL 1449 Performance Data						
	System Voltage	Voltag L-N	ge Protect L-G	ion Rating N-G	(VPR)	Maximum Continuous Operating Voltage (MCOV)
	120/240 VAC/CA SPLIT PHASE	700V	1200V	600V	1200V	180V/360V*
	208Y/120 VAC/CA 3 PHASE WYE	600V	1000V	600V	1000V	150V/300V*
	480Y/277 VAC/CA 3 PHASE WYE	1200V	2500V	1000V	2000V	350V/700V*

^{*}Second voltage refers to L-L rating


Standards Compliance & Certifications

UL 1449 5th Edition: 2021, cULus, (UL File: VZCA.E317603), UL 96A Compliant, ANSI/IEEE C62.41.1-2002, C62.41.2-2002, C62.45-2002, NEC Article 285
ISO 9001:2014 Quality Management System, ISO 17025:2007 Laboratory Certification (UL DAP Program) Compliance with RoHS, REACH & California Prop 65
100% Quality Tested prior to shipping, Made in Greece


Ordering Information

P2120-B	120/240 VAC/CA, SPLIT PHASE
P3120-YB	208Y/120 VAC/CA, THREE PHASE WYE
P3277-YB	480Y/277 VAC/CA, THREE PHASE WYE


Wiring Configurations




Architectural Drawings (Dimensions)



Size and Mechanic	ize and Mechanical Specifications		
Dimensions	5.02" x 2.93" x 3.25"		
Enclosure Type	Polycarbonate NEMA 4X		
Installation Type	Indoor / Outdoor		





102023



Visit our Website at:

www.leviton.com/surge

email: commercial@leviton.com
Q-1504

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

