

# JC17042

## Wall Spot

10.1W surface mount adjustable Spotlight 520mm 41° beam angle IP65

### Features & Benefits

- Durable die-cast aluminium construction
- IP65 protection weather resistant
- Stylish contemporary design
- LED wall light with matching colour temperature and finish to the Architectural exterior range



RATING



BEAM



WARRANTY



CLASS I



CRI:RA

### General Information

Mounting	Surface Mounted
Trade Name	Architectural
Environment	Outdoor
Product Group	LED - Surface
Color Finish	Anthracite
Product Shape	Cylinder
Product Range	Architectural Exterior Range
Overall Dimensions	120 x 520mm
Product Weight(kg)	1.3
Light Source	LED
Light Source Features	Warm White
Recommended Product Location	External use to light walkways & driveways
IP Rating	IP65
Origin of manufacturer	China
Warranty	2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for terms and conditions)
Driver Manufacturer	Mains chip
LED Manufacturer/Type	Lumens
Lighting Product Type 1	Surface Light

## Electrical

Voltage Rating	220-240
Operating Frequency Hz	50/60Hz
Luminaire Circuit Wattage	10.1
Total Harmonic Distortion (THD)%	20
EMC Compliant (EN55015)	Yes
Power Factor Correction	0.95
Dimmable	No

## Thermals

Operating Temperature Range °C	-20 to +50
--------------------------------	------------

## Performance Data

LED Life (Hours)	36000
------------------	-------

Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

Energy Rating	This product contains a light source of energy efficiency class G
Actual Lumen Output	700
Lumens Per Circuit Watt	69
Color Rendering Index	80-89
CRI: Ra	84
Correlated Color Temperature	3000K
Beam Angle °	41
LOR (Light Output Ratio) %	100
Photometry Available	Yes

## Construction




Primary Material	Aluminium
Seal Material	Silica/Rubber

## Packaging

Product Packaged Weight(kg)	1.48
Quantity Per Outer Carton	8
Product Bar Code EAN-13 Number	5052544079511

## Standards & Approvals

Manufactured In Accordance To	BS60598-2-2015
CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes



---

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.  
Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | [sales@jcc.co.uk](mailto:sales@jcc.co.uk) | [www.jcc.co.uk](http://www.jcc.co.uk)  
Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 92 [06/02/2023]