

Berk-Tek Outside Plant Dry Loose Tube (LTD-M2)

Berk-Tek

a LEVITON company

Berk-Tek's Outside Plant Loose Tube fiber optic cables are designed for installation in harsh environments such as direct burial, aerial lashing, conduit and pathways that are subjected to wide temperature variations. The Dry Loose Tube Outside Plant product is offered with 2-288 fibers per cable. These cables are thoroughly tested and verified to Telcordia GR-20 and ICEA-640 for outside cabling systems.

DESCRIPTION

Berk-Tek's Outdoor Dry Tube Jacket Loose Tube cables are available in multimode, single-mode and GIGAlite™ fibers.

Buffer Tube Construction

Tubes contain water-blocking yarn and up to 12, 250 µm, individually colored fibers.

Outdoor Consideration

Berk-Tek recommends that loose tube cables be utilized in an outside plant installation environment. Loose tube cables are especially recommended if the interbuilding conduit system is above the frost line and likely to fill with water.

Applications

Berk-Tek's Outdoor Loose Tube fiber optic cable is intended for all high speed data applications, including:

- ETHERNET: 10BASE – 40GBASE (10BASE, 100BASE, 1000BASE, 10GBASE, 40GBASE, 100GBASE, 400GBASE)
- Fibre Channel: 1G-FC – 128GFC (1, 2, 4, 8, 16, 32, 128 GFC)
- SONET: OC-1 – OC-768 (OC -1, 3, 12, 24, 48, 192, 768)
- SDH: STM-0 – STM-256 (STM-0, 1, 4, 16, 64, 256)
- OTN: OTU-1 – OTU4 (OTU1, 2, 2e, 2f, 3, 3e2, 4)
- CPRI: CPRI-1 – CPRI-9 (CPRI-1, 2, 3, 4, 5, 6, 7, 7a, 8, 9)


Features

- High tensile strength, crush resistant and small diameter design.
- Single-mode, multimode and hybrid design options available.
- Fully water-blocked core using dry water blocking system.

Benefits

- Provides for greater pulling distances thus reducing installation time.
- Broad design selection allows for mix and match of fiber components to specific networking applications.
- Long-term reliability.
- Low cable plant maintenance, ease of installation.
- Reduce network costs.

Country of Origin: U.S.A.



STANDARDS

National ANSI/ICEA S-87-640;
Telcordia GR-20

Berk-Tek Outside Plant Dry Loose Tube (LTD-M2)



TECHNICAL DATA - PHYSICAL						Install		Long Term		Install		Long Term	
Fibers	Part Number Prefix	Diameter		Weight		Min. Bend Radius				Max. Loading			
		in.	mm	lb./kft	kg/km	in.	cm	in.	cm	lbf.	N	lbf.	N
12	LTD12B012-M2	0.390	9.9	42	62	5.9	14.9	3.9	9.9	600	2700	180	800
24	LTD12B024-M2	0.390	9.9	42	62	5.9	14.9	3.9	9.9	600	2700	180	800
36	LTD12B036-M2	0.390	9.9	42	62	5.9	14.9	3.9	9.9	600	2700	180	800
48	LTD12B048-M2	0.390	9.9	42	62	5.9	14.9	3.9	9.9	600	2700	180	800
72	LTD12B072-M2	0.410	10.5	48	72	6.2	15.8	4.1	10.5	600	2700	180	800
96	LTD12B096-M2	0.480	12.3	65	96	7.2	18.5	4.8	12.3	600	2700	180	800
120	LTD12B120-M2	0.550	13.9	85	126	8.3	20.9	5.5	13.9	600	2700	180	800
144	LTD12B144-M2	0.620	15.7	107	159	9.3	23.6	6.2	15.7	600	2700	180	800
216	LTD12B216-M2	0.610	15.5	90	134	9.2	23.3	6.1	15.5	600	2700	180	800
240	LTD12B240-M2	0.640	16.3	102	152	9.6	24.5	6.4	16.3	600	2700	180	800
288	LTD12B288-M2	0.710	18.0	126	187	10.7	27.0	7.1	18.0	600	2700	180	800

TECHNICAL DATA										
Fiber Type	Part Number Suffix	Berk-Tek Fiber	Core Size	Wavelength (nm)	Maximum Attenuation (dB/km)	Effective Modal Bandwidth @ 850 nm (MHz·km)	Distance (meters)			
Multimode - Bend Insensitive							1 GbE	10 GbE	40 GbE	100 GbE
OM1	CB3510/25	GIGAlite	62.5 μm	850/1300	3.5/1.0	200	300	33	N/A	N/A
OM3	EB3010/25	GIGAlite-10	50 μm	850/1300	3.0/1.0	2000	1000	300	100	70
OM4	FB3010/F5	GIGAlite-10FB	50 μm	850/1300	3.0/1.0	4700	1040	550	150	100
OM4+	XB3010/X5	GIGAlite-10XB	50 μm	850/1300	3.0/1.0	4900	1210	600	300	150
WideBand Multimode - Bend Insensitive							1 GbE	10 GbE	40 GbE	100 GbE
OM5	WB3010/W5	GIGAlite-10WB	50 μm	850-953/1300	3.0/1.0	4700	1040	550	190	100
Single-Mode - Bend Insensitive - ITU-T G.657.A1							1 GbE	10 GbE	40 GbE	100 GbE
OS2	AB0302	Standard for Loose Tube	SMF	1310/1550	0.3/0.2	N/A	≥ 5000	≥ 10000	≥ 10000	≥ 10000

Berk-Tek Outside Plant Dry Loose Tube (LTD-M2)



CHARACTERISTICS

Construction characteristics

Jacket Material

Polyethylene

SHEATH COLORS

Fiber Type	Core Size (um)	ISO-TIA Standard	Effective Modal BW @ 850 nm	Overfilled Launch BW @ 850 nm	Attenuation @ 850 nm	Attenuation @ 1300 nm	Attenuation @ 1550 nm	Sheath Color
AB	8.3	OS2	NS	NS	NS	0.3 dB/km	0.2 dB/km	Black
AB	8.3	OS2	NS	NS	NS	0.4 dB/km	0.3 dB/km	Black
CB	62.5	OM1	200 MHz-km	200 MHz-km	3.5 dB/km	1.0 dB/km	NS	Black
EB	50	OM3	2000 MHz-km	1500 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
FB	50	OM4	4700 MHz-km	3500 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
XB	50	OM4+	4900 MHz-km	3675 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black

NS = Not Specified

MANUFACTURING RELEASE

IMPORTANT NOTICE: This product specification is provided for informational purposes only in order to illustrate typical product constructions, applications and/or methods of installation. Because conditions of actual installation and use are unique and will vary, Berk-Tek makes no representation or warranty as to the reliability, accuracy or completeness of this data, even if Berk-Tek is aware of the product's intended use or purpose. Furthermore, this data does not constitute, nor should it be regarded or relied upon, as professional engineering advice. Installation of product should only be done by qualified personnel and in conformance with all safety, electrical and other applicable codes, standards, rules or regulations. Appropriate and correct product selection, installation and use, and compliance with all such codes, standards, rules and regulations, is a customer/end-user responsibility. Product specifications, standards, programs or services are subject to improvement or changes without notice. Berk-Tek accepts no liability for typographical errors, technical inaccuracies, omissions or misuse of the information contained herein. Changes will be periodically made to address any such issues.