

# JC84214WH

## Architectural Pendants

Architectural LED Pendant Dimmable 25W 36° 3000K IP20 White

### Features & Benefits

- Stylish ultra modern design
- Pre-wired with three-core cable with a braided outer sleeving
- Triac dimmable as standard
- Available in white and black finishes
- Up to 80 lumens per circuit Watt



### General Information

Mounting	Suspended
Trade Name	Architectural
Environment	Indoor
Suitable For Zones	Outside zone 2
Product Group	LED - Pendant
Color Finish	White
Product Shape	Cylinder
Product Range	Architectural LED Pendant
Overall Dimensions	Ø112.5 x 160 x 1200 x 25 x Ø100mm
Length (mm)	1200
Width (mm)	160
Diameter (mm)	112.5
Product Weight(kg)	0.85
Light Source	LED
Light Source Features	Warm White
Recommended Product Location	Retail/Residential applications
Method Of Fix	Surface Mounted
IP Rating	IP20

Origin of manufacturer	<b>Made in China</b>
Warranty	<b>3 Year Warranty (See Website for terms and conditions)</b>
Dimming Protocol Compatibility	<b>Triac</b>
Driver Manufacturer	<b>JCC</b>
LED Manufacturer/Type	<b>COB/Cree</b>
Lighting Product Type 1	<b>Decorative Pendants</b>
Customs Tariff code**	<b>9405119090</b>

## Electrical

Voltage Rating	<b>200-240</b>
Primary Running Current(Amp)	<b>0.15</b>
Operating Frequency Hz	<b>50Hz</b>
Secondary running current(mA)	<b>600</b>
Luminaire Circuit Wattage	<b>25</b>
Class	<b>I</b>
Output Voltage Max/Range (VDC)	<b>35-38</b>
Total Harmonic Distortion (THD)%	<b>20</b>
EMC Compliant (EN55015)	<b>yes</b>
Power Factor Correction	<b>0.9</b>
Input Electrical Connections	<b>Live(L)Neutral(N)Earth (E)</b>
Dimmable	<b>Yes (Triac)</b>

## Thermals

Operating Temperature Range °C	<b>-10 to +40</b>
--------------------------------	-------------------

## Performance Data

LED Life (Hours)*	<b>36000</b>
Energy Rating	<b>This product contains a light source of energy efficiency class F</b>
Actual Lumen Output	<b>2010</b>
Lumens Per Circuit Watt	<b>80 LpcW</b>
Color Rendering Index	<b>80-89</b>
CRI: Ra	<b>80-85</b>
Correlated Color Temperature	<b>3000K</b>
Beam Angle °	<b>36</b>
Photometry Available	<b>Yes</b>

## Construction

Primary Material	<b>Aluminium</b>
Lens	<b>Glass</b>
Driver Housing	<b>Aluminium</b>

## Packaging

Product Packaged Weight(kg)	<b>1.05</b>
-----------------------------	-------------




Quantity Per Outer Carton  
Product Bar Code EAN-13 Number

24  
5052544078965

## Standards & Approvals

Manufactured In Accordance To  
CE Marked  
UKCA Marked  
Date code/Purchase order No.  
Certificate Of Conformity  
Accredited Members

**BS 60598-2-5**  
**Yes**  
**Yes**  
**Yes**  
**Available on request**  
**LIA, ISO9001-2015, ISO14001-2015**



\*Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

\*\*JCC Lighting Limited makes every effort to ensure that the Customs Tariff information in this document is timely and accurate. However, it's not possible for us to assure the absolute veracity and completeness of that information, as errors may occur. The placement of any inaccurate tariff information is completely unintentional. JCC Lighting Limited reserves the right, in its sole discretion, to correct any errors or omissions to the tariff code and to make any and all changes contained in this document at any time and without notice. It is the sole responsibility of the importer to ensure that the commodity code advised is correct for the products/goods being supplied by JCC Lighting Limited. JCC Lighting Limited does not assume any liabilities, losses, costs, and expenses arising out of or related to the importers use of this commodity code or the information related to the import of any JCC Lighting products.

