

JC84218

Architectural Pendants HO

High output pendant IP20 25W non-dimmable 4000K 3190lm 24° White

Features & Benefits

- 2 beam angle variants available
- Ultra efficient up to 128 lumens per circuit Watt
- Stylish ultra modern design
- Produced to order contact JCC customer services on 01243 838999



General Information

Mounting	Suspended
Trade Name	Architectural
Environment	Indoor
Suitable For Zones	Indoor
Product Group	LED - Pendant
Color Finish	White
Product Shape	Cylinder
Product Range	Architectural Pendant
Overall Dimensions	Ø112.5 x 1235mm (1080mm cable length)
Length (mm)	1235
Width (mm)	160
Diameter (mm)	112.5
Product Weight(kg)	0.95
Light Source	LED
Light Source Features	Neutral White
Recommended Product Location	Residential applications
Method Of Fix	Surface Mounted
Mounting Bracket Dimensions (mm)	Ø100 x 25mm

IP Rating	IP20
Origin of manufacturer	Made in China
Warranty	5 Year Warranty (See Website for terms and conditions)
Driver Manufacturer	JCC
LED Manufacturer/Type	CREE COB
Lighting Product Type 1	Decorative Pendants
Customs Tariff code**	9405119090

Electrical

Voltage Rating	200-240
Primary Running Current(Amp)	0.3
Operating Frequency Hz	50/60Hz
Secondary running current(mA)	600
Luminaire Circuit Wattage	25
Class	I
Output Voltage Max/Range (VDC)	30-40
EMC Compliant (EN55015)	yes
Power Factor Correction	0.9
Input Electrical Connections	Live(L)Neutral(N)Earth (E)
Dimmable	NO

Thermals

Operating Temperature Range °C	-20 to +40
--------------------------------	-------------------

Performance Data

LED Life (Hours)*	50000
Energy Rating	This product contains a light source of energy efficiency class E
Actual Lumen Output	2800
Lumens Per Circuit Watt	112
Color Rendering Index	80-89
CRI: Ra	80
Correlated Color Temperature	4000K
Beam Angle °	24
LOR (Light Output Ratio) %	100
Photometry Available	Yes

Construction




Primary Material	Aluminium
LED Brand	CREE
Heat Sink	Aluminium
Driver Housing	Polycarbonate

Packaging

Product Packaged Weight(kg)	26
Quantity Per Outer Carton	24
Product Bar Code EAN-13 Number	5052544087837

Standards & Approvals

Manufactured In Accordance To	BS 60598-2015
CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



*Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

**JCC Lighting Limited makes every effort to ensure that the Customs Tariff information in this document is timely and accurate. However, it's not possible for us to assure the absolute veracity and completeness of that information, as errors may occur. The placement of any inaccurate tariff information is completely unintentional. JCC Lighting Limited reserves the right, in its sole discretion, to correct any errors or omissions to the tariff code and to make any and all changes contained in this document at any time and without notice. It is the sole responsibility of the importer to ensure that the commodity code advised is correct for the products/goods being supplied by JCC Lighting Limited. JCC Lighting Limited does not assume any liabilities, losses, costs, and expenses arising out of or related to the importers use of this commodity code or the information related to the import of any JCC Lighting products.

