

JC84210WH

Architectural Pendants

Architectural LED Pendant Dimmable 10W 36° 3000K IP20 White

Features & Benefits

- Stylish ultra modern design
- Pre-wired with three-core cable with a braided outer sleeving
- Triac dimmable as standard
- Available in white and black finishes
- Up to 91 lumens per circuit Watt



General Information

Mounting	Suspended
Trade Name	Architectural
Environment	Indoor
Suitable For Zones	Outside zone 2
Product Group	LED - Pendant
Color Finish	White
Product Shape	Cylinder
Product Range	Architectural LED Pendant
Overall Dimensions	Ø80 x 130 x 1200 x 25 x Ø100mm
Length (mm)	1200
Width (mm)	130
Diameter (mm)	80
Product Weight(kg)	0.4
Light Source	LED
Light Source Features	Warm White
Recommended Product Location	Retail/Residential applications
Method Of Fix	Surface Mounted
IP Rating	IP20

Origin of manufacturer	Made in China
Warranty	3 Year Warranty (See Website for terms and conditions)
Dimming Protocol Compatibility	Triac
Driver Manufacturer	JCC
LED Manufacturer/Type	COB/Cree
Lighting Product Type 1	Decorative Pendants
Customs Tariff code**	9405119090

Electrical

Voltage Rating	200-240
Primary Running Current(Amp)	0.06
Operating Frequency Hz	50Hz
Secondary running current(mA)	215
Luminaire Circuit Wattage	10
Class	I
Output Voltage Max/Range (VDC)	35-38
Total Harmonic Distortion (THD)%	20
EMC Compliant (EN55015)	yes
Power Factor Correction	0.9
Input Electrical Connections	Live(L)Neutral(N)Earth (E)
Dimmable	Yes (Triac)

Thermals

Operating Temperature Range °C	-10 to +40
--------------------------------	-------------------

Performance Data

LED Life (Hours)*	36000
Energy Rating	This product contains a light source of energy efficiency class F
Actual Lumen Output	870
Lumens Per Circuit Watt	87 LpcW
Color Rendering Index	80-89
CRI: Ra	80-85
Correlated Color Temperature	3000K
Beam Angle °	36
Photometry Available	Yes

Construction

Primary Material	Aluminium
Lens	Glass
Driver Housing	Aluminium

Packaging

Product Packaged Weight(kg)	0.55
-----------------------------	-------------




Quantity Per Outer Carton
Product Bar Code EAN-13 Number

24
5052544078880

Standards & Approvals

Manufactured In Accordance To
CE Marked
UKCA Marked
Date code/Purchase order No.
Certificate Of Conformity
Accredited Members

BS 60598-2-5
Yes
Yes
Yes
Available on request
LIA, ISO9001-2015, ISO14001-2015



*Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

**JCC Lighting Limited makes every effort to ensure that the Customs Tariff information in this document is timely and accurate. However, it's not possible for us to assure the absolute veracity and completeness of that information, as errors may occur. The placement of any inaccurate tariff information is completely unintentional. JCC Lighting Limited reserves the right, in its sole discretion, to correct any errors or omissions to the tariff code and to make any and all changes contained in this document at any time and without notice. It is the sole responsibility of the importer to ensure that the commodity code advised is correct for the products/goods being supplied by JCC Lighting Limited. JCC Lighting Limited does not assume any liabilities, losses, costs, and expenses arising out of or related to the importers use of this commodity code or the information related to the import of any JCC Lighting products.

