

JC17046

Wall Light

16.4W Round wall Light 260mm 82° beam angle IP54

Features & Benefits

- Durable die-cast aluminium construction
- IP54 protection against dust and moisture
- LED wall light with matching colour temperature and finish to the Architectural exterior range



CLASS I



CRI:RA



WARRANTY



BEAM



RATING

General Information

Mounting	Wall
Trade Name	Architectural
Environment	Outdoor
Product Group	LED - Surface
Color Finish	Anthracite
Product Shape	Cylinder
Product Range	Architectural Exterior Range
Overall Dimensions	181 x 120 x 260mm
Product Weight(kg)	1.4
Light Source	LED
Light Source Features	Warm White
Recommended Product Location	External use, walkways, driveways
Method Of Fix	Fix using anchor bolts (supplied) or root mounting kit
IP Rating	IP54
Origin of manufacturer	China
Warranty	2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for terms and conditions)
Driver Manufacturer	HEP
LED Manufacturer/Type	CREE LED 1507

Electrical

Voltage Rating	220-240
Primary Running Current(Amp)	0.12
Operating Frequency Hz	50/60Hz
Secondary running current(mA)	350
Constant Current or Constant Voltage	CC
Luminaire Circuit Wattage	16.4
Total Harmonic Distortion (THD)%	21
EMC Compliant (EN55015)	Yes
Power Factor Correction	0.9
Dimmable	No

Thermals

Operating Temperature Range °C	-20 to +50
--------------------------------	------------

Performance Data

LED Life (Hours)	36000
------------------	-------

Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

Energy Rating	This product contains a light source of energy efficiency class G
Actual Lumen Output	530
Lumens Per Circuit Watt	32
Color Rendering Index	80-89
CRI: Ra	83
Correlated Color Temperature	3000K
Beam Angle °	82
Photometry Available	Yes

Construction

Primary Material	Aluminium
Seal Material	Silica/Rubber




Packaging

Product Packaged Weight(kg)	2.15
Quantity Per Outer Carton	4
Product Bar Code EAN-13 Number	5052544079535

Standards & Approvals

Manufactured In Accordance To	BS60598-2-2015
CE Marked	Yes

UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.
Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | sales@jcc.co.uk | www.jcc.co.uk
Company Registration Number: 03044848 | VAT Number: 918544112