

JC17017

Up Down Wall Light

18W Decorative wall/post light 28° beam angle IP65

Features & Benefits

- Durable die-cast aluminium construction
- IP54 protection against dust and moisture
- Stylish
- contemporary design
- LED wall light with matching colour temperature and finish to the Architectural exterior range



CLASS I



CRI:RA



WARRANTY



BEAM



RATING

General Information

Mounting	Wall
Trade Name	Architectural
Environment	Outdoor
Product Group	LED - Surface
Color Finish	Black
Product Shape	Square
Product Range	Architectural Exterior Range
Overall Dimensions	180 x 79 x 200
Product Weight(kg)	1.3
Light Source	LED
Light Source Features	Warm White
Recommended Product Location	Residential applications
Method Of Fix	Surface Mounted
IP Rating	IP65
Origin of manufacturer	China
Warranty	2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for terms and conditions)
Driver Manufacturer	HEP
LED Manufacturer/Type	PHILIPS 2835

Electrical

Voltage Rating	200-240
Operating Frequency Hz	50/60Hz
Luminaire Circuit Wattage	18
Class	I
EMC Compliant (EN55015)	yes

Thermals

Operating Temperature Range °C	-20 to +50
--------------------------------	------------

Performance Data

LED Life (Hours)	36000
------------------	-------

Hours life stated is an indication of expected L70 chip and light output calculations when operating in optimum conditions. Product warranty period supports the full product during the term given. The L70 hours expectancy is not correlated with the full product warranty term, nor is it a representation of lumen depreciation during the warranty period.

Energy Rating	This product contains a light source of energy efficiency class G
Actual Lumen Output	600
Lumens Per Circuit Watt	33 LpcW
Color Rendering Index	80-89
CRI: Ra	80
Correlated Color Temperature	3000K
Beam Angle °	28
Photometry Available	Yes

Construction




Primary Material	Aluminium
Seal Material	Silica

Packaging

Product Packaged Weight(kg)	1.48
Quantity Per Outer Carton	6
Product Bar Code EAN-13 Number	5052544079276

Standards & Approvals

Manufactured In Accordance To	BS 60598-2015
CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.
Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | sales@jcc.co.uk | www.jcc.co.uk
Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 138 [02/02/2023]