



Line Card **OEM**



OEM Solutions

Leviton offers an extensive product line of commercial & industrial grade electrical, lighting and energy management devices. We are the trusted brand that provides safe, high quality products. Whether it's design assistance, delivery time, or simply products that outperform and outlast, Leviton has a complete offering of solutions for Original Equipment Manufacturers.

SAFE & RELIABLE INDUSTRIAL CONNECTIONS • OVER 115 YEARS IN THE INDUSTRY

CONTACT YOUR APPLICATION SPECIALIST

LEVITON®

PLUGS & CONNECTORS

Industrial Grade Plugs & Connectors

- Black & White® Extra Heavy Duty: 15-50 A, 125-600 V
- Rhino-Hide® Rough Service: 15-20 A, 125-250 V
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec./CSA/NOM
- V-0-Max Locking Receptacles: 15-30 A, 125-600 V with UL V-0 flammability rating
- Industry leading limited lifetime warranty



Wetguard® Watertight Devices

- 15-30 A, 125-600 V, Single-Phase and Three-Phase
- Straight Blade and Locking Plugs, Connectors, Receptacles & Inlets
- IEC IP66, IP67 & IP69K*, NEMA 3, 3R, 4, 4X, 6 & 6P Enclosure Ratings

*Plugs and connectors when mated



IEC 60309 Pin & Sleeve Devices

- 30 A & 60 A North American Configurations
- Plugs, Connectors and Mechanical Interlocks available with Inform™ Technology
- IP66, IP67, IP68, & IP69K Rated, NSF Certified



PORTABLE POWER

Power Strips

- 15-20 A, 125 V
- Commercial, industrial, hospital and medical grade versions
- Medical grade versions available with load monitoring technology
- Surge protected versions



Portable GFCIs

- 15/20 A, 125 V Cord Sets & Field-Attachable Plugs
- Auto & Manual Reset Versions
- Meets OSHA Guidelines for Personnel Protection on Job Sites



Rhino-Hide® Single Pole Devices

- 15 (to 150A/600V), 16/18 (to 400A/600V), and 17/22/23 (to 690A/600V) Series devices
- Insulating sleeves are color-coded for phase identification and designed for rugged applications
- Available in a range of termination styles and cord range options



Weatherproof Covers

- For use with 15, 20, 30 and 50 A devices
- IP64 and NEMA 3R rated
- Provisions for OSHA compliant lockout/tagout
- Pre-mounted gasket and stay open feature simplify installation



CERTIFIED

Leviton is proud to help ensure adherence to the best practices in public health and safety standards. We offer a wide array of switches, wallplates, enclosures and now, a full line of LEV Series IEC 60309 Pin & Sleeve devices certified to meet NSF International hygiene requirements for food & beverage processing.

RECEPTACLES

Commercial and Heavy-Duty Industrial Grade Receptacles

- 15-20 A, 125-250 V
- Standard or Decora Plus™
- GFCI, Tamper-Resistant, Isolated Ground, Surge Protected, Marked "Controlled", USB and Weather-Resistant versions available



USB Receptacles

- 15-20 A, 125-250 V
- Combined total of 5.1A charging current and 25+ watts of power
- Built-in overcurrent protection helps protect electronics from receiving too much power, which can damage the device



SWITCHES

Toggle and Decora Plus™ Switches

- 20 A - 120/277 V
- Pilot Light, Illuminated, Key-Locking, Momentary, Maintained, and Tamper-Resistant versions available



LEV-LOK MODULAR DEVICES

Lev-Lok Switches, Receptacles and Occupancy Sensors

- 3x faster installations and 5x faster swap outs than traditional wiring
- Traditional and Decora® Duplex, GFCI, Illuminated, MRI, USB, Marked Controlled Power Indication and Surge Protective Receptacles
- Single-Pole, Three-Way, Tamper-Resistant, Illuminated, and Antimicrobial Treated Switches
- Passive Infrared (PIR) and Multi-Technology (Ultrasonic and PIR) Occupancy Sensors
- Mating Lev-Lok wiring module required for use



SURGE PROTECTIVE DEVICES

Type 1 SPDs

- Protection for line side of electrical service equipment

Type 2 SPDs

- Branch panel protection for single and three-phase applications

Type 3 SPDs

- Receptacles, power strips and plug-in adapters



SUBMETERING SOLUTIONS

VerifEye™ Meter Kits - Indoor & Outdoor

- 100 A - 5000 A, 120 V - 277/480 V
- Single Phase & Three Phase
- Isolated Pulse Output Standard
- NEMA 1 and 4X Enclosures
- Data collection hardware and BMO 3.0 energy information software available



THE SMART CHOICE for

OEM

LIGHTING CONTROLS

Decora® Wall Switch Multi-Technology Occupancy Sensors

- 120-277 V AC, 50/60Hz
- LED, Incandescent/Tungsten, Fluorescent



Ceiling-Mount Multi-Technology Occupancy Sensors

- Supports 24 V AC/DC power supplies
- Coverage Range: 500-2000 Sq. Ft.



Multi-Technology Wall or Corner Mount Occupancy Sensors

- Supports 24 V AC/DC power supplies
- Coverage: 1200 Sq. Ft.
- Adjustable swivel neck rotates 80° vertically and 60° horizontally




Fixture Mount PIR Sensors

- 120/277/347 V AC, 50/60Hz
- Indoor and outdoor models available



OEM Solutions

We are here to help.



CONTACT YOUR APPLICATION SPECIALIST

Leviton Canada

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9
Telephone: 1-800-461-2002
Tech Line: 1-800-405-5320

© 2026 Leviton Manufacturing Co., Inc. All rights reserved.

Q-1247A PC01272026 Rev. A