

4


3

2

1

B

B



REV B NOTE: TOLERANCE \pm 20% FOR LENGTH "M" & "B"

LEVITON PART NO.	CABLE RANGE (R)	MESH LENGTH (M)	EYE LENGTH (B)	APPROXIMATE BREAK LOAD
L8001	0.30"-0.43"	4.50"	2.00"	180LBS
L8002	0.40"-0.56"	5.00"	2.00"	180LBS
L8003	0.52"-0.73"	6.50"	2.00"	450LBS
L8004	0.70"-0.85"	8.50"	2.50"	600LBS
L8005	0.82"-1.00"	8.50"	2.50"	600LBS
L8006	0.94"-1.25"	11.75"	2.50"	600LBS

A

A

STATUS: Production Release						UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		TITLE: STRAIN RELIEF GRIP WIRE MESH										
<p>The information in this document is the exclusive PROPRIETARY property of LEVITON MFG. CO., INC. It is disclosed with the understanding that acceptance or review by the recipient constitutes an undertaking by the recipient:</p> <p>(1) to hold this information in strict confidence. (2) not to disclose, duplicate, copy, or use the information, in whole or in part, for any purpose other than that for which disclosed.</p> <p>Copyright 2016. Unpublished. All Rights Reserved.</p>						TOLERANCES		DWN BY: JA 06/24/2021 ENGRG AE 06/25/2021										
REV.	DATE	ECO NUMBER	CHGD	APVD	<table border="1"> <tr> <th>INCH</th> <th>METRIC</th> </tr> <tr> <td>.XX \pm .01</td> <td>.X \pm .2 mm</td> </tr> <tr> <td>.XXX \pm .005</td> <td>.XX \pm .1 mm</td> </tr> </table>		INCH	METRIC	.XX \pm .01	.X \pm .2 mm	.XXX \pm .005	.XX \pm .1 mm	CHK BY: AE 06/25/2021 MFG AE 06/25/2021					
INCH	METRIC																	
.XX \pm .01	.X \pm .2 mm																	
.XXX \pm .005	.XX \pm .1 mm																	
A	06/25/2021	NEW RELEASE	JA	AE	ANGLES: \pm 1/2°		DWG NO. ORC1075-D01											
-	-	-	-	-	THIRD ANGLE PROJECTION		PROJECT NO. PROJ-03543											
-	-	-	-	-			SIZE B		SCALE:1:1		SHEET 1 OF 1		REV B					
-	-	-	-	-	ALL PRINTED COPIES ARE UNCONTROLLED													

4

3

2

1