



International
Dock Products

ORDER FORM

Custom 21-Inch Metallic Power Pedestal



POWER PEDESTALS FOR MARINE:

- Built from corrosion-resistant aluminum - withstands harsh waterfront environments
- Engineered for extreme marine conditions - designed to resist saltwater, UV exposure, and extreme outdoor conditions for dependable performance year-round
- Safe, high quality power distribution - provides reliable electrical connections

STANDARDS:

- NEMA 3R, UL 231, NFPA 303, NFPA 70

WARRANTY:

- Housing: 15 years
- Construction/Fabrication: 2 years
- Wiring Devices: 1 year

Flat/Bulkhead
Mounting
Bracket

Round Piling
Mounting
Bracket

Both for maximum
install flexibility

DATE:

JOB NAME:

DISTRIBUTOR NAME & ACCOUNT NUMBER:

CITY:

STATE:

ZIP:

PO NUMBER:

CONTACT NAME:

EMAIL:

PHONE:

LEVITON SALES PERSON:



Visit our Website at:
www.leviton.com/powerpedestals
email: industrial@leviton.com

26-CI-0052

080626

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2026 Leviton Manufacturing Co., Inc. All rights reserved.

P21 - - - - - - - - - - - - - - - -

1

2

3

4

5

6

7

8

9

10

11

12

1 PEDESTAL MODEL			
P21 Metallic 21" Piling Mount Power Pedestal Base Unit - Includes one-piece extruded aluminum housing with powder-coated finish, integrated lighting, pre-wired power distribution block, thermoplastic receptacle covers, and mounting bracket and hardware for flat and/or round piling installation.			
2 RECEPTACLE Device Location A - Left		3 RECEPTACLE Device Location B - Right	
R0	No Receptacle	R0	No Receptacle
20S	20A GFI Recept. + Std. Brkr. + Cvr.	20S	20A GFI Recept. + Std. Brkr. + Cvr.
30S	30A (125V) Recept. + Std. Brkr. + Cvr.	30S	30A (125V) Recept. + Std. Brkr. + Cvr.
30E	30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	30E	30A (125V) Recept. + 30mA EPD Brkr. + Cvr.
50S	50A (125V) Recept. + Std. Brkr. + Cvr.	50S	50A (125V) Recept. + Std. Brkr. + Cvr.
50E	50A (125V) Recept. + 30mA EPD Brkr. + Cvr	50E	50A (125V) Recept. + 30mA EPD Brkr. + Cvr
50S2	50A (125/250V) Recept. + Std. Brkr. + Cvr	50S2	50A (125/250V) Recept. + Std. Brkr. + Cvr
50E2	50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.	50E2	50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.
50EV	50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.	50EV	50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.
7 LIGHTING		8 LIGHTING CONTROL	
LW	White (Std. White Lens)	PC	Photocell
LA	Amber (Amber Translucent Lens)	MB	Manual/breaker
LR	Red (Red Translucent Lens)		
LB	Blue (White Lens w/Blue Internal Tubing)	9 ELECTRICAL METER	
LG	Green (White Lens w/Green Internal Tubing)	M0	No Electrical Meter
LO	Orange (White Lens w/Orange Internal Tubing)	M1	Electrical Meter - QTY 1
FL	Fluorescent		
		10 REMOTE MONITORING	
		RM0	No Remote Monitoring
		RM1	Remote Monitoring Enabled
4 RECEPTACLE Device Location C - Right		5 DISTRIBUTION	
R0	No Receptacle	DF	Direct Feed
20S	20A GFI Recept. + Std. Brkr. + Cvr.	LF	Loop/Series Feed
30S	30A (125V) Recept. + Std. Brkr. + Cvr.		
30E	30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	6 MOUNTING BRACKET	
50S	50A (125V) Recept. + Std. Brkr. + Cvr.	BF	Mntng brckt - Flat/Bulkhead
50E	50A (125V) Recept. + 30mA EPD Brkr. + Cvr	BR	Mntng brckt - Round Piling
50S2	50A (125/250V) Recept. + Std. Brkr. + Cvr	BB	Mntng brckts - Both Flat/Bulkhead and Round Piling
50E2	50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.		
50EV	50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.		
11 SPARE BREAKER OPTION 1		12 SPARE BREAKER OPTION 2	
B0	No Spare Breaker	B00	No Spare Breaker
B20	20A 1-Pole Spare Breaker	B202	20A 1-Pole Spare Breaker
B2G	20A 1-Pole GFI Spare Breaker	B2G2	20A 1-Pole GFI Spare Breaker
B30	30A 1-Pole Spare Breaker	B302	30A 1-Pole Spare Breaker
B3G	30A 1-Pole GFI Spare Breaker	B3G2	30A 1-Pole GFI Spare Breaker
B3E	30A 1-Pole EPD Spare Breaker		
B3D	30A 2-Pole EPD Spare Breaker		
B50	50A 2-Pole Spare Breaker		

NOTES: Maximum 3 receptacles, but no 100A receptacle options due to space constraints.
Spare breaker availability is subject to remaining breaker panel capacity after receptacles are selected.
High-amperage receptacle combinations may limit or prevent spare breaker selection.
Outlying configurations will be reviewed during quoting or engineering validation.

COMPLETED NUMBER (APPEARS IN SPACE BELOW):

QUANTITY:

CUSTOMER
SIGNATURE
(Indicates build approval)



With this signature the customer acknowledges being advised that these Made-To-Order pedestals are non-cancelable, non-refundable, and non-returnable.

