



International
Dock Products



ORDER FORM

Custom 45-Inch Metallic Power Pedestal

POWER PEDESTALS FOR MARINE:

- Built from corrosion-resistant aluminum - withstands harsh waterfront environments
- Engineered for extreme marine conditions - designed to resist saltwater, UV exposure, and extreme outdoor conditions for dependable performance year-round
- Safe, high quality power distribution - provides reliable electrical connections

STANDARDS:

- NEMA 3R, UL 231, NFPA 303, NFPA 70

WARRANTY:

- Housing: 15 years
- Construction/Fabrication: 2 years
- Wiring Devices: 1 year



Hose
Holders



Hose
Hooks



Water
Faucets

DATE:

JOB NAME:

DISTRIBUTOR NAME & ACCOUNT NUMBER:

CITY:

STATE:

ZIP:

PO NUMBER:

CONTACT NAME:

EMAIL:

PHONE:

LEVITON SALES PERSON:



Visit our Website at:
www.leviton.com/powerpedestals
email: industrial@leviton.com

26-CI-0053

080626

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2026 Leviton Manufacturing Co., Inc. All rights reserved.

ORDERING NUMBER:

Ordering example: P45-1S25-R0-50S-30S-HH-HH-DF-LW-PC-M1-RM0-W0-WM0-NH



P45-

1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17

1 PEDESTAL MODEL

P45 Metallic 45" Dock Mount Power Pedestal – Includes one-piece extruded aluminum housing with powder-coated finish, integrated lighting, pre-wired power distribution block, powder coated aluminum angled receptacle covers, and dock-mount base gasket.

2 RECEPTACLE Device Location A - Right	3 RECEPTACLE Device Location B - Right	4 RECEPTACLE Device Location C - Left	5 RECEPTACLE Device Location D - Left
R0 No Receptacle	R0 No Receptacle	R0 No Receptacle	R0 No Receptacle
20S 20A GFI Recept. + Std. Brkr. + Cvr.	20S 20A GFI Recept. + Std. Brkr. + Cvr.	20S 20A GFI Recept. + Std. Brkr. + Cvr.	20S 20A GFI Recept. + Std. Brkr. + Cvr.
30S 30A (125V) Recept. + Std. Brkr. + Cvr.	30S 30A (125V) Recept. + Std. Brkr. + Cvr.	30S 30A (125V) Recept. + Std. Brkr. + Cvr.	30S 30A (125V) Recept. + Std. Brkr. + Cvr.
30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.
50S 50A (125V) Recept. + Std. Brkr. + Cvr.	50S 50A (125V) Recept. + Std. Brkr. + Cvr.	50S 50A (125V) Recept. + Std. Brkr. + Cvr.	50S 50A (125V) Recept. + Std. Brkr. + Cvr.
50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.	50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.	50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.	50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.
50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.	50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.	50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.	50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.
50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.	50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.	50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.	50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.
50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.	50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.	50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.	50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.
1S25* 100A (125/250V) Recept. + Std. Brkr.	1S25* 100A (125/250V) Recept. + Std. Brkr.	1S25* 100A (125/250V) Recept. + Std. Brkr.	1S25* 100A (125/250V) Recept. + Std. Brkr.
1S20* 100A (120/208V) Recept. + Std. Brkr.	1S20* 100A (120/208V) Recept. + Std. Brkr.	1S20* 100A (120/208V) Recept. + Std. Brkr.	1S20* 100A (120/208V) Recept. + Std. Brkr.
1S48* 100A (277/480V) Recept. + Std. Brkr.	1S48* 100A (277/480V) Recept. + Std. Brkr.	1S48* 100A (277/480V) Recept. + Std. Brkr.	1S48* 100A (277/480V) Recept. + Std. Brkr.
IMPORTANT: See NOTES below on ordering.	IMPORTANT: See NOTES below on ordering.	IMPORTANT: See NOTES below on ordering.	IMPORTANT: See NOTES below on ordering.

6 RECEPTACLE (OR OPT. HOSE HLDR.) Device Location E - Right	7 RECEPTACLE (OR OPT. HOSE HLDR.) Device Location F - Left	8 DISTRIBUTION	10 LIGHTING CONTROL
R0 No Receptacle	R0 No Receptacle	DF Direct Feed	PC Photocell
20S 20A GFI Recept. + Std/ Brkr. + Cvr.	20S 20A GFI Recept. + Std/ Brkr. + Cvr.	LF Loop/ Series Feed	MB Manual/Breaker
30S 30A (125V) Recept. + Std. Brkr. + Cvr.	30S 30A (125V) Recept. + Std. Brkr. + Cvr.		
30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.	30E 30A (125V) Recept. + 30mA EPD Brkr. + Cvr.		
50S 50A (125V) Recept. + Std. Brkr. + Cvr.	50S 50A (125V) Recept. + Std. Brkr. + Cvr.		
50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.	50E 50A (125V) Recept. + 30mA EPD Brkr. + Cvr.		
50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.	50S2 50A (125/250V) Recept. + Std. Brkr. + Cvr.		
50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.	50E2 50A (125/250V) Recept. + 30mA EPD Brkr. + Cvr.		
50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.	50EV 50A (125/250V) EV Recept. (14-50R) + Std. Brkr. + Cvr.		
HH Hose Holder - Pwdr. Ctd. Aluminum	HH Hose Holder - Pwdr. Ctd. Aluminum		

9 LIGHTING	11 ELECTRICAL METER	12 REMOTE MONITORING
LW White (Std. White Lens)	M0 No Electrical Meter	RM0 No Remote Monitoring
LA Amber (Amber Translucent Lens)	M1 Electrical Meter - QTY 1	RM1 Remote Monitoring Enabled
LR Red (Red Translucent Lens)	M2 Electrical Meter - QTY 2	
LB Blue (White Lens w/Blue Internal Tubing)		
LG Green (White Lens w/Green Internal Tubing)		
LO Orange (White Lens w/Orange Internal Tubing)		
FL Fluorescent		

13 WATER FAUCET	16 SPARE BREAKER OPTION 1
W0 No Water Service	B0 No Spare Breaker
W1 3/4" Water Faucet, 1/4 Turn Ball Valve - QTY 1	B20 20A 1-Pole Spare Breaker
W2 3/4" Water Faucet, 1/4 Turn Ball Valve - QTY 2	B2G 20A 1-Pole GFI Spare Breaker
	B30 30A 1-Pole Spare Breaker
	B3G 30A 1-Pole GFI Spare Breaker
	B3E 30A 1-Pole EPD Spare Breaker
	B3D 30A 2-Pole EPD Spare Breaker
	B50 50A 2-Pole Spare Breaker

14 WATER METER	17 SPARE BREAKER OPTION 2
WM0 No Water Meter	B00 No Spare Breaker
WM1 Internal Water Meter - QTY 1	B202 20A 1-Pole Spare Breaker
WM2 Internal Water Meter - QTY 2	B2G2 20A 1-Pole GFI Spare Breaker
	B302 30A 1-Pole Spare Breaker
	B3G2 30A 1-Pole GFI Spare Breaker

15 HOSE HOOKS
NH No Hooks
AH Aluminum Hose Hooks - QTY 2

NOTES: *100A receptacles can only be selected in combined locations A/B or C/D due to spacing.
If a 100A receptacle is selected, the adjacent location must be entered as "R0" (No Receptacle).
Spare breaker availability is subject to remaining breaker panel capacity after receptacles are selected.
High-amperage receptacle combinations may limit or prevent spare breaker selection.
Outlying configurations will be reviewed during quoting or engineering validation.

COMPLETED NUMBER (APPEARS IN SPACE BELOW):

QUANTITY:

CUSTOMER SIGNATURE

(Indicates build approval)



With this signature the customer acknowledges being advised that these Made-To-Order pedestals are non-cancelable, non-refundable, and non-returnable.

