

# SmartlockPro® Dual Function Hospital Grade Tamper-Resistant AFCI/GFCI Receptacle

15 and 20 Amp, 125 Volt

Offers protection both from electrical fires that could result from arc-faults and from electrical shock due to ground faults in one device, satisfying National Electrical Code® (NEC®) requirements for both AFCI and GFCI protection.

Status indicator light provides a simple visual indication to the user of the status of AFCI and GFCI protection

Hospital grade receptacle ensures dependable performance

Impact-resistant thermoplastic cover and body for durability

Engineered to meet the latest UL standard for auto-monitoring (self-test); periodically conducts an automatic internal test to confirm that GFCI protected power is available

### Patented Reset Lockout Mechanism

As an additional safeguard, all Leviton AFCI/GFCI devices feature a lockout function which prevents the device from being reset if any of the following conditions exist:

- It is not functioning properly
- Protection has been compromised
- Line and load wires were reversed during installation

Tamper-resistant shutters meet NEC Article 406.12 requirements



### Common Applications

- Behavioral Health Units (patient bedrooms, restrooms, corridors, and common spaces)
- Other Health Care Facilities



### Ordering Information

Ratings		15 A / 125 V	20 A / 125V
NEMA Configuration		NEMA 5-15R	NEMA 5-20R
ORDER ID	Brown	AGTR1-0HG	AGTR2-0HG
	Ivory	AGTR1-HGI	AGTR2-HGI
	White	AGTR1-HGW	AGTR2-HGW
	Black	AGTR1-HGE	AGTR2-HGE
	Gray	AGTR1-HGG	AGTR2-HGG
	Light Almond	AGTR1-HGT	AGTR2-HGT
	Red	AGTR1-HGR	AGTR2-HGR

## Specifications

Description	
<b>AC Horsepower Rating</b>	
At Rated Voltage	1 hp
<b>Electrical Specifications</b>	
Amperage	15 A or 20 A
Voltage	125 VAC
NEMA	5-15R or 5-20R
Grounding	Self-Grounding
Pole	2
Wire	3
Dielectric Voltage	Withstands 1250VAC per UL 1699A
Short Circuit Current Rating	10 kA
Trip Level	Class A, 5 mA plus or minus 1 mA
Temperature Rise	Max 30°C after 250 cycles OL at 200 percent rated current
<b>Environmental Specifications</b>	
Flammability	Rated V-2 per UL94
Operating Temperature	-35°C to +66°C
<b>Material Specifications</b>	
Face Material	Thermoplastic
Body Material	Polycarbonate
Line Contacts	Brass Double-Wipe .031 Thick
Terminal ID	Brass-Hot, Green-Ground, Silver-Neutral
Mounting Screws	Plated Steel
Strap Material	Galvanized Steel
Clamps	Brass
Ground Clip	Brass
Grounding Screw	Plated Steel
Terminal Screws	Plated Steel
Shutter Mechanism	Acetal
<b>Mechanical Specifications</b>	
Product ID	Ratings permanently marked on device
Terminal Accom.	14-10 AWG
Termination	Back & Side
<b>Standards &amp; Certifications</b>	
NEMA	WD-1 & WD-6
ANSI	C-73
Certification/Listing	UL, CSA (No. M-02A), NOM-ANCE
Applicable Standards	UL 498, UL 1699.A File E480630, CSA C22.2 No. 42, CSA C22.2 No. 144.1, FedSpec W-C-596
<b>Guarantees</b>	
Product Warranty	2-Year Limited

## Dimensions



Visit our Website at:  
[www.leviton.com/healthcare](http://www.leviton.com/healthcare)  
 email: [commercial@leviton.com](mailto:commercial@leviton.com)

Q-1230

020420

**Leviton Manufacturing Co., Inc.**  
 201 N Service Rd, Melville, NY 11747  
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538  
 Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2020 Leviton Manufacturing Co., Inc. All rights reserved.

