

Smart Sensors



Lighting Controls Done Right

Smart, simple sensing and switching or dimming control for virtually any application

Offering customers a complete code-compliant, easy-to-install, and easy-to-configure solution

App configurable with options for out-of-the-box operation

Select the sensing solution that best fits your needs—choose from simple standalone **Smart Wallbox Sensors** or for more advanced lighting control strategies, use **Smart Ceiling Mount Sensors**. For outdoor applications, use **Smart Fixture Mount Sensors**.







Smart Sensors

From standalone sensors to self-contained advanced lighting controls, Leviton has a smart solution for virtually any application. The Smart Sensor line is engineered to be easy to design, install, and configure for code compliance. Smart Wallbox Sensors, Smart Ceiling Mount Sensors, and Smart Fixture Mount Sensors are fully configurable with the Smart Sensor App.

For Distributors

- Stock less models to meet more project requirements
- Offer differentiating features for a competitive advantage
- Take advantage of competitive pricing

For Contractors

- Complete more projects faster for more profits—installation is quick and easy with less components for hardware, labor, and time savings
- Reduce callbacks with professional commercial-grade quality solutions
- Meet more project opportunities

For Building Owners and Facility Managers

- Implement simple to use code compliant solutions for increased energy savings
- Enable as little or as many capabilities as needed with scalable solutions
- Modify the lighting control system with the app to meet changing occupant needs and code changes

For Specifiers


- Specify lighting control solutions with confidence
- Comply with national and local energy codes with solutions that are easy to design, install, and commission
- Make client handoffs easier with easy-to-use customer interfaces





Smart Wallbox Sensors

Smart Wallbox Sensors combine occupancy/vacancy sensing with ON/OFF switching, 0-10V dimming, or 1000W dimming to provide a simple commercial grade solution for easy energy savings, local control, and code compliance. Smart Wallbox Sensors offer easy programming and configuration with the Smart Sensor App, an out-of-the-box default mode for auto-ON/auto-OFF operation with a 10-minute timeout, and convenient pushbutton programming for common room settings. Ideal for commercial spaces up to 1,100 SF including offices, meeting rooms, and lobbies.







Smart Ceiling Mount Sensors

Smart Ceiling Mount Sensors (CMS) deliver an all-in-one code compliant solution. The line simplifies advanced lighting controls by integrating several control strategies into a self-contained, cost-effective, easy-to-install, and easy-to-configure device. Ideal for education, commercial spaces, healthcare, hospitality, and retail applications.

Integrated occupancy/







Smart Fixture Mount Sensors

Smart Fixture Mount Sensors are IP66 rated and designed for use with switching, 0-10V LED dimming drivers, and fluorescent ballasts. The sensors use PIR detection technology and advanced optics to provide an exceptional field-of-view (FOV) for mounting heights from 8 to 40 feet. Configuration is made using the Smart Sensor App. Ideal for warehouses, parking lots and garages, outdoor sports facilities, and building facades.





Smart Wallbox Sensors Comparison

Smart Wallbox Sensors						
	The state of the s		The state of the s			
	ODS15-IDx ODS15-GDx ODS15-I1x	ODD10-IDx	ODD24-IDW	ODP10-l1x		
Technology	PIR					
Mounting	Wall					
Coverage (SF)		1,100				
Pattern		180°				
Mounting Height		40" to 48"				
Configuration	Out-of-the-box default	Out-of-the-box default mode, pushbutton programming, app configurable with the Smart Sensor App				
Timeouts	30 sec, 5 min, 10 min, 20 min, 30 min, and 60 min					
Voltage	120-277VAC, 50/60Hz (ODS15-IDx, ODS15-GDx) 120VAC, 60Hz (ODS15-I1x)	120-277VAC	24V	120VAC		
Occupancy or Vacancy	Occupancy and vacancy					
Dimming	Switching only	0-10V dimming	24V dimming	1000W dimming		
Daylighting	Ambient light hold-OFF					
Other	Connect up to 5 devices for multi-way control; create multi-room templates for fast room replication					
Listing	UL, cUL, FCC, IECC, IC					
Code Compliant	Can be used to comply with IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 occupancy/vacancy, dimming, daylight harvesting, and plug load control requirements					



Smart Wallbox Sensors Comparison

Smart Wallbox Sensors					
	The state of the s	TO THE PART OF T	TOTAL	TO T	
	ODSMT-MDx	ODDMT-MDx	ODDMT-MLx	ODP10-M1x	
Technology	Multi-Technology (PIR & microphonics)				
Mounting	Wall				
Coverage (SF)	1,100				
Pattern	180°				
Mounting Height	30" to 40"				
Configuration	Out-of-the-box default mode, pushbutton programming, app configurable with the Smart Sensor App				
Timeouts	30 sec, 5 min, 10 min, 20 min, 30 min, and 60 min				
Voltage	120-277VAC		24V	120VAC	
Occupancy or Vacancy	Occupancy and vacancy				
Dimming	Switching only	0-10V dimming	24V dimming	1000W dimming	
Daylighting		Ambient light hold-OFF			
Other	Connect up to 5 devices for multi-way control; create multi-room templates for fast room replication				
Listing	UL, cUL, FCC, IECC, IC				
Code Compliant	Can be used to comply with IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 occupancy/vacancy, dimming, daylight harvesting, and plug load control requirements				



Smart Ceiling Mount Sensors Comparison

Smart Ceiling Mount Sensors (CMS)						
	ACY15-DIW	AC705-DMW ACY20-DMW	ACS15-DIW	ACS05-DMW ACS10-DMW ACS20-DMW	AC205-DMW AC220-DMW	
Technology	PIR	Multi-Technology (PIR & U/S)	PIR	Multi-Technology (PIR & U/S)	Multi-Technology (PIR & U/S)	
Mounting			Ceiling Mount			
Coverage (SF)	450-1,500	500 2,000	450-1,500	500 1,000 2,000	500 2,000	
Pattern	180° (AC705 and ACS05), 360° (all others)					
Mounting Height	6' to 20'					
Configuration	Out-of-the-box o	default mode, pushbutt	on programming, app (configurable with the S	imart Sensor App	
Time Delay		30 sec, 5 min	, 10 min, 20 min, 30 mi	n, and 60 min		
Voltage			120-277VAC			
Number of Zones	2	1 (AC705-DMW) 2 (ACY20-DMW)	1	1	2	
Occupancy or Vacancy	Occupancy and vacancy					
Dimming	0-10V dimming		Switching only			
Partial-ON/ Partial-OFF	Yes		No			
Daylighting	Daylight harvesting		Ambient light hold-OFF			
Scheduling	Yes		Yes (when paired with AC705, ACY15, or ACY20)			
Manual Control	PLVSW 1-, 2-, and 4-Button Low Voltage Keypads, Wireless Companion Switch, or Wireless Companion Dimmer		PLVSW 1- and 2-Button Low Voltage Keypads or Wireless Companion Switch			
Other	Combines occupancy/vacancy sensor, photocell, and power pack; includes 2 interchangeable lenses and aisleway masks; independent zone control for up to 10 zones: wirelessly network up to 5 Smart Ceiling Mount Sensors to expand FOV up to 10,000 SF; multi-way control; create multi-room templates for fast room replication; UL924 Listed for emergency lighting					
Listing	UL773A (Occupancy Standard), UL924 (Emergency Equipment), cUL Listed, NOM Certified, RoHS Compliant, NY LLC48 Compliant					
Code Compliant	Can be used to comply with IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 occupancy/vacancy sensing, 0-10V dimming, partial-ON, partial-OFF, daylight harvesting, demand response, and plug load control requirements			acancy sensing,		



Smart Fixture Mount Sensors Comparison

	Sind of faction Floring School (1715)					
	The state of the s	The state of the s	The state of the s			
	ZLD1Z-IOW	ZLDUZ-I0W	OFD1Z	OFDUZ		
Technology	PIR					
Mounting	Internal fix	ture mount	End/external fixture mount			
Coverage (SF)	Up to 8,250					
Pattern	360°					
Mounting Height	8' to 40'					
Configuration	Out-of-the-box default mode and app configurable with the Smart Sensor App					
Timeouts	30 sec, 5 min, 10 min, 20 min, 30 min, and 60 min					
Voltage	120-277VAC	120-480VAC	120-277VAC	120-480VAC		
Occupancy or Vacancy	Occupancy					
Dimming	0-10V dimming					
Daylighting	Multiple daylighting modes: ambient light hold-OFF (switching), daylight harvesting (dimming), and daylight transition lighting (reverse daylight harvesting)					
Scheduling	No	Yes	No	Yes		
Other	IP66 rated, includes 2 interchangeable lenses and aisleway masks; create multi-room templates for fast room replication					
Listing	UL, cUL, FCC, IECC, IC					
Code Compliant	Can be used to comply with IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 occupancy sensing, dimming, and daylight harvesting requirements					





Leviton Manufacturing Co., Inc. Lighting & Controls

10385 SW Avery Street, Tualatin, OR 97062 tel 800-736-6682 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004