


## Hyper Plus 5e CMP UTP Cable

### APPLICATION

Hyper Plus 5e Cat 5e UTP Cables are designed for horizontal network and voice applications in a structured cabling network to connect between the user outlet and horizontal cross-connect.



### BENEFITS

- Universally accepted design for global commercial network installations
- Simplified structured cabling solution preserving long-term network investment
- Characterized to 350 MHz, 250 MHz greater than the standard
- Supports most data and voice applications

### CONSTRUCTION

24 AWG bare copper wire insulated with thermoplastic. Two insulated conductors twisted together to form a pair and four such pairs cabled to form the basic unit under a flame-retardant jacket.

### STANDARDS & REGULATIONS

- ANSI/TIA-568.2-D Cat 5e
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)
- RoHS compliant
- UL 444 rated

### FIRE RATING

- Plenum - NFPA 262, CMP
- ETL Listed

### COUNTRY OF ORIGIN

USA

### WARRANTY INFORMATION

For Leviton product warranties, go to [leviton.com/ns/warranty](http://leviton.com/ns/warranty)

**PRODUCT SPECIFICATIONS**  
**Hyper Plus 5e CMP UTP Cable**

**TECHNICAL SPECIFICATIONS**

**Electrical properties (20 °C ± 5 °C)**

DC resistance	Max. 9.38 Ω/100 m
DC resistance unbalance	Max. 5%
Mutual capacitance	Nom. 5.2 nF/100 m at 1 kHz
Capacitance unbalance (pair-to-ground)	Max. 330 pF/100 m at 1 kHz
Delay skew	45 ns/100 m max.
Nominal velocity of propagation	66%

**CHARACTERISTICS**

**Dimensional Characteristics**

Length per reel	1000 ft (305 m)
Number of pairs	4

**Usage Characteristics**

Category	Cat 5e
Type of cable	UTP
Temperature (Storage):	-20 °C to +60 °C (-4 °F to +140 °F)
Temperature (Installation):	+10 °C to +50 °C (+50 °F to +122 °F)
Temperature (Operating):	-20 °C to +60 °C (-4 °F to +140 °F)
Listed cable temp.	+75 °C (+167 °F)

**HIGH SPEED DATA AND POWER APPLICATIONS**

IEEE 802.3	2.5/5GBASE-T (2.5/5 Gb/s), 1000BASE-T (1 Gb/s), 100BASE-TX (100 Mb/s), 10BASE-T (10 Mb/s)
IEEE 802.3	PoE Types 1, 2, 3, and 4

**COLOR CODE**

Pair 1	Blue	White
Pair 2	Orange	White
Pair 3	Green	White
Pair 4	Brown	White

**TECHNICAL DATA - PHYSICAL**

Conductor	24 AWG bare copper	
Max conductor diameter - in. (mm)	0.020	(0.51)
Max insulated conductor diameter - in. (mm)	0.038	(0.97)
Nom. cable diameter - in. (mm)	0.21	(5.33)
Nom. cable weight - lb./kft (kg/km)	24.8	(36.9)
Max. installation tension - lb. (N)	25	(110)
Min. bend radius - in. (mm)	1	(25.4)

**PRODUCT SPECIFICATIONS**  
**Hyper Plus 5e CMP UTP Cable**

**GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS**

Freq. MHz	RL (dB)		NEXT (dB)		PSNEXT (dB)		ACRF (dB/100 m)	
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee
1	20.0	20.0	65.3	66.3	62.3	62.3	63.8	63.8
4	23.0	23.0	56.3	57.3	53.3	53.3	51.8	51.8
10	25.0	25.0	50.3	51.3	47.3	47.3	43.8	43.8
16	25.0	25.0	47.2	48.2	44.2	44.2	39.7	39.7
20	25.0	25.0	45.8	46.8	42.8	42.8	37.8	37.8
31.25	23.6	23.6	42.9	43.9	39.9	39.9	33.9	33.9
62.5	21.5	21.5	38.4	39.4	35.4	35.4	27.9	27.9
100	20.1	20.1	35.3	36.3	32.3	32.3	23.8	23.8
150**	—	18.9	—	33.7	—	29.7	—	20.3
200**	—	18.0	—	31.8	—	27.8	—	17.8
250**	—	17.3	—	30.3	—	26.3	—	15.8

**GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED**

Freq. MHz	IL (dB/100 m)		ACR* (dB/100 m)		PSACR* (dB/100 m)		PSACRF (dB/100 m)	
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee
1	2.0	2.0	63.3	64.3	60.3	60.3	60.8	60.8
4	4.1	4.1	52.2	53.2	49.2	49.2	48.8	48.8
10	6.5	6.5	43.8	44.8	40.8	40.8	40.8	40.8
16	8.2	8.2	39.0	40.0	36.0	36.0	36.7	36.7
20	9.3	9.3	36.5	37.5	33.5	33.5	34.8	34.8
31.25	11.7	11.7	31.2	32.2	28.2	28.2	30.9	30.9
62.5	17.0	17.0	21.4	22.4	18.4	18.4	24.9	24.9
100	22.0	22.0	13.3	14.3	10.3	10.3	20.8	20.8
150**	—	27.5	—	6.1	—	2.1	—	17.3
200**	—	32.4	—	-0.6	—	-4.6	—	14.8
250**	—	36.9	—	-6.5	—	-10.5	—	12.8

\*TIA values for ACR and PSACR are provided for information only

\*\*Hyper Plus 5e is guaranteed to 100 MHz; values shown above 100 MHz are for information only

**PRODUCT SPECIFICATIONS**  
**Hyper Plus 5e CMP UTP Cable**



Hyper Plus 5e CMP UTP Cable

PART NUMBERS				
Description	Color	Packaging	Length (Ft.)	Part No.
Hyper Plus 5e Plenum	White	Box	1000	10032223
Hyper Plus 5e Plenum	Blue	Box	1000	10032227
Hyper Plus 5e Plenum	Dark gray	Box	1000	10032207
Hyper Plus 5e Plenum	Yellow	Box	1000	10032235
Hyper Plus 5e Plenum	Green	Box	1000	10032232
Hyper Plus 5e Plenum	Pink	Box	1000	10033814
Hyper Plus 5e Plenum	Red	Box	1000	10032229
Hyper Plus 5e Plenum	Black	Box	1000	10033521
Hyper Plus 5e Plenum	Violet	Box	1000	10034885
Hyper Plus 5e Plenum	Orange	Box	1000	10032236
Hyper Plus 5e Plenum	Brown	Box	1000	10063926

For other colors or packaging, contact Customer Support at (800) 722-2082.

**PRINT LEGEND:**  
 BERK-TEK HYPER PLUS 5E 24 AWG CMP 75C C(ETL)US ETL VERIFIED TIA-568.2-D CAT 5E & ISO/IEC 11801 CAT 5 [DATE] [COUNTER] [UID]

For further support information, visit [leviton.com/ns/support](http://leviton.com/ns/support)

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
[infoUSA@leviton.com](mailto:infoUSA@leviton.com)  
 Leviton Berk-Tek Cable: +1 (800) 237 5835  
[berktek.info@leviton.com](mailto:berktek.info@leviton.com)

**Asia Pacific**  
 +852 3620 2602  
[infoAPAC@leviton.com](mailto:infoAPAC@leviton.com)

**Canada**  
 +1 (800) 461 2002  
[infoCanada@leviton.com](mailto:infoCanada@leviton.com)

**Europe**  
 +44 (0) 1592 772124  
[infoEurope@leviton.com](mailto:infoEurope@leviton.com)

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

**Middle East & Africa**  
 +971 (4) 247 9800  
[infoMEA@leviton.com](mailto:infoMEA@leviton.com)

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.