


Cat 6A Universal Tool-Free Plug

APPLICATION

The Cat 6A Universal Tool-Free Plug supports 10GBASE-T networks. The universal connector provides superior alien crosstalk (AXT) suppression and protects critical data from potential EMI/RFI (electromagnetic interference/radio frequency interference). The plug is ideal for government, healthcare, manufacturing, transportation, gaming, and other environments where EMI/RFI and/or security may be a concern. The plug is especially useful for connecting directly to ethernet devices in fixed locations.



SPECIFICATION

The universal plug shall meet or exceed all requirements for Category 6A as described in ANSI/TIA-568.2, as well as Class E_A requirements as described in ISO/IEC 11801-1:2017. The plug shall comply with all National Electrical Codes, be compliant with ANSI/TIA-1096-A, and be UL listed. The plug shall be encased in a die-cast housing to protect it from potential EMI/RFI. The plug shall not require a specialized termination tool. The plug wiring shall accommodate T568 A/B wiring schemes. The plug shall accommodate 26-22 AWG solid or stranded conductors.

MECHANICAL SPECIFICATIONS

Dimensions:	See page 2
Materials:	Connector body: Die-cast zinc Latch and nut: Nylon 94-V0
Cable Diameter:	0.24-0.31 inches (6.0 mm-8.0 mm)
Temp. (Storage):	-40 °C to +70 °C (-40 °F to +158 °F)
Temp. (Installation):	-10 °C to +60 °C (-14 °F to +140 °F)
Temp. (Operating):	-10 °C to +60 °C (-14 °F to +140 °F)

COUNTRY OF ORIGIN

Taiwan

FEATURES & BENEFITS

- Offers easy field termination without special tools
- Robust die-cast housing provides durability and shielding benefits
- Shielding provides EMI/RFI protection, signal isolation, and excellent alien crosstalk (AXT) suppression
- Terminates from 26- to 22-gauge solid or stranded conductors for use on various cable types
- Will exceed IEEE 802.3 PoE standard up to 0.7 Amps (140 watts) continuously
- 360° shield housing provides secure data transmission
- Long release latch ensures easy insertion and removal in confined spaces

DESIGN CONSIDERATIONS

- Suitable for use with Cat 6A and lower shielded and unshielded cable
- Terminate to horizontal cable when connecting to ethernet devices placed in fixed locations
- Verify that the plug housing will fit into the available opening for the application. For extremely tight openings, consider using an ATLAS-X1™ connector with a patch cord or VXC assembly
- After installation, test the connector-plug link using the method for a Modular Plug Terminated Link, as described in ANSI/TIA-568.2

STANDARDS & REGULATIONS

- ANSI/TIA-568.2
- ISO/IEC 11801-1
- c(UL)us Listed
- UL 2043
- RoHS 2
- IEC 60603-7
- IEC 60512-99-001 (includes IEC 60512-9-3)
- ANSI/TIA-1096-A
- UL 2043 Plenum Certified
- EN 50173-1
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)


WARRANTY INFORMATION

For Leviton product warranties, go to Leviton.com/ns/warranty

PRODUCT SPECIFICATIONS

6APLG-S6A

6APLG-S6A



PART NUMBER	
Description	Part No.
Cat 6A Universal Tool-Free Plug	6APLG-S6A

For further support information, visit [Leviton.com/ns/support](https://leviton.com/ns/support)

Page 2 of 2

USA
Network Solutions Headquarters
+1 (800) 722 2082
infoUSA@leviton.com

BERK-TEK™ Cable
+1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
+852 3620 2602
infoAPAC@leviton.com

Canada
+1 (800) 461 2002
infoCanada@leviton.com

Europe
+44 (0) 1592 772124
infoEurope@leviton.com

Latin America
MX: +52 (55) 2128 6286
LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
+971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](https://leviton.com/ns) TO LEARN MORE.