

i24e Dimmer Rack



FEATURES

- Compact wall-mount rack houses up to 24 individual dimmers
- Standard 500 microsecond filter chokes
- Optional redundant Control Module provides seamless backup for each rack
- All rack configuration data is stored in the rack electronics - changing control modules does not require any reprogramming
- Optional Hand Held Terminal provides feedback and control at each rack or remotely
- Stores 100 timed Backup Looks
- Stores 12 Looks for house or stage
- Stacked design provides fresh cooling air to each module, allows full frontal access to interior wiring and terminations
- Built-in Panic Function for each dimmer
- 120V Units, UL Listed and C-UL Listed
- Compatible with Leviton Dimension® Controllers

DIMENSIONAL DATA - IN. [CM] LBS. [KG]

Width	16.0 [40.6]
Depth	15.0 [38.1]
Height	31.0 [78.7]
Weight (w/dimmers)	168.0 [76.0]

SPECIFICATIONS

- The i24e dimmer rack contains 12 dimmer module slots for housing up to 24 dimmers. The rack offers an option for a redundant control module that provides seamless backup in case of the main control module's failure or removal from the rack.

MECHANICAL

- The rack is built from extruded aluminum and code gauge steel, measuring 31" high x 16" wide x 15" deep. All exterior surfaces are finished in textured black polyurethane coat finish. Knock-outs are provided in top and bottom for conduit access. Since the racks require no rear or side access, racks can be wall-mounted side-to-side. The front of the rack is completely open, allowing clear installer access to all line, load and control terminations. Each load termination accepts up to a #4 AWG wire.

- The cooling fans and their control unit are mounted in removable modular housing for easy cleaning and maintenance. Each dimmer receives fresh air through the door-mounted electrostatic filter. Each rack has a locking door.
- All dimmers are housed in removable modules made of die-cast aluminum. Each module contains one or two circuit breakers, a solid-state SCR switching device (SSR), a control PCB, and two filter chokes. All electrical contacts feature self-aligning floating connectors to insure precise alignment of all connections. Modules are keyed so that a module of higher ampacity cannot be inserted into a slot that is wired for a lower ampacity dimmer. All dimmer modules can be inserted and removed without the use of any tools.

ELECTRICAL

- The i Series e rack is designed to operate on voltages ranging from 90-135VAC (120V in nominal) or 187-265VAC (230V is nominal) at 47-63 Hz. Rack can be ordered for use with four-wire three-phase, three-wire single-phase or two-wire single-phase power. The 120V i24e rack is UL Listed and C-UL Listed (for Canadian applications) with a short-circuit current rating of 100,000 AIC providing listed dimmer modules are installed and the racks are not modified. In systems that require a ground wire per load circuit, an optional ground bus can be installed inside the rack. All bussing, and all line and load terminals are copper.

CONTROL MODULES

- Each rack contains an electronic backplane, with all control wiring connections on removable screw terminals for easy control wiring. The backplane also retains all rack configuration and Backup Looks in non-volatile memory, so that when any new control module is inserted, it automatically comes on-line fully functional within ten seconds without requiring programming by the user.
- Each rack requires a single control module that connects to the rack's electronic backplane. Control modules can be inserted and removed without the use of any tools. The backup module is on-line automatically in case of main control module failure.
- Each control module has three LEDs to indicate the presence of voltage on each power phase. The control module stores 100 timed Backup Looks and 12 Looks for house or stage. The 120V control module is UL Listed and C-UL Listed.

FUNCTIONAL

- The control module has an opto-isolated DMX512 input. Control module supports analog controls for storage and playback of 12 Looks of 512 channels each.
- The Hand Held Terminal also provides access to configuration and feedback information.
- Each dimmer can be programmed for the following operation parameters: Minimum and maximum level, and non-dim operation.
- Feedback information appears through the LEDs of each dimmer module or on the Hand Held Terminal plugged into the control module. Feedback information for each dimmer includes the following elements: Active load, Overtemperature.
- Each rack comes with software-selectable Panic operation for each dimmer. Terminals for dry contact closures are provided to initiate a Panic condition, which drives all selected dimmers to full without affecting any other control settings.

HAND HELD TERMINAL

- Each rack system may have an optional Hand Held Terminal. Rack configuration, direct control of dimmers and Backup Looks, and dimmer feedback can all be achieved through the Hand Held Terminal. In multi-rack installations, Hand Held Terminals may access and edit dimmers system wide.

CAT. NO.	DESCRIPTION
IER24-130	i Series e, 24 circuit rack, 120V 3-phase, standard configuration w/ hand held terminal mount
IER24-430	i Series e, 24 circuit rack, 230 V 3-phase, 2.5KW, sequential/phase balanced w/ hand held terminal mount
IER24-43B	i Series e, 24 circuit rack, 230V 3-phase, configured for dual 5KW dimmer modules w/ hand held terminal mount
ACCESSORIES	
IoRg6-GBK	Ground Bus Kit for 96 circuit racks
IoR48-GBK	Ground Bus Kit for 48 circuit racks
IoR24-GBK	Ground Bus Kit for 24 circuit racks
TAHHR-oIE	Hand Held Terminal
For dimmer & air flow module part numbers, please reference the dimmer module data sheet	

LEVITON SPECIFICATION SUBMITTAL	
JOB NAME:	CATALOG NUMBERS:
JOB NUMBER:	

Leviton Manufacturing Co., Inc. Lighting & Energy Solutions

20497 SW Teton Avenue, Tualatin, OR 97062 • Tel: 1-800-736-6682 • FAX: 503-404-5594 • Tech Line (6:00AM-4:00PM P.S.T. Mon-Fri): 1-800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 N. Service Rd. Melville, NY 11747-3138 • Tech Line: 1-800-824-3005 • Fax: 1-800-832-9538

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1Eg • Telephone: 1-800-469-7890 • FAX: 1-800-563-1853

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel. (+52) 55-5082-1040 • FAX: (+52) 5386-1797 • www.leviton.com.mx

Visit our Website at: www.leviton.com/les

© 2013 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.