


Premium Plus Fiber Pigtails and Pigtail Kits

APPLICATION

Premium Plus Fiber Optic Pigtails and Pigtail Kits are ideal for fusion splicing the required fiber connectivity in the data centers, Broadband CATV, Passive Optical Network PON, WDM or DWDM multiplexing, FTTh and voice services in ATM and SONET metropolitan and access networks. Quick turn service is available with orders of up to 100 pigtails or 20 pigtail kits, and ships within three business days. Contact customer service for details.



SPECIFICATION

Multimode and single-mode pigtails shall be manufactured in the USA. Insertion loss shall be a maximum of 0.25 dB for multimode and single-mode. Multimode return loss shall be greater than 26 dB and greater than 50 dB for single-mode connectors. Single-mode angle position polished connectors (APC) shall have a minimum of 60 dB return loss. Pigtails shall have a pull force of 5 N \pm 0.5 (1.12 lb.) per IEC 61300-2-44. Connector durability of greater than 500 matings for both multimode and single-mode. Pigtails or pigtail kits shall be individually packaged with part numbers, descriptions, optical performance, code 39 barcode part number printed on each package, and QR code to access supporting documentation. Individual pigtails shall have flag labels including fiber type and serial number providing traceability to factory collected test data.

COUNTRY OF ORIGIN

USA

WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](https://leviton.com/ns/warranty)

FEATURES & BENEFITS

- Available LC, LC/APC, SC, SC/APC, ST, FC, and FC/APC connector options
- Pigtail kits of 6, 8, 12, or 16 following TIA color sequence
- TIA color-coded LC and SC connectors with white 900-micron boots
- Fiber options: OS2, OM1, OM3, OM4, and OM5
- 100% tested for insertion loss and single-mode return loss
- Premium Plus Series cords include a Limited Lifetime Warranty when used with other Leviton cabling and installed by a Leviton certified contractor
- Quick-turn service for fast delivery
- Custom configurations via [Leviton.com/configurator](https://leviton.com/configurator)

DESIGN CONSIDERATIONS

- All connectors have precision pre-radiused or pre-angled zirconia ferrules for consistent End Face Geometry (EFG)
- Single-mode UPC and APC polish
- FC and ST connectors have metal bodies
- Duplex clips included with duplex configurations
- Bend-insensitive glass (OS2, OM3, OM4, and OM5)

STANDARDS & REGULATIONS

- ANSI/TIA-568.3-E
- ISO/IEC 11801-1
- ANSI/TIA-598-D

Fiber Optic Connector Intermatability Standards (FOCIS)

- TIA -604-10B (LC)
- TIA -604-3B (SC)
- TIA -604-2B (ST)
- TIA -604-4B (FC)
- End face geometry:
IEC 61755-3-1 (UPC/PC), IEC 61755-3-2 (APC)

Fiber compliance:

- OS2: IEC 60793-2-50, TIA 492CAAC, ITU-T G.657.A1
- OM1: IEC 60793-2-10, TIA 492AAAF
- OM3: IEC 60793-2-10, TIA 492AAAF, ITU-T G.651.1
- OM4: IEC 60793-2-10, TIA 492AAAF, ITU-T G.651.1
- OM5: IEC 60793-2-10, TIA 492AAAF, ITU-T G.651.1
- RoHS

PRODUCT SPECIFICATIONS

Premium Plus Fiber Pigtails and Pigtail Kits

MECHANICAL SPECIFICATIONS

Dimensions: 1, 2, or 3 meters
Materials: 900-micron tight buffer fiber
Temp. (Storage): -40 °C to +75 °C (-40 °F to +167 °F)
Temp. (Operating): -20 °C to +70 °C (-4 °F to +158 °F)

OPTICAL SPECIFICATIONS			
	Insertion Loss: Standard Performance	Insertion Loss: Low Loss	Return Loss
Single-mode	≤ 0.25 dB	≤ 0.12 dB	UPC: ≥ 50 dB, APC: ≥ 60 dB
Multimode	≤ 0.25 dB	≤ 0.15 dB	≥ 26 dB

Make-to-order!		PREMIUM PLUS FIBER PIGTAILS AND KITS						
Assembly Type	Fiber Type	Cable Rating	Cable Type	Termination	Kits or Singles	Colors in TIA Order	Cable Length (Ft.)*	Labeling
<ul style="list-style-type: none"> Premium Plus Pigtail Single (PSF) Premium Plus Pigtail Kit (PKF) 	<ul style="list-style-type: none"> 8.2/125 µm SM OS2 (S2) 62.5/125 µm MM OM1 (M1) 50/125 µm LO (10G-300m) MM OM3 (M3) 50/125 µm LO (10G-550m) MM OM4 (M4) 50/125 µm WBMMF OM5 (M5) 	<ul style="list-style-type: none"> PVC (No Rating) (N) 	<ul style="list-style-type: none"> 900-micron tight buffer (9) 	FIRST END <ul style="list-style-type: none"> ST (A) SC (Q) SC/APC (E) LC (R) LC/APC (F) FC (D) FC/APC (G) 	<ul style="list-style-type: none"> Singles** (01) 12 pack of color selected** (00) 6 pack of TIA Colors 1-6 (06) 8 pack of TIA Colors 1-8 (08) 12 pack of TIA Colors 1-12 (12) 16 pack of TIA Colors 1-16 (16) 	<ul style="list-style-type: none"> Blue (01) Orange (02) Green (03) Brown (04) Slate (05) White (Default for Singles) (06**) Red (07) Black (08) Yellow (09) Violet (10) Rose (11) Aqua (12) Olive (13) Magenta (14) Tan (15) Lime (16) 	<ul style="list-style-type: none"> 1 m (3.28) 2 m (6.56) 3 m (9.84) 	<ul style="list-style-type: none"> Custom (C)

*Note on length: Pigtails and Pigtails Kits > 3 meters in length are available upon request
**Note on colors: The standard color is white for OS2, OM1, OM3, and OM4 singles and pack of 12 singles. The standard color is lime for OM5 singles and pack of 12 singles. Other colors are available with longer lead times



For further support information, visit [Leviton.com/ns/support](https://leviton.com/ns/support)

USA Network Solutions Headquarters +1 (800) 722 2082 infoUSA@leviton.com BERK-TEK™ Cable +1 (800) 237 5835 infoUSA@leviton.com	Asia Pacific +852 3620 2602 infoAPAC@leviton.com	Canada +1 (800) 461 2002 infoCanada@leviton.com	Europe +44 (0) 1592 772124 infoEurope@leviton.com	Latin America MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 infoLATAM@leviton.com	Middle East & Africa +971 (4) 247 9800 infoMEA@leviton.com
NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.					