

## MOS Stainless-Steel Wallplates

### APPLICATION

Leviton Multimedia Outlet System (MOS) Stainless-Steel Wallplates provide flush-mount workstation connectivity for copper, fiber, and AV applications. Wallplates accept all MOS modules. The stainless steel wallplates are offered in single-, dual-, and three-gang sizes to provide a durable multimedia solution for education, healthcare, conference rooms, and many other applications. ID windows conceal the mounting screws and provide clean, aesthetic labeling.



### SPECIFICATION

Wallplates shall be front-loading, such that reconfiguration shall be possible from the front without requiring removal or detachment of the wallplate. Wallplate mounting screw holes shall be hidden behind labeling identification windows at the top and bottom of each wallplate opening. Label areas shall be compatible with ANSI/TIA-606-B labeling requirements. Wallplates shall be manufactured from type 304 stainless steel, and shall be available in 1-, 2-, or 3-gang sizes.

### FEATURES

- Front-loading modules allow access to rear connections or terminations without removing entire wallplate
- Ideal for locations where an aesthetic flush-mount look is important along with the durability and appearance of stainless steel is required
- ID windows provide labeling option and conceal mounting screws
- Beveled edge protects against damage from side impact of furniture, equipment, or other forces

### DESIGN CONSIDERATIONS

- Accepts 1-, 1.5-, 2-, and 3-unit-high MOS modules
- Wallplates available in 1-, 2-, and 3-gang sizes
- Wallplates mount to standard NEMA boxes, mud rings, and reducers

### PHYSICAL SPECIFICATIONS

Capacity: Each wallplate opening (“gang”) has a three-unit capacity for MOS modules:

- Three 1-unit high inserts
- Two 1.5-unit high inserts
- One 2-unit high insert + one 1-unit high
- One 3-unit high insert

Dimensions: see page two

Materials: Type 304 stainless steel  
Black polycarbonate (UL 94V-0)

### STANDARDS COMPLIANCE

ANSI/TIA-568-C, cULus, RoHS compliant

### COUNTRY OF ORIGIN


Taiwan

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty)

**ELECTRONIC FILES**

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit [www.leviton.com](http://www.leviton.com).



**41290-xMS**

**PART NUMBERS**

Description	Part No.
MOS Wallplate, single gang w/ ID windows, stainless steel	41290-SMS
MOS Wallplate, dual gang w/ ID windows, stainless steel	41290-DMS
MOS Wallplate, three gang w/ ID windows, stainless steel	41290-TMS

<b>Leviton Network Solutions</b> 2222 - 222nd St. SE Bothell, WA 98021-4416  tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	<b>Asia / Pacific</b> T +1.631.812.6228 E infoasean@leviton.com	<b>Canada</b> T +1.514.954.1840 E pcservice@leviton.com	<b>Caribbean</b> T +1.954.593.1896 E infocaribbean@leviton.com	<b>China</b> T +852.2774.9876 E infochina@leviton.com	<b>Colombia</b> T +57.1.743.6045 E infocolombia@leviton.com
	<b>Europe</b> T +44.0.1592.772124 E customerservice@brand-rex.com	<b>India / SAARC</b> T +971.4.886.4722 E infoindia@leviton.com	<b>Mexico</b> T +52.55.5082.1040 E isamarketing@leviton.com	<b>Middle East &amp; Africa</b> T +971.4.886.4722 E lmeinfo@leviton.com	<b>South Korea</b> T +82.2.3273.9963 E infokorea@leviton.com