

# Berk-Tek Indoor/Outdoor Riser LSZH Premises Distribution (PDRZ-I/O)

Berk-Tek's tight buffered, fiber optic cable is designed for installation in riser and horizontal environments and interbuilding backbone structures.

## DESCRIPTION

Berk-Tek's tight buffered cable is available with standard multimode, single-mode and GIGALite™ fibers.

### Construction

900 µm buffered fibers surrounded by aramid yarns. Sheathed using a special, state-of-the-art low smoke zero halogen polymer material.

All dielectric.

### Outdoor Considerations

- These black jacketed water-blocked riser-rated LSZH cables feature UV and fungus resistant jacketing.
- For use in conduit, below the frost line.
- Loose Tube cables are recommended if interbuilding conduit systems lie above the frost line and are likely to fill with water.
- Tight Buffer fiber cables are not suitable for aerial-lashed installations.

### Flame Rating

Riser, Low-Smoke, OFNR - NFPA 130-2014 Compliant


### Applications

Berk-Tek's tight buffered cable is intended for all high speed data applications including:

- ETHERNET: 10BASE – 40GBASE (10BASE, 100BASE, 1000BASE, 10GBASE, 40GBASE, 100GBASE, 400GBASE)
- Fibre Channel: 1G-FC – 128GFC (1, 2, 4, 8, 16, 32, 128 GFC)
- SONET: OC-1 – OC-768 (OC -1, 3, 12, 24, 48, 192, 768)
- SDH: STM-0 – STM-256 (STM-0, 1, 4, 16, 64, 256)
- OTN: OTU-1 – OTU4 (OTU1, 2, 2e, 2f, 3, 3e2, 4)
- CPRI: CPRI-1 – CPRI-9 (CPRI-1, 2, 3, 4, 5, 6, 7, 7a, 8, 9)
- PON (SMF): RFoG, APON, BPON, EPON, GPON, WDM-PON, NG-PON

### Features

- Low Smoke Zero Halogen Riser-rated UV and fungus resistant polymer used for jacket and subunits
- Flexible, small diameter, 900 µm tight buffered construction
- High tensile strength and small diameter design
- Two to 48 count fiber construction riser-rated LSZH designs ideal for indoor/outdoor, horizontal and backbone installation
- Single-mode, multimode, and hybrid designs available
- Water blocked for Indoor/Outdoor installations, in-conduit and below the frost line.



## STANDARDS

**International** EN 50173;  
IEC 60332-1-2; IEC 60332-1-3;  
IEC 60332-2-2;  
IEC 60332-3-24 Cat.C;  
IEC 60332-3-25 Cat.D;  
IEC 60754-1; IEC 60754-2;  
IEC 61034-2; ISO/IEC 11801;  
NES 713

**National** ANSI/ICEA S-104-696;  
ANSI/ICEA S-83-596;  
ANSI/TIA-568.3-D;  
Telcordia GR-409

## Benefits

- Cost-saving design, easy to install and terminate
- Provides for greater pulling distances thus reducing installation time
- Assurance that cables will meet required specifications for communication networking applications
- Broad design selection allows for mix and match of fiber components to specific networking applications

Country of Origin: U.S.A.

## CHARACTERISTICS

### Construction characteristics

Type of cable

Tight Buffered (TB)

### STANDARD SHEATH COLORS - TIGHT BUFFER - BLACK

Fiber Type	Core Size (µm)	ISO-TIA Standard	Effective Modal BW @ 850 nm	Overfilled Launch BW @ 850 nm	Attenuation @ 850 nm	Attenuation @ 1300 nm	Attenuation @ 1550 nm	Sheath Color
AB	8.3	OS2	NS	NS	NS	0.5 dB/km	0.5 dB/km	Black
CB	62.5	OM1	200 MHz·km	200 MHz·km	3.5 dB/km	1.0 dB/km	NS	Black
EB	50	OM3	2000 MHz·km	1500 MHz·km	3.0 dB/km	1.0 dB/km	NS	Black
FB	50	OM4	4700 MHz·km	3500 MHz·km	3.0 dB/km	1.0 dB/km	NS	Black
XB	50	OM4+	4900 MHz·km	3675 MHz·km	3.0 dB/km	1.0 dB/km	NS	Black
WB	50	OM5	4700 MHz·km	3500 MHz·km	3.0 dB/km	1.0 dB/km	NS	Black

NS = Not Specified

## MANUFACTURING RELEASE

IMPORTANT NOTICE: This product specification is provided for informational purposes only in order to illustrate typical product constructions, applications and/or methods of installation. Because conditions of actual installation and use are unique and will vary, Berk-Tek makes no representation or warranty as to the reliability, accuracy or completeness of this data, even if Berk-Tek is aware of the product's intended use or purpose. Furthermore, this data does not constitute, nor should it be regarded or relied upon, as professional engineering advice. Installation of product should only be done by qualified personnel and in conformance with all safety, electrical and other applicable codes, standards, rules or regulations. Appropriate and correct product selection, installation and use, and compliance with all such codes, standards, rules and regulations, is a customer/end-user responsibility. Product specifications, standards, programs or services are subject to improvement or changes without notice. Berk-Tek accepts no liability for typographical errors, technical inaccuracies, omissions or misuse of the information contained herein. Changes will be periodically made to address any such issues.

# Berk-Tek Indoor/Outdoor Riser LSZH Premises Distribution (PDRZ-I/O)

TECHNICAL DATA - PHYSICAL						Install		Long Term		Install		Long Term	
Fibers	Part Number Prefix	Diameter		Weight		Min. Bend Radius				Max. Loading			
		in.	mm	lb./kft	kg/km	in.	cm	in.	cm	lbf.	N	lbf.	N
6	PDRZ006-I/O(BLA)	0.256	6.5	28	42	3.8	9.8	2.6	6.5	150	667	45	200
12	PDRZ012-I/O(BLA)	0.278	7.1	35	51	4.2	10.6	2.8	7.1	150	667	45	200
24	PDRZ024-I/O(BLA)	0.301	7.6	55	82	4.5	11.5	3.0	7.6	300	1335	90	400
36	PDRZ12B036-I/O(BLA)	0.555	14.1	115	171	8.3	21.1	5.6	14.1	300	1335	90	400
48	PDRZ12B048-I/O(BLA)	0.590	15.0	137	207	8.9	22.5	5.9	15.0	600	2670	180	800

TECHNICAL DATA										
Fiber Type	Part Number Suffix	Berk-Tek Fiber	Core Size	Wavelength (nm)	Maximum Attenuation (dB/km)	Effective Modal Bandwidth @ 850 nm (MHz•km)	Distance (meters)			
<b>Multimode - Bend Insensitive</b>							<b>1 GbE</b>	<b>10 GbE</b>	<b>40 GbE</b>	<b>100 GbE</b>
OM1	CB3510/25	GIGAlite	62.5 µm	850/1300	3.5/1.0	200	300	33	N/A	N/A
OM3	EB3010/25	GIGAlite-10	50 µm	850/1300	3.0/1.0	2000	1000	300	100	70
OM4	FB3010/F5	GIGAlite-10FB	50 µm	850/1300	3.0/1.0	4700	1040	550	150	100
OM4+	XB3010/X5	GIGAlite-10XB	50 µm	850/1300	3.0/1.0	4900	1210	600	300	150
<b>WideBand Multimode - Bend Insensitive</b>							<b>1 GbE</b>	<b>10 GbE</b>	<b>40 GbE</b>	<b>100 GbE</b>
OM5	WB3010/W5	GIGAlite-10WB	50 µm	850-953/1300	3.0/1.0	4700	1040	550	190	100
<b>Single-Mode - Bend Insensitive - ITU-T G.652.D and G.657.A1 Compliant</b>							<b>1 GbE</b>	<b>10 GbE</b>	<b>40 GbE</b>	<b>100 GbE</b>
OS2	AB0707	Standard for Tight Buffer	SMF	1310/1550	0.5/0.5	N/A	≥ 5000	≥ 10000	≥ 10000	≥ 10000