


PRODUCT SPECIFICATIONS

BERK-TEK™ LANMARK™-1000 Cat 6 OSP Cable

BERK-TEK LANMARK-1000 Cat 6 OSP Cable

APPLICATION

BERK-TEK LANMARK-1000 OSP (Outside Plant) enhanced Category 6 OSP cables are designed for outside applications, either aerial or buried in conduit or duct, where building to building interconnections must be made. Can be used to interconnect buildings or can be run beneath a slab in duct or conduit.



FEATURES & BENEFITS

- Fully water blocked
- 23 AWG bare copper wire insulated with a black weather-resistant thermoplastic jacket
- Two insulated conductors twisted together to form a pair and four such pairs laid up with cross filler to form the basic unit
- Cable injected with a water-resistant flooding compound
- Simplified structured cabling solution preserving long-term network investment
- Warranted, trouble-free cabling installation and maintenance
- Meets NEC requirement for wet locations

STANDARDS & REGULATIONS

- ANSI/TIA-568.2 Cat 6
- ANSI/ICEA S-56-434
- ISO/IEC 11801
- ANSI/ICEA 5-107-704-2012, PAR 8.2.1
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

COUNTRY OF ORIGIN

USA

WARRANTY INFORMATION

For Leviton product warranties, go to Leviton.com/ns/warranty

PRODUCT SPECIFICATIONS
BERK-TEK™ LANMARK™-1000 Cat 6 OSP Cable

TECHNICAL SPECIFICATIONS

Electrical Properties (20 °C ± 5 °C)	
DC resistance	Max. 9.38 Ω/100 m
DC resistance unbalance	Max. 5 %
Mutual capacitance	Nom. 5.3 nF/100 m at 1 kHz
Capacitance unbalance (pair-to-ground)	Max. 330 pF/100 m at 1 kHz
Delay skew	35 ns/100 m max.
Nominal velocity of propagation	65 %

CHARACTERISTICS

Category	Cat 6
Field of application	Outdoor
Type of cable	OSP
Temp. (Storage):	-40 °C to +60 °C (-40 °F to +140 °F)
Temp. (Installation):	-10 °C to +50 °C (14 °F to +122 °F)
Temp. (Operating):	-40 °C to +60 °C (-40 °F to +140 °F)

TECHNICAL DATA - PHYSICAL

Conductor	23 AWG bare copper	
Max conductor diameter - in. (mm)	0.022	(0.56)
Max insulated conductor diameter - in. (mm)	0.04	(1.02)
Nom. cable diameter - in. (mm)	0.245	(6.22)
Nom. cable weight - lb./kft (kg/km)	30.5	(45.4)
Max. installation tension - lb. (N)	25	(110)
Min. bend radius - in. (mm)	1.00	(25.4)

HIGH SPEED DATA AND POWER APPLICATIONS

IEEE 802.3	2.5/5GBASE-T (2.5/5 Gb/s), 1000BASE-T (1 Gb/s), 100BASE-TX (100 Mb/s), 10BASE-T (10 Mb/s)
IEEE 802.3	PoE Types 1, 2, 3, and 4

COLOR CODE

Pair 1	Blue	White
Pair 2	Orange	White
Pair 3	Green	White
Pair 4	Brown	White

PRODUCT SPECIFICATIONS

BERK-TEK™ LANMARK™-1000 Cat 6 OSP Cable



BERK-TEK LANMARK-1000 Cat 6 OSP Cable

GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS

Freq. MHz	RL (dB)		NEXT (dB)		PSNEXT (dB)		ACR** (dB)		PSACR† (dB)	
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee
1	20.0	20.0	74.3	79.3	72.3	77.3	72.3	77.3	70.3	75.3
4	23.0	23.6	65.3	70.3	63.3	68.3	61.5	66.5	59.5	64.5
10	25.0	26.0	59.3	64.3	57.3	62.3	53.3	58.4	51.3	56.4
16	25.0	26.0	56.2	61.2	54.2	59.2	48.7	53.7	46.7	51.7
20	25.0	26.0	54.8	59.8	52.8	57.8	46.3	51.4	44.3	49.4
31.25	23.6	25.0	51.9	56.9	49.9	54.9	41.2	46.3	39.2	44.3
62.5	21.5	23.5	47.4	52.4	45.4	50.4	32.0	37.1	30.0	35.1
100	20.1	22.5	44.3	49.3	42.3	47.3	24.5	29.6	22.5	27.6
250	17.3	20.5	38.3	43.3	36.3	41.3	5.5	10.7	3.5	8.7
350	—	19.8	—	41.1	—	39.1	—	1.6	—	-0.4
400*	—	19.5	—	40.3	—	38.3	—	-2.4	—	-4.4
500*	—	19.0	—	38.8	—	36.8	—	-9.8	—	-11.8
550*	—	18.8	—	38.2	—	36.2	—	-13.2	—	-15.2

*LANMARK-1000 OSP is guaranteed to 350 MHz; values shown above 350 MHz is for information only.

**ACR is provided for information only for LANMARK-1000 OSP (not guaranteed).

†PSACR is a guaranteed parameter for LANMARK-1000 OSP up to 250 MHz; any value above this is provided for information only. TIA values are provided as calculations.

GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED

Freq. MHz	IL (dB)		ACRF (dB)		PSACRF (dB)		LCL/TCL** (dB)	ELTCTL (dB)
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	Product Guarantee	Product Guarantee
1	2.0	2.0	67.8	72.8	64.8	69.8	50.0	35.0
4	3.8	3.8	55.8	60.8	52.8	57.8	44.0	23.0
10	6.0	5.9	47.8	52.8	44.8	49.8	40.0	15.0
16	7.6	7.5	43.7	48.7	40.7	45.7	38.0	10.9
20	8.5	8.4	41.8	46.8	38.8	43.8	37.0	9.0
31.25	10.7	10.6	37.9	42.9	34.9	39.9	35.1	—
62.5	15.4	15.3	31.9	36.9	28.9	33.9	32.0	—
100	19.8	19.7	27.8	32.8	24.8	29.8	30.0	—
250	32.8	32.6	19.8	24.8	16.8	21.8	26.0	—
350	—	39.5	—	21.9	—	18.9	24.6	—
400*	—	42.7	—	20.8	—	17.8	24.0	—
500*	—	48.6	—	18.8	—	15.8	23.0	—
550*	—	51.4	—	18.0	—	15.0	22.6	—

*LANMARK-1000 is guaranteed to 350 MHz; values shown above 350 MHz is for information only.

**LCL/TCL is a guaranteed parameter for LANMARK-1000 OSP up to 250 MHz; any value above this is provided for information only.

PRODUCT SPECIFICATIONS
BERK-TEK™ LANMARK™-1000 Cat 6 OSP Cable

PART NUMBERS

Description	Color	Packaging	Part No.
LANMARK-1000 Category 6 OSP Cable	Black	Reel	11072213

PRINT LEGEND:

BERK-TEK LANMARK-1000 CAT 6 23AWG TYPE F OUTDOOR TIA-568.2 CAT 6 & ISO/IEC 11801 CAT 6 [DATE] [COUNTER]
FTTIA-568.2 CAT 6 & ISO/IEC 11801 CAT 6 [DATE] [COUNTER] FT

BERK-TEK LANMARK-1000 Cat 6 OSP Cable

For further support information, visit Leviton.com/ns/support

Page 4 of 4

USA
Network Solutions Headquarters
+1 (800) 722 2082
infoUSA@leviton.com
BERK-TEK™ Cable
+1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
+852 3620 2602
infoAPAC@leviton.com

Canada
+1 (800) 461 2002
infoCanada@leviton.com

Europe
+44 (0) 1592 772124
infoEurope@leviton.com

Latin America
MX: +52 (55) 2128 6286
LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
+971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.