


## AC6FF Cat 6A F/FTP EuroClass B2ca Cables

### APPLICATION

Leviton Cat 6A F/FTP cables exceed Category 6A performance standards. They are rated to 500 MHz and are suitable for use in all Class E<sub>A</sub> structured cable systems. The applications supported include 10 Gigabit Ethernet, Gigabit Ethernet, Power over Ethernet, and broadband video transmissions at frequencies up to 500 MHz.



### COUNTRY OF ORIGIN

UK

### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/NS/Warranty](http://Leviton.com/NS/Warranty)

### FEATURES & BENEFITS

- 23 AWG solid annealed copper wire
- 4 twisted pairs individually screened and cabled together – providing excellent EMI immunity
- Overall aluminum polyester screen – for improved shielding efficiency and increased heat dissipation
- Designed to support all Class E<sub>A</sub> protocols including 10GBASE-T
- Halogen Free Flame Retardant – Low Smoke
- Enhanced HFFR-LS material meets the requirements of the Construction Products Regulation (CPR) EuroClass B2ca
- Orange jacket to identify EuroClass level B2ca. Also available in a range of non-standard colors
- CE marked for CPR
- Reel and box packaging are 100% recyclable

### STANDARDS & REGULATIONS

- ISO/IEC 11801 Class E<sub>A</sub>
- IEC 61156-5
- EN 50173-1
- EN 50288-10-1
- ANSI/TIA 568.2-D
- 10GBASE-T
- 802.11ac wireless
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

**PRODUCT SPECIFICATIONS**  
**AC6FF Cat 6A F/FTP EuroClass B2ca Cables**

**TECHNICAL SPECIFICATIONS**

**Primary Electrical Parameters**

Conductor loop resistance	Max 19 Ω/100m	14Ω/100m
Conductor resistance unbalance	Max. 2%	0.1%
Insulation resistance	>5GΩ.km	>50GΩ.km
Dielectric strength	2500 Vdc/2secs	Pass

**Secondary Electrical Parameters**

Velocity of propagation	<534nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay skew	Max. 45nsec/100m @ 100MHz	4nsec/100m @ 100MHz
Mean Characteristic Impedance	100Ω +/- 5Ω @ 100MHz	100Ω ± 3Ω @ 100MHz
Coupling Attenuation	Type 1	84dB
Transfer Impedance	Grade 2	11mΩ/m @ 10MHz

**MECHANICAL SPECIFICATIONS**

**Usage Characteristics**

Category	Cat 6A
Type of cable	F/FTP
Temp. (Installation)	0 °C to +50 °C (32 °F to +122 °F)
Temp. (Operating)	-20 °C to +75 °C (-4 °F to +167 °F)

**TECHNICAL DATA - PHYSICAL**

Max. tensile load (Installation)	10kg
Segregation class	Class D
Min. bend radius (Installation)	8 x Outer Diameter
Min. bend radius (Operation)	4 x Outer Diameter
Field test NVP value	0.80

**REACTION TO FIRE**

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / EuroClass	—	EN 13501-6	B2ca s1a d1 a1
Single Cable Flame Rating	IEC 60332-1-2	—	—
Smoke Production	—	EN 50399	s1a
Flaming Droplets/Particles	—	EN 50399	d1
Acid Gas Emission/Acidity	—	EN 50267-2-3	a1

**PRODUCT SPECIFICATIONS**  
**AC6FF Cat 6A F/FTP EuroClass B2ca Cables**



AC6FF Cat 6A F/FTP EuroClass B2ca Cables

**PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS**

Freq. MHz	IL (dB)		NEXT (dB)		PSNEXT (dB)		ACRF (dB)		PSACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	2.1	1.9	75.3	100.0	72.3	97.0	68.0	90.0	65.0	87.0
4	3.8	3.5	66.3	100.0	63.3	97.0	56.0	90.0	53.0	87.0
10	5.9	5.5	60.3	100.0	57.3	97.0	48.0	90.0	45.0	87.0
20	8.4	7.8	55.8	100.0	52.8	97.0	42.0	84.8	39.0	81.8
100	19.1	18.0	45.3	94.3	42.3	91.3	28.0	70.8	25.0	67.8
200	27.6	26.1	40.8	88.9	37.8	85.9	22.0	64.8	19.0	61.8
250	31.1	29.4	39.3	87.1	36.3	84.1	20.0	62.8	17.0	59.8
500	45.3	43.0	34.8	81.7	31.8	78.7	14.0	56.8	11.0	53.8
550	—	45.4	—	81.0	—	78.0	—	56.0	—	53.0

Note: The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters

**PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED**

Freq. MHz	RL (dB)		PSANEXT (dB)		PSAACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical
1	20.0	27.0	67.0	100.0	67.0	98.1
4	23.0	30.0	67.0	100.0	66.2	96.5
10	25.0	30.0	67.0	100.0	58.2	94.5
20	25.0	30.0	67.0	100.0	52.2	92.2
100	20.1	25.1	62.5	100.0	38.2	82.0
200	18.0	23.0	58.0	100.0	32.2	73.9
250	17.3	22.3	56.5	100.0	30.2	70.6
500	17.3	20.2	52.0	100.0	24.2	57.0
550	—	19.9	—	100.0	—	54.6

Note: The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters

**STANDARD PACKAGING SPECIFICATIONS - REELS**

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Reel Size Flange Dia. x Width (mm)	Gross Weight (kg/Item)	Items Per Pallet
AC6F/FTP-B2ca-500OR	500	Orange †	7.0	50.2	400 x 390	27.6	12
AC6F/FTP-B2ca-1000OR	1000	Orange †	7.0	50.2	600 x 325	56.2	6

† Also available in a range of non-standard colors

For further support information, visit [Leviton.com/NS/Support](http://Leviton.com/NS/Support)

Page 3 of 3

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
[infoUSA@leviton.com](mailto:infoUSA@leviton.com)  
 Leviton Cable (formerly Berk-Tek)  
 +1 (800) 237 5835 | [infoUSA@leviton.com](mailto:infoUSA@leviton.com)

**Asia Pacific**  
 +852 3620 2602  
[infoAPAC@leviton.com](mailto:infoAPAC@leviton.com)

**Canada**  
 +1 (800) 461 2002  
[infoCanada@leviton.com](mailto:infoCanada@leviton.com)

**Europe**  
 +44 (0) 1592 772124  
[infoEurope@leviton.com](mailto:infoEurope@leviton.com)

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

**Middle East & Africa**  
 +971 (4) 247 9800  
[infoMEA@leviton.com](mailto:infoMEA@leviton.com)

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.