

## eXtreme™ CAT 6+ U/UTP Cable, Riser Rated

### PART NUMBERS


Description	Part No.
eXtreme CAT 6+ U/UTP Cable, Riser Rated, blue, 305-meter reel in box	104-UTP6R-MLB
eXtreme CAT 6+ U/UTP Cable, Riser Rated, grey, 305-meter reel in box	105-UTP6R-MSB
eXtreme Cat 6+ U/UTP Cable, Riser Rated, white, 305-meter reel in box	106-UTP6R-MWB

### APPLICATION

IEEE 802.3: 1000BASE-T; 100BASE-T; 10BASE-T

### STANDARDS COMPLIANCE

- ANSI/TIA-568.2-D CAT 6
- ISO/IEC 11801-1 Class E
- EN 50173-1 Class E
- IEC 61156-5
- EN 50288-6-1
- RoHS 2 Compliant
- IEEE 802.3bt PoE Type 1 (15.4 Watts) formerly 802.3af, Type 2 (30 Watts) formerly 802.3at, Type 3 (60 Watts), Type 4 (90 Watts)
- Cisco UPoE (60 Watts), UPoE+ (90 Watts)
- Power over HDBaseT™ PoH (95 Watts)



### FIRE RATING

UL 1666

### COUNTRY OF ORIGIN

Taiwan

### Construction

Conductor	Bare copper wire	23 AWG
Insulation	Polyethylene	Ø 0.99 mm
Twisting	4 twisted pairs, 2 single conductors paired Twisted pair color code: 1: Blue+White/Blue      2: Orange+White/Orange 3: Green+White/Green    4: Brown+White/Brown	
Cable lay-up	4 pairs with different pitches	
Outer jacket	CMR	
Outer diameter	Ø 6.1 mm (.240")	

<b>TECHNICAL SPECIFICATIONS</b>	
<b>Mechanical Properties</b>	
Bending Radius	≥ 4 x OD without load
Temperature range	during operation: -20° C ~ 60° C during installation: 0° C ~ 50° C
<b>Electrical Properties (-20° C ± 5° C)</b>	
DC resistance	Max. 9.38 Ω/100 m at 20° C
Resistance unbalance	Max. 2% at 20° C
Insulation resistance (500V)	Min. 5000 MΩ/Km at 20° C
Mutual capacitance	Nom. 5.1 nf/100 m at 1kHz
Capacitance unbalance (pair to ground)	Max. 160 pf/100 m at 1kHz
Characteristic impedance (1 - 100MHz)	(100 ± 15) Ω
Nominal velocity of propagation	66%
Test voltage (DC, 1 min.)	1 kV/1 min.
Delay Skew	45 ns/100 m (Max.)

<b>Transmission characteristics acc. to ANSI/TIA-568.2-D CAT 6 (20° C)</b>							
Freq. (MHz)	Attenuation (dB) max.	NEXT (dB) min.	PS-NEXT (dB) min.	ACRF (dB) min.	PS-ACRF (dB) min.	Return Loss (dB) min.	Propagation Delay (ns/100m) max.
1	2.0	74.3	72.3	67.8	64.8	20.0	570.0
4	3.8	65.3	63.3	55.8	52.8	23.0	552.0
10	6.0	59.3	57.3	47.8	44.8	25.0	545.4
16	7.6	56.3	54.3	43.7	40.7	25.0	543.0
20	8.5	54.8	52.8	41.8	38.8	25.0	542.0
31.25	10.7	51.9	49.9	37.9	34.9	23.6	540.4
62.5	15.4	47.4	45.4	31.9	28.9	21.5	538.6
100	19.8	44.3	42.3	27.8	24.8	20.1	537.6
200	29.0	39.8	37.8	21.8	18.8	18.0	536.6
250	32.8	38.3	36.3	19.8	16.8	17.3	536.3

<b>Leviton Network Solutions</b> 2222 - 222nd St. SE Bothell, WA 98021-4416  tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	<b>Asia / Pacific</b> T +1.631.812.6228 E infoasean@leviton.com	<b>Canada</b> T +1.514.954.1840 E pcservice@leviton.com	<b>Caribbean</b> T +1.954.593.1896 E infocaribbean@leviton.com	<b>China</b> T +852.2774.9876 E infochina@leviton.com	<b>Colombia</b> T +57.1.743.6045 E infocolombia@leviton.com
	<b>Europe</b> T +44.0.1592.772124 E customerserviceeu@leviton.com	<b>Mexico</b> T +52.55.5082.1040 E lsamarketing@leviton.com	<b>Middle East &amp; Africa</b> T +971.4.247.9800 E lmeinfo@leviton.com	<b>South Korea</b> T +82.2.3273.9963 E infokorea@leviton.com	