

eXtreme™ Cat 5e U/UTP Cable, Riser Rated


UTP5R-M*B

PART NUMBERS

Description	Part No.
eXtreme Cat 5e U/UTP Cable, Riser Rated, blue, 305-meter reel in box	290-UTP5R-MLB
eXtreme Cat 5e U/UTP Cable, Riser Rated, white, 305-meter reel in box	291-UTP5R-MWB
eXtreme Cat 5e U/UTP Cable, Riser Rated, grey, 305-meter reel in box	292-UTP5R-MSB

APPLICATION

IEEE 802.3: Gigabit Ethernet; 1000BASE-T; 100BASE-T; 10BASE-T



STANDARDS COMPLIANCE

- ANSI/TIA-568.2-D
- ISO/IEC 11801-1 Class D
- EN 50173-1 Class D
- IEC 61156-5
- RoHS 2 Compliant
- IEEE 802.3bt PoE Type 1 (15.4 Watts) formerly 802.3af, Type 2 (30 Watts) formerly 802.3at, Type 3 (60 Watts)
- Cisco UPoE (60 Watts)

FIRE RATING

UL 1666

COUNTRY OF ORIGIN

Korea

Construction		
Conductor	Bare copper wire	24 AWG
Insulation	Polyethylene	Ø 0.90 mm
Twisting	4 twisted pairs, 2 single conductors paired Twisted pair color code: 1: Blue+White/Blue 2: Orange+White/Orange 3: Green+White/Green 4: Brown+White/Brown	
Cable lay-up	4 pairs with different pitches	
Outer jacket	CMR	
Outer diameter	Ø 5.2 mm ± 0.2 mm (.205")	

Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E infocaribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +44.0.1592.772124 E customerserviceeu@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.247.9800 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com	

TECHNICAL SPECIFICATIONS

Mechanical Properties	
Bending Radius	≥ 4 x OD without load
Temperature range	during operation: -20° C ~ 75° C during installation: 0° C ~60° C
Electrical Properties (-20° C ± 5° C)	
DC resistance	Max. 9.38 Ω/100 m at 20° C
Resistance unbalance	Max. 5% at 20° C
Insulation resistance (500V)	Min. 5000 MΩ/Km at 20° C
Mutual capacitance	Max. 5.6 nf/100 m at 1kHz
Capacitance unbalance (pair to ground)	Max. 330 pf/100 m at 1kHz
Characteristic impedance (1 - 100MHz)	(100 ± 15) Ω
Nominal velocity of propagation	70%
Test voltage (DC, 1 min.)	1 kV/1 min.
Delay Skew	≤ 45 ns/100 m
Propagation Delay	≤ 535 ns/100 m

Transmission characteristics acc. to ANSI/TIA-568.2-D Cat 5e (20° C)

Freq. (MHz)	Attenuation (dB) max.	NEXT (dB) min.	PS-NEXT (dB) min.	ELFEXT (dB) min.	PS-ELFEXT (dB) min.	Return Loss (dB) min.
1	2.0	65.3	62.3	63.8	60.8	20.0
4	4.1	56.3	53.3	51.7	48.7	23.0
8	5.8	51.8	48.8	45.7	42.7	24.5
10	6.5	50.3	47.3	43.8	40.8	25.0
16	8.2	47.3	44.4	39.7	36.7	25.0
20	9.3	45.8	42.8	37.7	34.7	25.0
25	10.4	44.3	41.3	35.8	32.8	24.3
31.25	11.7	42.9	39.9	33.9	30.9	23.6
62.5	17.0	38.4	35.4	27.8	24.8	21.5
100	22.0	35.3	32.3	23.8	20.8	20.1

Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
T +44.0.1592.772124
E customerserviceeu@leviton.com

Mexico
T +52.55.5082.1040
E lsamarketing@leviton.com

Middle East & Africa
T +971.4.247.9800
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com