


C7SF Euroclass Cca Cables

APPLICATION

Leviton Category 7 S/FTP cables exceed Category 7 performance standards. They are specified to 600 MHz and rated to 1000 MHz and are suitable for use in all Class F structured wiring cable systems. The applications supported include 10 Gigabit Ethernet, Gigabit Ethernet, Power over Ethernet (PoE), and broadband video transmissions at frequencies up to 600 MHz.



COUNTRY OF ORIGIN

UK

WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](https://leviton.com/ns/warranty)

FEATURES & BENEFITS

- 23 AWG solid annealed copper wire
- 4 twisted pairs individually shielded and cabled together – providing EMI immunity
- Twisted pairs color coded in accordance with EN 50288-1
- Overall braided screen – for improved shielding efficiency, increased mechanical robustness and heat dissipation
- Designed to support all Class F protocols including 10GBASE-T
- Enhanced HFFR-LS (Halogen-Free Flame Retardant – Low Smoke) material enables the cable to meet the requirements of the Construction Products Regulation (CPR) Euroclass Cca

STANDARDS & REGULATIONS

- ISO/IEC 11801 Class F
- IEC 61156-5
- EN 50173-1
- EN 50288-4-1
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

PRODUCT SPECIFICATIONS

C7SF Euroclass Cca Cables

TECHNICAL SPECIFICATIONS

Primary Electrical Parameters	Specification	Typical Performance
Conductor loop resistance	Max 19 Ω /100m	14 Ω /100m
Conductor resistance unbalance	Max. 2%	0.1%
Insulation resistance	>5G Ω .km	>50G Ω .km
Dielectric strength	2500 Vdc/2secs	Pass
Secondary Electrical Parameters		
Velocity of propagation	<534nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay skew	Max. 45nsec/100m @ 100MHz	4nsec/100m @ 100MHz
Mean Characteristic Impedance	100 Ω +/- 5 Ω @ 100MHz	100 Ω $\pm$ 3 Ω @ 100MHz
Coupling Attenuation	Type 1	90dB
Transfer Impedance	Grade 1	8m Ω /m @ 10MHz

MECHANICAL SPECIFICATIONS

Usage Characteristics

Category	Cat 7
Type of cable	S/FTP
Temp. (Installation)	0 °C to +50 °C (32 °F to +122 °F)
Temp. (Operating)	-20 °C to +75 °C (-4 °F to +167 °F)

TECHNICAL DATA - PHYSICAL

Max. tensile load (Installation)	10 kg
Segregation class	Class D
Min. bend radius (Installation)	8 x Outer Diameter
Min. bend radius (Operation)	4 x Outer Diameter
Field test NVP value	0.80

REACTION TO FIRE (SINGLE CABLES)

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / Euroclass	—	EN 13501-6	Cca s1a d1 a1
Single Cable Flame Rating	IEC 60332-1-2	—	Pass
Bundled Cable Flame Rating	IEC 60332-3-24	—	Pass
Smoke Production	—	EN 60134	Pass
Acid Gas Emission/Acidity	IEC 50267-2-3	—	Pass

REACTION TO FIRE (DUPLEX CABLES)

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / Euroclass	—	EN 13501-6	Cca s1a d1 a1
Single Cable Flame Rating	IEC 60332-1-2	—	Pass
Bundled Cable Flame Rating	IEC 60332-3-24	—	Pass
Smoke Production	—	EN 60134	Pass
Acid Gas Emission/Acidity	IEC 50267-2-3	—	Pass

PRODUCT SPECIFICATIONS

C7SF Euroclass Cca Cables

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS										
Freq.	IL (dB)		NEXT (dB)		PSNEXT (dB)		ACRF (dB)		PSACRF (dB)	
MHz	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	2.0	1.9	80.0	100.0	77.0	97.0	80.0	103.9	77.0	100.9
4	3.7	3.5	80.0	100.0	77.0	97.0	80.0	103.9	77.0	100.9
10	5.9	5.5	80.0	100.0	77.0	97.0	74.0	102.8	71.0	99.8
100	19.0	18.0	72.4	100.0	69.4	97.0	54.0	89.4	51.0	86.4
200	27.5	25.7	67.9	100.0	64.9	97.0	48.0	78.2	45.0	75.2
250	31.0	28.7	66.5	100.0	63.5	97.0	46.0	74.6	43.0	71.6
500	45.3	41.1	61.9	100.0	58.9	97.0	40.0	65.2	37.0	62.2
600	50.1	45.5	60.8	95.0	57.8	92.0	38.4	55.2	35.4	52.2
1000	—	60.9	—	89.0	—	86.0	—	50.8	—	47.8

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED				
Freq.	RL (dB)		PSANEXT (dB)	PSAACRF (dB)
MHz	Standard	Typical	Typical	Typical
1	20.0	27.0	100.0	98.1
4	23.0	33.1	100.0	96.5
10	25.0	34.0	100.0	94.5
100	20.1	39.3	100.0	92.2
200	18.0	38.4	100.0	82.0
250	17.3	34.4	100.0	73.9
500	17.3	28.7	100.0	70.6
600	17.3	27.1	100.0	57.0
1000	—	24.6	100.0	54.6

Note: The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters

PART NUMBER									
Description	Color	Length (m)	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Packaging				Part No.
					Type	Reel Size Flange Dia. x Width (mm)	Gross Weight (kg/Item)	Items Per Pallet	
Cat 7 S/FTP Cable, Euroclass Cca	Green†	500	7.2	54.3	Reel	400 x 390	29.6	12	UM10-Cca-500GN
Cat 7 S/FTP Cable, Euroclass Cca	Green†	1000	7.2	54.3	Reel	600 x 405	60.8	4	UM10-Cca-1000GN
Cat 7 S/FTP Cable, Euroclass Cca	Green†	500	7.1 x 14.4	102.2	Reel	600 x 405	57.6	4	UM10-Cca-D500GN

† Also available in a range of non-standard colors

For further support information, visit Leviton.com/ns/support