

Category 6 F/FTP EuroClass Cca Cables

Datasheet: GD103458v12




APPLICATION

Leviton Category 6 F/FTP cables exceed Category 6 performance standards. They are rated to 250MHz and are suitable for use in all Class E structured wiring cable systems. The applications supported include Gigabit Ethernet, Power over Ethernet, and broadband video transmissions at frequencies as high as 250MHz.

FEATURES AND BENEFITS

- 23 AWG solid annealed copper wire
- 4 twisted pairs individually screened and cabled together – providing EMI immunity
- Overall aluminum polyester screen – for improved shielding efficiency and increased heat dissipation
- Designed to support all Class E protocols including Gigabit Ethernet
- Enhanced HFFR-LS* material meets the requirements of the Construction Products Regulation (CPR) EuroClass Cca
- Green jacket to identify EuroClass level Cca
- Included in the Leviton Limited 25-Year System Warranty when used in conjunction with Leviton copper connectivity. System warranties are available for qualified projects installed by certified contractors

*Halogen Free Flame Retardant – Low Smoke



STANDARDS

- Designed and constructed to give optimum electrical performance to the following standards:
 - ISO/IEC 11801 Class E, IEC 61156-5
 - EN50173-1 and EN 50288-5-1
 - ANSI/TIA 568.2-D
- Recommended for PoE standards:
 - IEEE 802.3bt PoE Type 1 (15.4 Watts) formerly 802.3af and IEEE 802.3bt PoE Type 2 (30 Watts) formerly 802.3at
 - IEEE 802.3bt PoE Type 3 (60 Watts) and IEEE 802.3bt PoE Type 4 (90 Watts)
 - Cisco UPoE (60 Watts), Cisco UPoE+ (90 Watts) and Power over HDBaseT™ PoH (95 Watts)

REACTION TO FIRE

CHARACTERISTIC	STANDARD	RATING
Single Cable Flame Rating	IEC 60332-1-2	Pass
Bundled Cable Flame Rating	EN 50399 20.5kW source	Cca
Smoke Production	EN 50399	s1a
Flaming Droplets/Particles	EN 50399	d1
Acid Gas Emission/Acidity	EN 50267-2-3	a1
Classification/EuroClass	EN 13501-6	Cca s1a d1 a1

Category 6 F/FTP EuroClass Cca Cables

Datasheet: GD103458v12



PRIMARY ELECTRICAL PARAMETERS

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE @ 20°C
Conductor Loop Resistance	Max 19 Ω/100m	14Ω/100m
Conductor Resistance Unbalance	Max 2%	0.1%
Insulation Resistance	>5GΩ.km	>50GΩ.km
Dielectric Strength	2500 Vdc/2secs	Pass

SECONDARY ELECTRICAL PARAMETERS

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE @ 20°C
Velocity of Propagation	<534nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay Skew	Max 45nsec/100m @ 100MHz	4nsec/100m @ 100MHz
Mean Characteristic Impedance	100Ω +/- 5Ω @ 100MHz	100Ω ± 3Ω @ 100MHz
Coupling Attenuation	Type 1b	84dB
Transfer Impedance	Grade 2	11mΩ/m @ 10MHz

ELECTRICAL PERFORMANCE

Frequency (MHz)		1	4	10	20	100	200	250	500	550
Insertion Loss (dB/100m)	Standard	2.0	3.8	6.0	8.5	19.8	29.0	32.8	N/A	N/A
	Typical	1.9	3.5	5.5	7.8	18.0	26.1	29.4	43.0	45.4
NEXT (dB)	Standard	75.3	66.3	60.3	55.8	45.3	40.8	39.3	N/A	N/A
	Typical	100.0	100.0	100.0	100.0	94.3	88.9	87.1	81.7	81.0
PSNEXT (dB)	Standard	72.3	63.3	57.3	52.8	42.3	37.8	36.3	N/A	N/A
	Typical	97.0	97.0	97.0	97.0	91.3	85.9	84.1	78.7	78.0
ACR-F (dB)	Standard	67.8	58.0	50.0	44.0	30.0	24.0	22.0	N/A	N/A
	Typical	90.0	90.0	90.0	84.8	70.8	64.8	62.8	56.8	56.0
PSACR-F (dB)	Standard	64.8	55.0	47.0	41.0	27.0	21.0	19.0	N/A	N/A
	Typical	87.0	87.0	87.0	81.8	67.8	61.8	59.8	53.8	53.0
Return Loss (dB)	Standard	20.0	23.0	25.0	25.0	20.1	18.0	17.3	N/A	N/A
	Typical	27.0	30.0	30.0	30.0	25.1	23.0	22.3	20.2	19.9

- The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters
- N/A – Not Applicable

INSTALLATION

Temperature (Installation)	0°C to +50°C	Min Bend Radius (Installation)	8 x Outer Diameter
Temperature (Operation)	-20°C to +75°C	Min Bend Radius (Operation)	4 x Outer Diameter
Max Tensile Load (Installation)	10kg	Field Test NVP Value	0.80
Segregation Class	Class D		

Category 6 F/FTP EuroClass Cca Cables

Datasheet: GD103458v12



STANDARD PACKAGING SPECIFICATIONS

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Reel Size Flange Dia. x Width (mm)	Gross Weight (kg/Item)	Items Per Pallet
C6F/FTP-Cca-500GN	500	Green†	7.0	50.2	400 x 390	27.5	12
C6F/FTP-Cca-1000GN	1000	Green†	7.0	50.2	600 x 325	55.9	6
C6F/FTP-Cca-D500GN††	500	Green†	14.3 x 7.1	102.4	600 x 325	57.7	6

†Also available in a range of non-standard colors

†† 'D' denotes Duplex Cable

COUNTRY OF ORIGIN

COO: United Kingdom

*“Leviton is **dedicated to designing, developing and manufacturing** sustainable **high-performance** structured cabling and specialty **cabling solutions.**”*

The information contained in this document is valid and correct at the time of issue. Leviton reserves the right to modify details without notice in light of subsequent standard/specification changes and ongoing technical developments.