

# Category 6 U/FTP EuroClass Eca Cables

Datasheet: GD103084v14




## APPLICATION

Leviton Category 6 U/FTP cables exceed the Category 6 performance standards. They are specified to 250MHz and are suitable for use in all Class E structured wiring cable systems. The applications supported include Gigabit Ethernet, Power over Ethernet, and broadband video transmissions at frequencies up to 250MHz.

## FEATURES AND BENEFITS

- 23 AWG solid annealed copper wire
- Gas injection foamed polyolefin core insulation – offering superior signal speed
- 4 twisted pairs individually screened and cabled together – providing EMI immunity
- Available in a range of jacket materials – to suit a variety of installation environments and color coded for identification
- Designed to support all Class E protocols including Gigabit Ethernet
- HFFR-LS\* versions meet the requirements of the Construction Products Regulation (CPR) EuroClass Eca
- Included in the Leviton Limited 25-Year System Warranty when used in conjunction with Leviton copper connectivity. System warranties are available for qualified projects installed by certified contractors

\*Halogen Free Flame Retardant – Low Smoke



## STANDARDS

- Designed and constructed to give optimum electrical performance to the following standards:
  - ISO/IEC 11801 Class E, IEC 61156-5
  - EN50173-1 and EN 50288-5-1
  - ANSI/TIA 568.2-D
- Recommended for PoE standards:
  - IEEE 802.3bt PoE Type 1 (15.4 Watts) formerly 802.3af and IEEE 802.3bt PoE Type 2 (30 Watts) formerly 802.3at
  - IEEE 802.3bt PoE Type 3 (60 Watts) and IEEE 802.3bt PoE Type 4 (90 Watts)
  - Cisco UPoE (60 Watts), Cisco UPoE+ (90 Watts) and Power over HDBaseT™ PoH (95 Watts)

## MATERIAL IDENTIFICATION

Material Identifier	HF1	HF1-X
Material Description	Standard HFFR-LS	Inner - HFFR-LS Outer - Polyethylene
Flammability Rating	IEC 60332-1-2	N/A – External Only
Fire EuroClass EN13501-6	Eca	N/A – External Only
Smoke Emission	IEC 61034-1 & 2	N/A – External Only
Acid Gas Emission	IEC 60754-2	N/A – External Only
Color	Violet	Inner - Violet Outer - Black

# Category 6 U/FTP EuroClass Eca Cables

Datasheet: GD103084v14



## PRIMARY ELECTRICAL PARAMETERS

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE @ 20°C
Conductor Loop Resistance	Max 19 Ω/100m	14Ω/100m
Conductor Resistance Unbalance	Max 2%	0.1%
Insulation Resistance	>5GΩ.km	>50GΩ.km
Dielectric Strength	2500 Vdc/2secs	Pass

## SECONDARY ELECTRICAL PARAMETERS

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE @ 20°C
Velocity of Propagation	<534nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay Skew	Max 25nsec/100m @ 100MHz	4nsec/100m @ 100MHz
Mean Characteristic Impedance	100Ω +/- 5Ω @ 100MHz	100Ω ± 3Ω @ 100MHz
Coupling Attenuation	Type 1b	75dB
Transfer Impedance	Grade 2	28mΩ/m @ 10MHz

## ELECTRICAL PERFORMANCE

Frequency (MHz)		1	4	10	20	100	200	250	500	550
Insertion Loss (dB/100m)	Standard	2.0	3.8	6.0	8.5	19.8	29.0	32.8	N/A	N/A
	<b>Typical</b>	<b>1.9</b>	<b>3.5</b>	<b>5.5</b>	<b>7.8</b>	<b>18.0</b>	<b>26.1</b>	<b>29.4</b>	<b>43.0</b>	<b>45.4</b>
NEXT (dB)	Standard	75.3	66.3	60.3	55.8	45.3	40.8	39.3	N/A	N/A
	<b>Typical</b>	<b>100.0</b>	<b>100.0</b>	<b>100.0</b>	<b>100.0</b>	<b>94.3</b>	<b>88.9</b>	<b>87.1</b>	<b>81.7</b>	<b>81.0</b>
PSNEXT (dB)	Standard	72.3	63.3	57.3	52.8	42.3	37.8	36.3	N/A	N/A
	<b>Typical</b>	<b>97.0</b>	<b>97.0</b>	<b>97.0</b>	<b>97.0</b>	<b>91.3</b>	<b>85.9</b>	<b>84.1</b>	<b>78.7</b>	<b>78.0</b>
ACR-F (dB)	Standard	67.8	58.0	50.0	44.0	30.0	24.0	22.0	N/A	N/A
	<b>Typical</b>	<b>90.0</b>	<b>90.0</b>	<b>90.0</b>	<b>84.8</b>	<b>70.8</b>	<b>64.8</b>	<b>62.8</b>	<b>56.8</b>	<b>56.0</b>
PSACR-F (dB)	Standard	64.8	55.0	47.0	41.0	27.0	21.0	19.0	N/A	N/A
	<b>Typical</b>	<b>87.0</b>	<b>87.0</b>	<b>87.0</b>	<b>81.8</b>	<b>67.8</b>	<b>61.8</b>	<b>59.8</b>	<b>53.8</b>	<b>53.0</b>
Return Loss (dB)	Standard	20.0	23.0	25.0	25.0	20.1	18.0	17.3	N/A	N/A
	<b>Typical</b>	<b>27.0</b>	<b>30.0</b>	<b>30.0</b>	<b>30.0</b>	<b>25.1</b>	<b>23.0</b>	<b>22.3</b>	<b>20.2</b>	<b>19.9</b>

- The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters
- N/A – Not Applicable

## INSTALLATION

Temperature (Installation)	0°C to +50°C	Min Bend Radius (Installation)	8 x Outer Diameter
Temperature (Operation)	-20°C to +75°C	Min Bend Radius (Operation)	4 x Outer Diameter
Max Tensile Load (Installation)	10kg per simplex cable	Field Test NVP Value	0.80
Segregation Class	Class C		

# Category 6 U/FTP EuroClass Eca Cables

Datasheet: GD103084v14



## STANDARD PACKAGING SPECIFICATIONS - REELS

Part Number	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Packaging Dimensions (mm)	Gross Weight (kg/Item)	Items Per Pallet
C6U/FTP-HF1-Eca-500VT <sup>†</sup>	6.8	45.0	400 x 390	25	12
C6U/FTP-HF1-Eca-D500VT <sup>‡</sup>	6.8 x 13.7	90.0	600 x 405	51.5	4

<sup>†</sup>500 = 500m length

<sup>‡</sup>'D' denotes Duplex Cable

## STANDARD PACKAGING SPECIFICATIONS - BOXES

Part Number	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Box Size L x W x H (mm)	Gross Weight (kg/Item)	Items Per Pallet
C6U/FTP-HF1-Eca-Rlx-305VT	6.8	45.0	475 x 295 x 475	14.7	12

## COUNTRY OF ORIGIN

COO: United Kingdom

*“Leviton is **dedicated to designing, developing and manufacturing** sustainable **high-performance** structured cabling and speciality **cabling solutions.**”*

The information contained in this document is valid and correct at the time of issue. Leviton reserves the right to modify details without notice in light of subsequent standard/specification changes and ongoing technical developments.