


Category 6A U/FTP AC6Z Euroclass Eca Cables

APPLICATION

Leviton AC6Z cables exceed the Category 6A performance standards in a channel of up to 70m in length. They are specified to 500MHz and are suitable for use in all class EA structured wiring cable systems. AC6Z cables have been designed specifically for the challenges in the data center environment by being smaller and lighter than equivalent conventional cables. AC6Z cables support 10 Gigabit Ethernet, Gigabit Ethernet, Power over Ethernet (PoE), voice, and broadband video transmissions at frequencies up to 500MHz.



FEATURES & BENEFITS

- 26 AWG solid annealed copper wire
- 4 twisted pairs individually screened and cabled together – providing EMI immunity
- Available in a range of HFFR-LS (Halogen Free Flame Retardant – Low Smoke) jacket materials to suit a variety of installation environments, including CPR fire performance ratings Eca, Dca, Cca and B2ca and color coded for identification
- Designed and manufactured in a carbon neutral facility in the UK
- Delivered in 100% recyclable packaging

STANDARDS & REGULATIONS

- ISO/IEC 11801 Class E_A
- IEC 61156-6
- EN50173-1
- EN 50288-10-2
- ANSI/TIA 568.2-D
- IEEE 802.3 PoE Type 1, 2, 3, 4 (90 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

COUNTRY OF ORIGIN

UK

WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](https://www.leviton.com/ns/warranty)

PRODUCT SPECIFICATIONS
Category 6A U/FTP AC6Z Euroclass Eca Cables

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS

Freq.	RL (dB)		NEXT (dB)		PS NEXT (dB)		IL (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	20.0	27.0	75.3	100.0	72.3	97.0	2.1	2.4
4	23.0	30.0	66.3	100.0	63.3	97.0	3.8	4.4
10	25.0	30.0	60.3	100.0	57.3	97.0	5.9	6.8
20	25.0	30.0	55.8	100.0	52.8	97.0	8.4	9.7
100	20.1	25.1	45.3	94.3	42.3	91.3	19.1	22.0
200	18.0	23.0	40.8	88.9	37.8	85.9	27.6	31.7
250	17.3	22.3	39.3	87.1	36.3	84.1	31.1	35.7
500	17.3	20.2	34.8	81.7	31.8	78.7	45.3	52.0
550	—	19.9	—	81.0	—	78.0	—	54.8

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED

Freq.	ACRF (dB)		PSACRF (dB)		PSA NEXT (dB)		PSAACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	68.0	90.0	65.0	87.0	67.0	100.0	67.0	98.1
4	56.0	90.0	53.0	87.0	67.0	100.0	66.2	96.5
10	48.0	90.0	45.0	87.0	67.0	100.0	58.2	94.5
20	42.0	84.8	39.0	81.8	67.0	100.0	52.2	92.2
100	28.0	70.8	25.0	67.8	62.5	100.0	38.2	82.0
200	22.0	64.8	19.0	61.8	58.0	100.0	32.2	73.9
250	20.0	62.8	17.0	59.8	56.5	100.0	30.2	70.6
500	14.0	56.8	11.0	53.8	52.0	100.0	24.2	57.0
550	—	56.0	—	53.0	—	100.0	—	54.6

- The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters
- N/A – Not Applicable

PRODUCT SPECIFICATIONS

Category 6A U/FTP AC6Z Euroclass Eca Cables

CHARACTERISTICS

Installation Characteristics	
Min Bend Radius (Installation)	8 x Outer Diameter
Min Bend Radius (Operation)	4 x Outer Diameter
Field Test NVP Value	0.80
Temp. (Installation)	0 °C to +50 °C
Temp. (Operating)	-20 °C to +75 °C
Segregation Class	Class C

TECHNICAL SPECIFICATIONS

Primary Electrical Properties (20 °C)		
CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE
Conductor Loop Resistance	Max 28.5 Ω/100 m	23Ω/100m (<17Ω/70m)
Conductor Resistance Unbalance	Max 2%	0.2%
Insulation Resistance	>5GΩ.km	>50GΩ.km
Dielectric Strength	2500 Vdc/2secs	Pass

TECHNICAL SPECIFICATIONS

Secondary Electrical Properties (20 °C)		
CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE
Velocity of Propagation	<537.6nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay Skew	Max 45nsec/100m @ 100MHz	3nsec/100m @ 100MHz
Characteristic Impedance (Fitted)	100Ω +/- 5Ω @ 100MHz	100Ω ± 3Ω @ 100 MHz

REACTION TO FIRE

Flammability Rating	IEC/EN 60332-1-2
EuroClass Level EN13501-6	Eca

STANDARD PACKAGING SPECIFICATIONS – REELS

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Reel Size	Gross Weight (kg/Item)	Items Per Pallet
AC6-DCZ-Eca-500VT	500	Violet†	5.6	32.5	400 x 315	18.3	18
AC6-DCZ-Eca-1000VT	1000	Violet†	5.6	32.5	465 x 375	35.5	6

* Available in Latin America

** May be ordered using alternative part number in some regions

STANDARD PACKAGING SPECIFICATIONS – BOXES

Part Number	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Box Size (L x W x H)	Gross Weight (kg/Item)	Items Per Pallet
AC6-DCZ-Eca-Rlx-305VTS§	Violet†	5.6	32.5	405 x 265 x 405	10.1	27 or 18††

§ = 305m box

† Also available in a range of non-standard colors

†† 3 Layer pallet is 27 boxes, 2 layers is 18

For further support information, visit Leviton.com/ns/support

Page 3 of 3

USA
 Network Solutions Headquarters
 +1 (800) 722 2082
infoUSA@leviton.com
 Leviton Cable (formerly Berk-Tek)
 +1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
 +852 3620 2602
infoAPAC@leviton.com

Canada
 +1 (800) 461 2002
infoCanada@leviton.com

Europe
 +44 (0) 1592 772124
infoEurope@leviton.com

Latin America
 MX: +52 (55) 2128 6286
 LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
 +971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.