


AC6FF Cat 6A F/FTP Euroclass Dca Cables

APPLICATION

Leviton Cat 6A F/FTP cables exceed Category 6A performance standards. They are rated to 500 MHz and are suitable for use in all Class E_A structured cable systems. The applications supported include 10 Gigabit Ethernet, Gigabit Ethernet, Power over Ethernet (PoE), and broadband video transmissions at frequencies up to 500 MHz.



COUNTRY OF ORIGIN

UK

WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](https://leviton.com/ns/warranty)

FEATURES & BENEFITS

- 23 AWG solid annealed copper wire
- 4 twisted pairs individually screened and cabled together – providing excellent EMI immunity
- Overall aluminum polyester screen – for improved shielding efficiency and increased heat dissipation
- Designed to support all Class E_A protocols including 10GBASE-T
- Halogen Free Flame Retardant – Low Smoke (HFFR-LS)
- HFFR-LS material meets the requirements of the Construction Products Regulation (CPR) Euroclass Dca
- Blue jacket to identify Euroclass level Dca. Also available in a range of non-standard colors
- CE marked for CPR
- Delivered in 100% recyclable packaging

STANDARDS & REGULATIONS

- ISO/IEC 11801 Class E_A
- IEC 61156-5
- EN 50173-1
- EN 50288-10-1
- ANSI/TIA 568.2-D
- 10GBASE-T
- 802.11ac wireless
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

PRODUCT SPECIFICATIONS

AC6FF Cat 6A F/FTP Euroclass Dca Cables

TECHNICAL SPECIFICATIONS

Primary Electrical Parameters

Conductor loop resistance	Max 19 Ω/100m	14Ω/100m
Conductor resistance unbalance	Max. 2%	0.1%
Insulation resistance	>5GΩ.km	>50GΩ.km
Dielectric strength	2500 Vdc/2secs	Pass

Secondary Electrical Parameters

Velocity of propagation	<534nsec/100m @ 100MHz	413nsec/100m @ 100MHz
Delay skew	Max. 45nsec/100m @ 100MHz	4nsec/100m @ 100MHz
Mean Characteristic Impedance	100Ω +/- 5Ω @ 100MHz	100Ω ± 3Ω @ 100MHz
Coupling Attenuation	Type 1b	84dB
Transfer Impedance	Grade 2	11mΩ/m @ 10MHz

MECHANICAL SPECIFICATIONS

Usage Characteristics

Category	Cat 6A
Type of cable	F/FTP
Temp. (Installation)	0 °C to +50 °C (+32 °F to +122 °F)
Temp. (Operating)	-20 °C to +75 °C (-4 °F to +167 °F)

TECHNICAL DATA - PHYSICAL

Max. tensile load (Installation)	10kg
Segregation class	Class D
Min. bend radius (Installation)	8 x Outer Diameter
Min. bend radius (Operation)	4 x Outer Diameter
Field test NVP value	0.80

REACTION TO FIRE (SINGLE CABLES)

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / EuroClass	—	EN 13501-6	Dca s1a d2 a1
Single Cable Flame Rating	IEC 60332-1-2	—	—
Smoke Production	—	EN 50399	s1a
Flaming Droplets/Particle	—	EN 50399	d2
Acid Gas Emission/Acidity	—	EN 50267-2-3	a1

REACTION TO FIRE (DUPLEX CABLES)

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / EuroClass	—	EN 13501-6	Dca s1a d1 a1
Single Cable Flame Rating	IEC 60332-1-2	—	—
Smoke Production	—	EN 50399	s1a
Flaming Droplets/Particle	—	EN 50399	d1
Acid Gas Emission/Acidity	—	EN 50267-2-3	a1

PRODUCT SPECIFICATIONS
AC6FF Cat 6A F/FTP Euroclass Dca Cables



AC6FF Cat 6A F/FTP Euroclass Dca Cables

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS

Freq. MHz	IL (dB)		NEXT (dB)		PSNEXT (dB)		ACRF (dB)		PSACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	2.1	1.9	75.3	100.0	72.3	97.0	68.0	90.0	65.0	87.0
4	3.8	3.5	66.3	100.0	63.3	97.0	56.0	90.0	53.0	87.0
10	5.9	5.5	60.3	100.0	57.3	97.0	48.0	90.0	45.0	87.0
20	8.4	7.8	55.8	100.0	52.8	97.0	42.0	84.8	39.0	81.8
100	19.1	18.0	45.3	94.3	42.3	91.3	28.0	70.8	25.0	67.8
200	27.6	26.1	40.8	88.9	37.8	85.9	22.0	64.8	19.0	61.8
250	31.1	29.4	39.3	87.1	36.3	84.1	20.0	62.8	17.0	59.8
500	45.3	43.0	34.8	81.7	31.8	78.7	14.0	56.8	11.0	53.8
550	—	45.4	—	81.0	—	78.0	—	56.0	—	53.0

Note: The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED

Freq. MHz	RL (dB)		PSANEXT (dB)		PSAACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical
1	20.0	27.0	67.0	100.0	67.0	98.1
4	23.0	30.0	67.0	100.0	66.2	96.5
10	25.0	30.0	67.0	100.0	58.2	94.5
20	25.0	30.0	67.0	100.0	52.2	92.2
100	20.1	25.1	62.5	100.0	38.2	82.0
200	18.0	23.0	58.0	100.0	32.2	73.9
250	17.3	22.3	56.5	100.0	30.2	70.6
500	17.3	20.2	52.0	100.0	24.2	57.0
550	—	19.9	—	100.0	—	54.6

Note: The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters

STANDARD PACKAGING SPECIFICATIONS - REELS

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Reel Size Flange Dia. x Width (mm)	Gross Weight (kg/Item)	Items Per Pallet
AC6F/FTP-Dca-500BU	500	Blue†	7.1	50.4	465 x 390	27.7	12
AC6F/FTP-Dca-1000BU	1000	Blue†	7.1	50.4	600 x 325	56.4	6
AC6F/FTP-Dca-D500BU††	500	Blue†	7.1 x 14.4	100.9	600 x 325	56.9	6

† Also available in a range of non-standard colors †† Duplex Cable

For further support information, visit Leviton.com/ns/support

USA
 Network Solutions Headquarters
 +1 (800) 722 2082
infoUSA@leviton.com
 Leviton Cable (formerly Berk-Tek)
 +1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
 +852 3620 2602
infoAPAC@leviton.com

Canada
 +1 (800) 461 2002
infoCanada@leviton.com

Europe
 +44 (0) 1592 772124
infoEurope@leviton.com

Latin America
 MX: +52 (55) 2128 6286
 LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
 +971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.