


## AX0 Cat 6 UTP Jack

### APPLICATION

The AX0 Cat 6 UTP jack supports 1000BASE-T networks and is ideal for applications requiring optimal network performance with additional features. The jack is designed to be used with a variety of Leviton modular panels, wallplates, surface-mount boxes, and QUICKPORT™ compatible products.



### SPECIFICATION

The jack shall meet the requirements for channel and component-level electrical transmission performance as described in ANSI/TIA-568.2 (Cat 6), ISO/IEC 11801-1 (Class E), and EN 50173-1 (Class E). The jack shall be compliant with ANSI/TIA-1096-A, c(UL)us Listed, and be independently verified for electrical transmission performance and power delivery. All plastics used in construction of jack bodies shall be fire retardant with a UL flammability rating of 94V-0. The jack shall support tool-free termination and re-termination and shall not require a specialized termination tool. The modular jack shall fit in a variety of telecommunications wallplates, outlets, and field-configurable patch panels and patch blocks. The jack wiring shall be universal to accommodate T568A and T568B wiring schemes. The jack shall be compatible with interchangeable icons. The jack shall be compliant with IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max).

### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/support](http://Leviton.com/ns/support)

### FEATURES & BENEFITS

- Independently tested and guaranteed to meet component performance
- Supports tool-free termination/re-termination and requires no specialized termination tool
- Supports a wider range of applications (e.g. shallow boxes, enclosures, and bend radius)
- Terminates from 26 to 22 AWG solid or stranded conductors for use on various cable types
- Withstands 20 re-termination cycles
- Jack contacts are tested to exceed 750 plug-mating cycles to ensure system longevity
- Compatible with interchangeable icons
- Available in 3 colors for color coding or organization
- Compatible with QUICKPORT™ and modular panels, wallplates, and surface-mount boxes

### STANDARDS & REGULATIONS

- ANSI/TIA-568.2
- ISO/IEC 11801-1
- EN 50173-1
- ANSI/TIA-1096-A (formerly FCC Part 68)
- IEC 60603-7 and -7-4
- IEC 60512-99-002
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)
- c(UL)us Listed (UL1863)
- RoHS 3

### MECHANICAL SPECIFICATIONS

Dimensions: See Page 2

Materials: **Jack Body:**  
Polycarbonate

**Spring-Wire Contacts:**

High-quality, copper-based alloy (phosphor bronze), plated with 50 microinches of gold over nickel plating for lowest contact resistance and maximum life

Temp. (Storage): -40 °C to +70 °C (-40 °F to +158 °F)


Temp. (Installation): Refer to cable installation temperature

Temp. (Operating): -10 °C to +60 °C (+14 °F to +140 °F)

Humidity (Max.): 95% relative humidity, non-condensing

**PRODUCT SPECIFICATIONS**  
**AX61U-Gx6**

**AX61U-Gx6**



PART NUMBER	
Description	Part No.
AX0 Cat 6 UTP Jack, black, 12-Pack	AX61U-GE6
AX0 Cat 6 UTP Jack, white, 12-Pack	AX61U-GW6
AX0 Cat 6 UTP Jack, blue, 12-Pack	AX61U-GL6

Icons (ICONS-ICx) can be ordered separately in 72-quantity packs.  
x = icon color



For further support information, visit [Leviton.com/ns/support](http://Leviton.com/ns/support)